




SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S13A4PV00**	D09S13A6PV00**
15	39.14	33.32	25.18	24.54	19.18	D15S13A4PV00**	D15S13A6PV00**
25	53.03	47.04	39.12	38.25	33.12	D25S13A4PV00**	D25S13A6PV00**
37	69.32	63.50	55.68	54.71	49.68	D37S13A4PV00**	D37S13A6PV00**
						Gold flash	0,76 μ gold

REQUIREMENTS

Technical characteristics:

Shell: steel tin plated

Insulators: self-extinguishing thermoplastic, UL class 94V0

Contacts size 20:phosphor bronze,gold on mating end,bright tin on termination end over nickel on entire contact

Cycles : 500 for plating 6

Cycles : 200 for plating 4

Screwlock: brass, tin plated

Electrical characteristics:

max.current rating: 5A

Test voltage: 1000V

Rated voltage: 300V

Contact resistance: $\leq 15\text{m}\Omega$

Shell resistance: $\leq 5\text{m}\Omega$

Insulation resistance: $\geq 5000\text{M}\Omega$


Climatic characteristics:

Operating temperature range: -55°C $+125^{\circ}\text{C}$

Dimensions:

in accordance with MIL-C-24308

LF FOR LEAD FREE



FOR ROHS DETAILS REFER DWG.NO: C01-8646-0000

[illegible]