

# T2240 Serial Matrix Printer

## Rugged, Fast and Affordable



- Print speeds up to 500 characters per second at 12 CPI!
- 10,000 pages per month workload.
- 24-pin configurations produce letter-quality print.
- 80-column (small footprint) or 136-column configurations available.
- Straight paper path means jam-free operation.
- Up to 6-part forms.
- Front load single sheet feed standard; optional 150 page sheet feeder.
- Zero tear-off means no wasted forms.

### **Fast and Affordable.**

Rugged, fast and affordable, the T2240 is built to handle multi-part forms with ease. Specially engineered "flat" push tractors drive forms through an uncommonly straight paper path for jam-free operation. With accessible, front-load tractors and a platen knob to facilitate forms adjustment, paper loading is quick, and down time minimal.

The T2240 industrial strength forms printers deliver versatile transaction printing in no time, every time. Versatile Configuration. Depending on your specific needs, there is a configuration exactly suited for you.

### **Ideal For Many Markets & Applications.**

Federal, State & Local Government - Print tax forms, payroll checks, expense reports, inventory reports, invoices.

Manufacturing, Transportation, & Distribution - Print pick lists, shipping labels and freight bills. Excellent readability on all industry standard bar codes, including POSTNET. Energy Star compliant and low-cost to own and operate.

Healthcare - Handles a wide variety of media including bar code labels for patient charts, prescription labels, pre-printed forms for billing departments. High reliability ensures accurate patient information with 24-wire print quality.

---

Available Configuration:

**T2240/9** - 500 CPS Printer, 9 Wire, 80 Column, Parallel

**T2240/24** - 440 CPS Printer, 24 Wire, 80 Column, Parallel

<b>Print Speed</b>	9 wire Printhead: At 10, 12 cpi: Draft: 413, 500 Copy/Draft: 310, 310 NLQ: 77, 77; 24 wire Printhead: At 10, 12 cpi: Draft: 409, 440 Copy/Draft: 275, 330 LQ: 92, 110
<b>Print Method</b>	Serial Impact, 80 columns.
<b>Resolution</b>	9 wire: 144 X 240 DPI. 24 wire: 360 X 360 DPI.
<b>Character Density</b>	10, 12, 15, 17.1, 20 cpi + Elongated
<b>Line Density</b>	2, 3, 4, 6, 8, 12 lpi
<b>Character Sets</b>	256 characters, 20 international sets, IBM PC® and Epson®
<b>Printhead Life</b>	300 million
<b>Printhead Type</b>	9 wire or 24 wire
<b>Memory</b>	64kB
<b>Standard Connectivity</b>	Bi-directional Centronics Parallel, 64K interface buffer
<b>Optional Connectivity</b>	RS232 Serial, RS422 Serial, TallyCom+ 10/100BaseT External Print Server
<b>Standard Emulation</b>	9-wire: MTPL*, IBM® Proprinter XL, Epson® FX850+/FX1050+. 24-wire: MTPL*, IBM® Proprinter XL24e, Epson® LQ850+/LQ1050+ /EscP
<b>Fonts</b>	9-wire: Draft, Copy Draft, Courier, Quadrato, OCR A & OCR B, Bar Code + LCP. 24-wire: Draft, Copy Draft, Courier, Roman, San Serif, Prestige, Script, OCR A & OCR B, Bar Codes + LCP
<b>Consumables</b>	4 million characters
<b>STD Paper Handling</b>	Flat push tractors (front/bottom), straight path for continuous forms and labels, auto paper load, auto quick tear, auto view, paper advance knob
<b>Opt'l Paper Handling</b>	push tractor, automatic sheet feeder
<b>Number of Copies</b>	9-wire: 1 + 5; 24-wire: 1 + 3
<b>Paper Type</b>	Continuous, Cut Forms (optional feeder)
<b>Paper Weight</b>	NA
<b>Paper Size</b>	Width: 3–10"; Length: continuous Forms 3"-22", Cut Forms 3"-14"
<b>Physical Weight</b>	17.6 lbs
<b>Physical Size</b>	19" x 9.7" x 7.9"
<b>Power Voltage</b>	AC 120V +/- 10% OR AC 220V - 240V +/- 10%
<b>Power Frequency</b>	60Hz OR 50Hz
<b>Power Consumption</b>	50 watts (operating)
<b>Compliance</b>	Energy Star compliant, Ozone-free, RoHS, Microsoft, ISO-compliant
<b>Workload</b>	Up to 10,000 pages per month
<b>Reliability MTBF</b>	12,500 hours @ 100% duty cycle
<b>Drivers</b>	Windows 95/98/Me, NT 4.0, 2000, XP; SAP
<b>Temperature</b>	NA
<b>Humidity</b>	NA
<b>Acoustic</b>	53 dB (A) LQ
<b>Warranty</b>	Two Years Return To Depot
<b>Option 1</b>	second front push tractors; front automatic cut sheet feeder
<b>Option 2</b>	RS-232 Serial Interface; RS-422 Serial Interface; TallyCom+ 10/100BaseT External Print Server
<b>Option 3</b>	Printer Stand; Paper Basket; Castors



Tally and TallyGenicom are registered trademarks of TallyGenicom, L.P. All other company and product names are trademarks or registered trademarks of their respective owner. Specifications are subject to change without notice. Copyright © 2009 TallyGenicom, L.P.

Printed Date: 05/17/2009



4500 Daly Drive, Suite 100  
Chantilly, VA 20151  
T 800.436.4266  
www.tallygenicom.com