





| LOC |  | DIST |  | REVISIONS |     |                           |  |  |           |     |      |
|-----|--|------|--|-----------|-----|---------------------------|--|--|-----------|-----|------|
| AD  |  | 00   |  | P         | LTR | DESCRIPTION               |  |  | DATE      | DWN | APVD |
|     |  |      |  |           | 5   | REVISED PER ECO-12-006575 |  |  | 30APR2012 | KH  | RP   |
|     |  |      |  |           |     |                           |  |  |           |     |      |
|     |  |      |  |           |     |                           |  |  |           |     |      |
|     |  |      |  |           |     |                           |  |  |           |     |      |
|     |  |      |  |           |     |                           |  |  |           |     |      |

7  
⊕ Ø0.05Ⓢ X|Y  
FINISHED HOLE SIZE  
AND PLATED THRU HOLES

CONNECTOR OUTLINE



- 1 MATERIAL:  
CONTACT AND SHIELD: PHOS BRONZE  
HOUSING AND CHICKLET: LCP, UL 94V-0, COLOR: BLACK
- 2 FINISH:  
CONTACT AREA FINISH CONFORMS TO THE REQUIREMENTS  
OF TE PRODUCT SPECIFICATION 108-2303; BASED ON  
TELCORDIA GR-1217-CORE FOR SYSTEM QUALITY  
LEVEL III APPLICATIONS IN CONTROLLED  
ENVIRONMENTS (CENTRAL OFFICE).
- 3 CONNECTOR MARKED WITH PART NUMBER, DATE CODE, 85 OHM, AND STANDARD IN  
APPROXIMATE AREA SHOWN.
- 4 DIMENSION APPLIES TO CENTERLINE OF THRU HOLE.
- 5 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
6. CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT.  
TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995.
- 7 REFERENCE APPLICATION SPEC FOR RECOMMENDED PLATED THRU  
HOLE DIAMETER AND PLATING THICKNESS.
- 8 THE GROUNDS IN EACH COLUMN ARE COMMONED.



PRELIMINARY - NOT  
RELEASED FOR PRODUCTION

|                                           |  |                                 |  |  |
|-------------------------------------------|--|---------------------------------|--|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT.    |  | OWN<br>W. SOURBEER<br>01MAY2008 |  |  |
| DIMENSIONS:                               |  | CHK<br>C. RITTER<br>01MAY2008   |  |  |
| mm                                        |  | APVD<br>30APR2012               |  |  |
| TOLERANCES UNLESS<br>OTHERWISE SPECIFIED: |  | PRODUCT SPEC                    |  |  |
| 9 PLC ±                                   |  | 108-2303-1                      |  |  |
| 1 PLC ±                                   |  | APPLICATION SPEC                |  |  |
| 3 PLC ±                                   |  | 114-13243                       |  |  |
| 5 PLC ±                                   |  | WEIGHT                          |  |  |
| 4 PLC ±                                   |  | A100779                         |  |  |
| ANGLES                                    |  | C=1934951                       |  |  |
| FINISH                                    |  | CUSTOMER DRAWING                |  |  |
| MATERIAL                                  |  | SCALE 3:1                       |  |  |
|                                           |  | SHEET 1 OF 1                    |  |  |
|                                           |  | REV 5                           |  |  |

1934951-1  
PART NUMBER

STE TE Connectivity

RECEPTACLE ASSEMBLY, 3 PAIR,  
10 COLUMN  
Z-PACK TinMan 85 OHM