



NOTE

- 1-UNIT INCLUDES CAT. LIST. ISM23-T TYPE BASIC SWITCH (2)
- 2-TERMINALS ARE PLATED FOR SOLDERING
- 3-BASIC SWITCHES HAVE 24 K GOLD OVERLAY CONTACTS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

CHARACTERISTICS

ELECTRICAL DATA

SCALE FULL

CONTACT ARRANGEMENT
 S P D T (2)

DO NOT SCALE PRINT

30 VOLTS DC RATING

INDUCTIVE ---- SEA LEVEL - 1/2 AMP
 50,000 FT --- 1/2 AMP
 RESISTIVE ---- SEA LEVEL --- 1 AMP
 50,000 FT --- 1 AMP
 MAXIMUM INRUSH ----- 2 AMP

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE ±

	DIM. mm	TOL. mm/in	DIM. in	TOL. mm/in
NO PLACES	X	1/64	X	0.005
ONE PLACE	X,X	0.0018	X,X	0.0018
TWO PLACES	X,X,X	0.0005	X,X,X	0.0005
THREE PLACES	X,X,X,X		X,X,X,X	
ANGLES				

DESIGN UNITS ☐ SI METRIC ☒ US CUSTOMARY

WEIGHT .06 LB

13AT18-T

M

DRAWING
 NUMBER

ISSUE

7

REPLACES

PR-8915

CHECK

REVISIONS

A	WAS ETS PR8915
WJM	18 JUN 80
B	CO 50566-B
WJM	5 MAY 82
C	CO-52725
KAG	2 JUN 83
D	CO 66089
DAW	13 FEB 91

CHECK

19 JUN 80

19 JUN 80

19 JUN 80

19 JUN 80

19 JUN 80

19 JUN 80

19 JUN 80

19 JUN 80

19 JUN 80

19 JUN 80

FO-52848-A

DRAWN

19 JUN 80