

[Home](#) [About Us](#) [Products](#) [Applications](#) [Sales Support](#) [Contact Us](#) [Search](#) [Industrial Products](#) > [Jacks and Plugs](#) > [1/4" Jacks and Plugs](#) > [1/4" Open Frame Jacks](#) > [1/4" 3 Conductor Open Frame Jacks](#)

1/4" 3 Conductor Open Frame Jacks

[enlarge](#)

Littel-Jax phone jacks mate with standard commercial phone plugs and are available with .25 inch inside diameter bushings.

[Products](#)[Specifications](#)[User Guide](#)

Need more info? Contact Switchcraft customer service

[Printer friendly version](#)

MECHANICAL

Life: Commercial Jacks - 10,000 insertion/withdrawal cycles, minimum. Military Jacks - 20,000 insertions/withdrawals, minimum.

Mechanical Shock: Military Jacks - Per MIL-STD 202, method 213, Test Condition H (75g).

Vibration: Military Jacks - Per MIL-STD-202, method 213, (10-55 Hz).

Insertion/Withdrawal Forces: (see charts below)

Commercial Jacks		
Plug Diameter (inches)	.210	.250
Insertion (maximum)	7 lb.	7 lb.
Withdrawal (minimum)	1 lb.	1 lb.

ELECTRICAL

Contact Resistance: Commercial Jacks - .030 ohms maximum (initial), .050 ohms maximum (after humidity, durability exposure). Per MIL-STD-202E. Military Jacks - .010 ohms maximum (initial), .020 ohms maximum (after life), .10 ohms maximum (after salt spray).

Insulation Resistance: Commercial Jacks - 10,000 M(omega) minimum (initial), 1,000 M(omega) minimum (after humidity). Military Jacks - 10,000 M(omega) minimum (initial), 1,000 M(omega) minimum (after humidity, durability exposure).

Dielectric Withstanding Voltage: 500 V, 60 Hz (rms) AC.

Contact Rating: 1 A, 25 V DC.

ENVIRONMENTAL

Thermal Range: Commercial Jacks; -55°C to +85°C (non-operating); -20°C to +65°C (operating). Military Jacks; -55°C to +85°C (non-operating); -40°C to +65°C (operating).

Thermal Shock: Commercial Jacks - Per MIL-STD 202, method 107. Military Jacks - Per MIL-STD 202, method 107.

Humidity: Commercial Jacks - Per MIL-STD 202, method 106. Military Jacks - 0% to 95% operating and non-operating.

Salt Spray: Commercial Jacks - Per MIL-STD 202, method 101. Military Jacks - Per MIL-STD 202, method 101 (48 hours).

Moisture Resistance: Military Jacks - Per MIL-STD 202, method 106 (240 hours).

MATERIAL

Mounting Bushing: Nickel-plated copper alloy.

Insulation: Rigid plastic.

Springs: Special copper alloy. Integral contacts are standard in the isolated switching circuits; fine silver contacts in C12A switching circuit.

Sleeve Terminal: Copper alloy.

Hardware: Supplied with one Number **P10001** copper alloy nickel-plated hex nut, and one Number **S1022** steel nickel-plated washer - except copper alloy nickel-plated washer Number **S10451** supplied on C11, C12A and C12B.

* Commercial jacks feature integral contacts. Integral contacts should not be used where low contact resistance is a requirement.