



PRODUCT NO. NOTE ①	DIM L	DIM S
72337-000CA	0	13
72337-020CA	2	
72337-022CA	2.2	
72337-040CA	4	
72337-043CA	4.3	
72337-050CA	5	15.6
72337-000DA	0	
72337-020DA	2	
72337-022DA	2.2	
72337-040DA	4	
72337-043DA	4.3	21
72337-050DA	5	
72337-000FA	0	
72337-020FA	2	
72337-022FA	2.2	
72337-040FA	4	
72337-043FA	4.3	
72337-050FA	5	

NOTES:

- ① ADD "H" TO PART NUMBER FOR
OPTIONAL HOLD DOWN (2 PER ASSEMBLY).



- LINK TO MOVE ALONG INSIDE WALL
OF COVER PLATE SMOOTHLY AFTER ASSEMBLING
WITH HEADER.
- MATERIAL:
PLASTIC GUIDES: POLYPHTHARAMIDE UL94V-0
COLOR: BLACK
COVER PLATE: STAINLESS STEEL
EMI CONTACT: PHOSPHOR BRONZE
- FINISH:
EMI CONTACT: CONTACT AREA: 0.5um Au
UNDER PLATING: 2.0um Ni
- RECOMMENDED SCREW TORQUE:
1.0-1.5 MAX IN-LBS (1.2-1.7 CM-KGS)



mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		FCI Electronics www.fciconnect.com	
ltr	ecn no	dr	date	linear	.X±.3	projection	title	product family	code
A	V81135	RHG	8/9/98		.XX±.13	MM	NARROW BODY FRONT EJECT MECHANISM ASSEMBLY TYPE 123	MCA	-
B	T70090	RHG	4/28/97		.XXX±.051	1:1	size	dwg no	sheet
C	V12231	TFG	8/18/01	angles	0° ±2°		A4	72337	1 of 2
				dr	R.GRAPE 5/30/98				
				enqr	J.SPICKLER 5/30/98				
				chr	J.SPICKLER 5/30/98				
				appd	J.SPICKLER 5/30/98				
sheet	revision	C	C						
index	sheet	1	2						

cage code
22526


ACAD

PDM: Rev:C

STATUS: Released


Printed: Oct 12, 2010

PRODUCT NO. NOTE ①	DIM L	DIM S
72337-100CA	0	13
72337-120CA	2	
72337-122CA	2.2	
72337-140CA	4	
72337-143CA	4.3	
72337-150CA	5	15.8
72337-100DA	0	
72337-120DA	2	
72337-122DA	2.2	
72337-140DA	4	
72337-143DA	4.3	21
72337-150DA	5	
72337-100FA	0	
72337-120FA	2	
72337-122FA	2.2	
72337-140FA	4	
72337-143FA	4.3	
72337-150FA	5	




NOTES:

- ① ADD "H" TO PART NUMBER FOR
OPTIONAL HOLD DOWN (2 PER ASSEMBLY).



- LINK TO MOVE ALONG INSIDE WALL
OF COVER PLATE SMOOTHLY AFTER ASSEMBLING
WITH HEADER.
- MATERIAL:
PLASTIC GLIDES: POLYPHTHARAMIDE UL94V-0
COLOR: BLACK
COVER PLATE: STAINLESS STEEL
EMI CONTACT: PHOSPHOR BRONZE
- FINISH:
EMI CONTACT: CONTACT AREA: 0.5um Au
UNDER PLATING: 2.0um Ni
- RECOMMENDED SCREW TORQUE:
1.0-1.5 MAX IN-LBS (1.2-1.7 CM-KGS)



mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY	FCI Electronics www.fciconnect.com	
ltr	ecn no	dr	date	linear	.X±.3	projection	title	
C					.XX±.13	MM	NARROW BODY FRONT EJECT MECHANISM ASSEMBLY TYPE 123	
				angles	.XXX±.051	1:1	product family MCS	
				dr	0° ±2°		code	
				enr	R.GRAPE 5/30/98		size	
				chr	J.SPICKLER 5/30/98		dwg no	
				appd	J.SPICKLER 5/30/98		sheet	
sheet	revision						A4	
index	sheet						72337	
							2 of	

cage code
22526