



## VHL2-38-3WH/B

**0.6 m | 2 ft ValuLine® High Performance Low Profile Antenna, single-polarized, 37.000–40.000 GHz, UBR320, white antenna, polymer white radome without flash, compact pack—one-piece reflector**

### General Specifications

Antenna Type	VHL2 - ValuLine® High Performance Low Profile Antenna, single-polarized
Diameter, nominal	0.6 m   2 ft
Packing	Compact pack
Radome Color	White
Radome Material	Polymer
Reflector Construction	One-piece reflector
Antenna Input	UBR320
Antenna Color	White
Antenna Type	VHL2 - ValuLine® High Performance Low Profile Antenna, single-polarized
Diameter, nominal	0.6 m   2 ft
Flash Included	No
Polarization	Single

### Electrical Specifications

Operating Frequency Band	37.000 – 40.000 GHz
Beamwidth, Horizontal	0.9 °
Beamwidth, Vertical	0.9 °
Cross Polarization Discrimination (XPD)	30 dB
Electrical Compliance	Brazil Anatel Class 2   Canada SRSP 338.6 Part A   ETSI 302 217 Class 3B   US FCC Part 101A
Front-to-Back Ratio	64 dB
Gain, Low Band	44.6 dBi
Gain, Mid Band	45.2 dBi
Gain, Top Band	45.8 dBi
Operating Frequency Band	37.000 – 40.000 GHz
Radiation Pattern Envelope Reference (RPE)	7209B
Return Loss	17.7 dB
VSWR	1.30

### Mechanical Specifications

Fine Azimuth Adjustment	±15°
Fine Elevation Adjustment	±15°
Mounting Pipe Diameter	48 mm–115 mm   1.9 in–4.5 in
Net Weight	14 kg   31 lb

# Product Specifications

COMMSCOPE®

VHLP2-38-3WH/B

Side Struts, Included	0
Side Struts, Optional	0
Wind Velocity Operational	200 km/h   124 mph
Wind Velocity Survival Rating	250 km/h   155 mph

POWERED BY



## Wind Forces At Wind Velocity Survival Rating

Axial Force (FA)	1272 N   286 lbf
Side Force (FS)	630 N   142 lbf
Twisting Moment (MT)	473 N•m
Weight with 1/2 in (12 mm) Radial Ice	17 kg   37 lb
Zcg with 1/2 in (12 mm) Radial Ice	162 mm   6 in
Zcg without Ice	157 mm   6 in

# Product Specifications


COMMSCOPE®

VHLP2-38-3WH/B

POWERED BY

 ANDREW®

## Wind Forces At Wind Velocity Survival Rating Image



## Packed Dimensions

Gross Weight, Packed Antenna	16.0 kg   35.3 lb
Height	330.0 mm   13.0 in
Length	706.0 mm   27.8 in
Volume	0.2 m <sup>3</sup>
Width	798.0 mm   31.4 in

# Product Specifications


COMMSCOPE®

VHLP2-38-3WH/B

POWERED BY

 ANDREW®

## Antenna Dimensions And Mounting Information



Dimensions in Inches (mm)				
Antenna Size, ft (m)	A	B	C	D
2(0.6)	25.9 (658)	14.6 (372)	10.2 (259)	6.4 (162)

## Regulatory Compliance/Certifications

**Agency** ISO 9001:2008 **Classification** Designed, manufactured and/or distributed under this quality management system

### \* Footnotes

Axial Force (FA)	Maximum forces exerted on a supporting structure as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.
Cross Polarization Discrimination (XPD)	The difference between the peak of the co-polarized main beam and the maximum cross-polarized signal over an angle twice the 3 dB beamwidth of the co-polarized main beam.
Front-to-Back Ratio	Denotes highest radiation relative to the main beam, at $180^\circ \pm 40^\circ$ , across the band. Production antennas do not exceed rated values by more than 2 dB unless stated otherwise.
Gain, Mid Band	For a given frequency band, gain is primarily a function of antenna size. The gain of Andrew antennas is determined by either gain by comparison or by computer integration of the measured antenna patterns.
Operating Frequency Band	Bands correspond with CCIR recommendations or common allocations used throughout the world. Other ranges can be accommodated on special order.
Packing	Andrew standard packing is suitable for export. Antennas are shipped as

# Product Specifications

COMMSCOPE®

VHLP2-38-3WH/B

POWERED BY



standard in totally recyclable cardboard or wire-bound crates (dependent on product). For your convenience, Andrew offers heavy duty export packing options.

Radiation Pattern Envelope Reference (RPE)	Radiation patterns determine an antenna's ability to discriminate against unwanted signals under conditions of radio congestion. Radiation patterns are dependent on antenna series, size, and frequency.
Return Loss	The figure that indicates the proportion of radio waves incident upon the antenna that are rejected as a ratio of those that are accepted.
Side Force (FS)	Maximum side force exerted on the mounting pipe as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.
Twisting Moment (MT)	Maximum forces exerted on a supporting structure as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.
VSWR	Maximum; is the guaranteed Peak Voltage-Standing-Wave-Ratio within the operating band.
Wind Velocity Operational	The wind speed where the antenna deflection is equal to or less than 0.1 degrees. In the case of ValuLine antennas, it is defined as a maximum deflection of $0.3 \times$ the 3 dB beam width of the antenna.
Wind Velocity Survival Rating	The maximum wind speed the antenna, including mounts and radomes, where applicable, will withstand without permanent deformation. Realignment may be required. This wind speed is applicable to antenna with the specified amount of radial ice.