



Search Results

- Evaluate
- FAQ's
 - Press Releases
 - OPTI-CORE Fi ..
 - Product Bulletins
 - PDF-Opti-Core Fi ..
 - Technical References
 - PDF-OM3 Multimod ..
- Design a Solution
- Best Practices
 - PDF-Cable Prepar ..
 - PDF-Instructions ..
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click to remove) Search Tips ☐ Within Results

Text Search: 'FOGPX12Y'

Your search criteria matched only one product, shown below

FOGPX12Y



- Allows installation using loose tube cable methods within buildings and outdoor environments for transitional aerial and duct applications, and in entrance facilities that require riser (OFCR) or plenum (OFCP) rated cable
- Eliminates the need for building entrance transition point
- Interlocking aluminum armor eliminates the need for inner duct or conduit to provide a smaller crush resistant pathway for design flexibility and a lower installed cost
- UV resistant cable sheathing meets the light absorption requirement defined by Telcordia GR-20, Issue 2 to withstand harsh outdoor environmental demands
- Dry water-blocking technology allows rapid cable preparation and termination for lower termination costs and time (no messy gel required)
- Available in 6 and 12-fiber counts in "central loose tube" design, and in 24, 36, 48, 72, 96 and 144-fiber counts in a "stranded loose tube" design
- Singlemode (OS1/OS2) and multimode (OM1, OM2, and 10Gig™ OM3 laser optimized) fiber available

- Sheath markings provide positive identification, quality traceability, and length verification
- 250?m buffer coating protects fibers during handling and allows for ease of stripping
- *Opti-Core® 10Gig™* Cable is designed to support network transmission speeds up to 10 Gb/s for link lengths up to 300 meters with an 850nm source per IEEE 802.3ae 10 GbE Standard; backward compatible for use with all 50/125?m system requirements

These products are available for sale in the Americas regions only. Contact Customer Service for minimum order quantities, availability, and additional product configurations. Options include fiber counts, jacket colors, hybrid constructions (multiple fiber types within a single cable), flame ratings, subunit counts, premium optical performance grades and ribbonized constructions.

Part Number	FOGPX12Y
RoHS Compliancy Status	Compliant
Part Description	12-fiber 10Gig™ 50/125?m (OM3) multimode plenum rated indoor/outdoor interlocking armored central cable.
Product Type	Indoor/Outdoor Interlocking Armored Cable
Color	Aqua
Fiber Compatibility	10GbE 50/125?m
Fiber Type	Multimode
Fiber Count	12
Flammability Rating	Plenum (OFCP)
Min. Order UOM	FT
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.