




Part Number: 120098-0153

PROFIBUS* 90° D-Sub to 90° D-Sub Connector with Programming Port, 5.0m Cable Length



Status:	OBsolete
Replacement:	Contact Molex
Series:	120098
Category:	Industrial Cordsets
Overview:	Brad® PROFIBUS Solutions
Old Part Number:	@MP3S62PP4M050

Series image - Reference only

Product Environmental Compliance

[EU RoHS](#): Compliance Status Not Reviewed

[China RoHS](#):

[REACH SVHC](#): Not Reviewed

[Low-Halogen Status](#): Not Reviewed

Part Detail

General

Status	Obsolete
Category	Industrial Cordsets
Series	120098
Comments	With Programming Port
Connector End A	D-Sub (9-pin)
Connector End B	D-Sub (9-pin)
IP Rating	IP40
NEMA Rating	NEMA 4
Overview	Brad® PROFIBUS Solutions
Product Name	Micro-Change® (M12), Profibus*
Type	Double Ended
UPC	78678805756

Physical

Cable Diameter	8.00mm (.315")
Cable Length	5.0m
Color - Cable Jacket	Purple
Coupling Style	Threaded
Gender	Male-Female
Keyway	None
LED Indicator	No
Material - Cable Jacket	PUR
Material - Connector Body	PUR
Material - Contact	N/A
Material - Coupling Nut	Gray Anodized Aluminum
Material - Plating Mating	N/A
Net Weight	453.540/kg
Orientation	90° Angle
Poles	9
Temperature Range - Operating	-20°C to +80°C
Wire Size AWG	22
Wire/Cable Type	N/A

Electrical

(Please review the Product Specification for specific details.)

Current - Maximum per Contact	4A
Voltage - Maximum	250V AC/DC

Material Info

Old Part Number	@MP3S62PP4M050
-----------------	----------------

Reference - Drawing Numbers

Sales Drawing

SD-120098-026

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)