

GLASS PASSIVATED BRIDGE RECTIFIERS



REVERSE VOLTAGE - **50 to 1000** Volts
FORWARD CURRENT - **25** Amperes

FEATURES

- Rating to 1000V PRV
- High efficiency
- Glass passivated chip junction
- Electrically isolated metal case for maximum heat dissipation
- UL recognized file # E95060

MECHANICAL DATA

- Case : Mounted in the bridge encapsulation
- Mounting : Hole for # 10 screw
- Polarity : As marked on case
- Weight : 0.85 ounces , 24.0 grams (terminal)
: 0.74 ounces , 21.0 grams (wire)

KBPC-GW (Wire)

KBPC-G (Terminal)


KBPC-G/KBPC-GW		
DIM.	MIN.	MAX.
A	31.80	-
B	7.90	8.40
C	28.30	28.80
D	17.60	18.60
E	0.97	1.07
F	10.90	11.90
G	17.60	18.60
H	13.80	14.80
I	16.10	17.10
J	16.10	17.10
K	18.80	21.30
L	0.76	0.86
M	6.30	6.50
N	HOLE FOR NO. 10 SCREW	
	5.08	5.59

All Dimensions in millimeter

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.

CHARACTERISTICS	SYMBOL	KBPC25 005G/W	KBPC25 01G/W	KBPC25 02G/W	KBPC25 04G/W	KBPC25 06G/W	KBPC25 08G/W	KBPC25 10G/W	UNIT
Maximum Recurrent Peak Reverse Voltage	V_{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS Voltage	V_{RMS}	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage	V_{DC}	50	100	200	400	600	800	1000	V
Maximum Average Forward Rectified Current @ $T_C = T_a$	$I_{(AV)}$	25.0							A
Peak Forward Surge Current 8.3ms single half sine-wave super imposed on rated load	I_{FSM}	350							A
Maximum forward Voltage at 12.5A DC	V_F	1.1							V
Maximum DC Reverse Current at Rated DC Blocking Voltage @ $T_J = 25^\circ\text{C}$ @ $T_J = 125^\circ\text{C}$	I_R	5.0 500							μA
I^2t Rating for fusing ($t < 8.3\text{ms}$), (Note 1)	I^2t	508							A^2S
Typical Junction Capacitance per element (Note 2)	C_J	300							pF
Typical Thermal Resistance (Note 3)	$R_{\theta JC}$	3.0							$^\circ\text{C/W}$
Operating Temperature Range	T_J	-55 to +150							$^\circ\text{C}$
Storage Temperature Range	T_{STG}	-55 to +150							$^\circ\text{C}$

NOTES : 1. Measured at non-repetitive, for greater than 1ms and less than 8.3ms
2. Measured at 1.0MHz and applied reverse voltage of 4.0V DC.
3. Device mounted on 300mm x 300mm x 1.6mm Cu Plate Heatsink.

REV. 4, Sep-2010, KBD102

FIG.1 - FORWARD CURRENT DERATING CURVE




FIG.2 - MAXIMUM NON-REPETITIVE SURGE CURRENT




FIG.3 - TYPICAL JUNCTION CAPACITANCE




FIG.4 - TYPICAL FORWARD CHARACTERISTICS





FIG.5 - TYPICAL REVERSE CHARACTERISTICS



Important Notice and Disclaimer

LSC reserves the right to make changes to this document and its products and specifications at any time without notice. Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.

LSC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does LSC assume any liability for application assistance or customer product design. LSC does not warrant or accept any liability with products which are purchased or used for any unintended or unauthorized application.

No license is granted by implication or otherwise under any intellectual property rights of LSC.

LSC products are not authorized for use as critical components in life support devices or systems without express written approval of LSC.