


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	E1	REDRAWN PER ECO-17-007400	13DEC2017	RS	DR

AMP WIRE RANGE	 Listed FILE E13288	 LR7189 Certified
16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED



- 1 BODY MATERIAL THK 0.787 ± 0.051 [$.031 \pm .002$]
 2 FOR $\phi 2.921$ [$\phi .115$] TO $\phi 4.318$ [$\phi .170$] WIRE INSULATION.


3 STAMP AMP 16-14* APPROX AS SHOWN.

4 APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE

5 MATERIAL:
 BODY & SLEEVE: COPPER PER ASTM B-152
 INSULATION: NYLON

6 FINISH:
 BODY & SLEEVE: TIN PLATE PER ASTM B 545
 INSULATION: COLOR-BLUE.

1000	LOOSE PIECE	321283
QTY.	PACKAGE TYPE	PART NUMBER

DIMENSIONS: mm [INCHES]		DWN RAVI S	13DEC2017	MATERIAL 5		FINISH 6		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± -		CHK ROHDE DANIEL F	13DEC2017	TE TE Connectivity				
		APVD ROHDE DANIEL F	13DEC2017					
		PRODUCT SPEC UL 486 A-B		NAME WIRE TERMINAL, P.I.D.G, RECTANGULAR TONGUE, WIRE SIZE: 16-14 AWG				
		APPLICATION SPEC 114-2157						
		WEIGHT —		SIZE A4	CAGE CODE 00779	DRAWING NO C-321283	RESTRICTED TO —	
		CUSTOMER DRAWING				SCALE 1:1	SHEET 1 OF 1	REV E1

