


- HOUSING MATERIAL: LIQUID CRYSTAL POLYMER
COLOR: NATURAL.
- CONTACT MATERIAL: PHOSPHOR BRONZE
- CONTACT FINISH:
UNDERPLATE (ENTIRE CONTACT):
0.00127 MIN NICKEL.
ON MATING SURFACES:
CONFORMS TO ALL TESTING SPECIFIED FOR TELCORDIA
UNCONTROLLED ENVIRONMENT.
ON LEADS
0.0006 MIN TIN-LEAD OVER UNDERPLATE.
LUBRICATION (ENTIRE CONTACT):
SURFACE CONDITIONER PER AMP SPEC 112-1002 AFTER PLATING.
- PART MARKING LOCATED APPROXIMATELY AS SHOWN.
- DIMENSION APPLIES WHEN SEATED ON PRINTED CIRCUIT BOARD.



ROW	E	N	N	N	N	N	N
	D	J	J	J	J	J	J
	C	J	J	J	J	J	J
	B	J	J	J	J	J	J
	A	T	T	T	T	T	T
1 2 3 4 5 6							
SIGNAL							
POSITION							

CODE LETTER	MATING POST LENGTH ±0.10	LEAD LENGTH (REF)
J	6.5	4.25
N	7.25	4.25
T	8.0	4.25

30	223014-1
NO. OF SIGNAL POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DATE: 30/07/98
BY: R. BUCHHEISTER
FOR: R. BACCHITTE
REV: 47/07/98

PRODUCT SPEC: 30/07/98





APPLICATION SPEC: 30/07/98

SIZE: A1
CASE CODE: 00779
DRAWING NO: C-223014

CUSTOMER DRAWING

SCALE: 4:1
SHEET: 1 OF 2

REV: H



DETAIL Z
SCALE 20:1

RECOMMENDED CIRCUIT PATTERN
(COMPONENT SIDE)

[illegible]