

Connector - CIOC 4-1-LIV - 1701375

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Header, Nominal current: 5 A, Number of positions: 4, Pitch: 2.54 mm, Color: black, Contact surface: Gold, Assembly: Soldering

Product Features

- ✓ Gold-plated contact system
- ✓ A plug-in tap at any point in the bus and power cable can be achieved using two CIOC 4-18-LI plugs
- ✓ The CIOC 4-18-LI plug can be combined with -LIH or -LIV base strips for a horizontal or vertical PCB connection
- ✓ The CIOC plug-in plug range is complemented by a 4-pos. link plug with 2.54 mm pitch



Key commercial data

Packing unit	1 pc
Minimum order quantity	100 pc
Weight per Piece (excluding packing)	4.94 GRM
Custom tariff number	85366990
Country of origin	Japan

Technical data

Dimensions

Pitch	2.54 mm
Dimension a	7.5 mm
Pin spacing	2.54 mm

General

Range of articles	CIOC-LINK
Rated voltage (III/3)	160 V
Connection in acc. with standard	EN-VDE
Nominal current I_N	5 A
Maximum load current	5 A

Connector - CIOC 4-1-LIV - 1701375

Technical data

General

Insulating material	PBT
Inflammability class according to UL 94	V0
Color	black
Number of positions	4

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002637
ETIM 5.0	EC002637


UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

Drawings

Connector - CIOC 4-1-LIV - 1701375

Drilling diagram



Dimensioned drawing

