






THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
D1		REVISED PER ECR-18-005392	26NOV2018	BDA	SG



- 1. PINS TO COMPLY WITH AMP SOLDERABILITY SPEC. 109-11-3.
- 2. 0.00381 MIN MATTE TIN PLATE OVER 0.00127 MIN NICKEL.
- 3. MATES WITH PART P/N 1586590-1.
- 4. 0.00076 MIN GOLD PLATE IN THE LOCALIZED GOLD PLATE AREA 0.00381 MIN MATTE TIN IN THE LOCALIZED TIN PLATE AREA, BOTH OVER 0.00127 MIN NICKEL.



RECOMMENDED HOLE PATTERN FOR 1.57 THICK BOARD

OBSOLETE	BRASS	4	NYLON, UL94V-0	WHITE	1586599-2
	BRASS	2	NYLON, UL94V-0	WHITE	1586599-1
	MATERIAL	FINISH	MATERIAL	COLOR	PART NO.
	PIN		HOUSING		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 08APR2005															
DIMENSIONS: mm		CHK C. JONES 08APR2005															
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C. JONES 08APR2005	NAME HDR ASMBLY, 10 CIR, DBL ROW VERTICAL, SPEC KEYING, MINI-UNIVERSAL MATE-N-LOK(TM)														
<table border="1"> <tr><td>0 PLC</td><td>±</td></tr> <tr><td>1 PLC</td><td>±</td></tr> <tr><td>2 PLC</td><td>± 0.13</td></tr> <tr><td>3 PLC</td><td>±</td></tr> <tr><td>4 PLC</td><td>±</td></tr> <tr><td>ANGLES</td><td>±</td></tr> </table>		0 PLC	±	1 PLC	±	2 PLC	± 0.13	3 PLC	±	4 PLC	±	ANGLES	±	PRODUCT SPEC	SIZE A2	CAGE CODE 00779	DRAWING NO. C=1586599
0 PLC	±																
1 PLC	±																
2 PLC	± 0.13																
3 PLC	±																
4 PLC	±																
ANGLES	±																
MATERIAL SEE TABLE	FINISH SEE TABLE	APPLICATION SPEC	WEIGHT 0.000000	SCALE NA	SHEET 1 of 1												
CUSTOMER DRAWING			RESTRICTED TO	REV D1													