










RECOMMENDED MODULE LAYOUT



TYPE "R"	3.3 VOLT.
TYPE "L"	2.5 VOLT.
TYPE "C"	1.8 VOLT.
CENTER KEY	DESCRIPTION

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY	
ltr	ecn no	dr	date	linear	.X ±0.38/.015 .XX ±0.25/.010 .XXX ±0.15/.005	projection	title
A				angles	0° ±2°	MM	DDR 184P .050" 1-ROW, V/T ASS'Y PLASTIC POST
				dr	MAGGIE WU 04/12/02	scale	product family
				enr	JEFF.HSIEH 04/12/02	1.5:1	DDR
				chr	JEFF.HSIEH 04/12/02		code
				appd	JENN TSAO 04/12/02		TWN
sheet index	revision sheet						size
							dwg no
							10002394
							sheet 2 of



DDR ASSEMBLY PART NUMBER
10002394 - □ □ □ □

RECOMMENDED CIRCUIT BOARD HOLE LAYOUT

STYLE

- 1 : FOR 3.3 VOLT.
- 2 : FOR 2.5 VOLT.
- 3 : FOR 1.8 VOLT.

RESERVED

0

TAIL LENGTH

CODE	DIM. "B"	TOLERANCE
1	2.29 .090	±0.25 ±.01
2	2.79 .110	±0.25 ±.01
3	2.67 .105	±0.25 ±.01
4	3.05 .120	±0.25 ±.01

PLATING

CODE	CONTACT	SOLDERTAIL	UNDERPLATE	CODE	CONTACT	SOLDERTAIL	UNDERPLATE
2	15μ"(0.38μm) MIN. GOLD	100μ"(2.54μm) MIN. TIN/LEAD	50μ" (1.27μm) MIN. NICKEL OVERALL	7LF	15μ"(0.38μm) MIN. GOLD	100μ"(2.54μm) MIN. 100% TIN	50μ" (1.27μm) MIN. NICKEL OVERALL
3	30μ"(0.76μm) MIN. GOLD			8LF	30μ"(0.76μm) MIN. GOLD		
4	1μ"MIN.GOLD FLASH			9LF	1μ"MIN.GOLD FLASH		

COLOR OF HOUSING AND EJECTOR

0 : BLACK HOUSING + IVORY EJECTOR

mat'l. code				tolerances unless otherwise specified				CUSTOMER COPY		 www.fciconnect.com		
ltr	ecn no	dr	date	linear	.X ±0.38/.015			projection		title		
B					.XX ±0.25/.010					DDR 184P .050" 1-ROW, V/T ASS'Y PLASTIC POST		
					.XXX ±0.15/.005							
				angles	0° ±2'			 MM 1.5:1	A4	product family	DDR	
				dr	MAGGIE WU	04/12/02	size			dwg no	code	TWN
				enrg	JEFF.HSIEH	04/12/02	10002394			sheet	3 of	
				chr	JEFF.HSIEH	04/12/02						
				appd	JENN TSAO	04/12/02						
sheet index	revision sheet									cage code	526	