


LOC		DIST		REV		REVISIONS		DATE		APPD	
G	14	P	F	ZONE	LTR	DESCRIPTION					
				A		REVISED PER 0720-0230-93		2/28/94			

METRIC
DIMENSIONS LISTED IN mm [INCHES]

AMP WIRE RANGE		UL E13288 Listed
22-16 AWG STRANDED		22-16 AWG STRANDED
LR7189 Certified		MILITARY P/N AND CLASS
NOT CERTIFIED		NOT APPLICABLE

△ STAMP AMP 22-18* APPROX AS SHOWN

22-16 TERMINALS ARE STAMPED 22-18 IN
ACCORDANCE WITH MILITARY SPECIFICATION
MIL-T-7928, COMMERCIAL WIRE RANGE IS 22-16



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
170°C MAX

VOLTAGE RATING:
NOT APPLICABLE

WIRE CROSS SECTIONAL AREA RANGE:
0.26-1.65mm² [509-3,260] CIR MILS
STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
WITHOUT NOTICE. FOR THE LATEST REVISION,
SEE THE CONTROLLING DOCUMENT.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm - FINISHES - TOLERANCES ON: 2 PLG DEC ± . 3 PLG DEC ± . ANGLES ± .	DR 2-23-93 TA BRINKMAN CHK 2-23-93 DA PATTERSON APPD 2-23-93 DE MILLER APPD 2-23-93 JL NECKLEY PRODUCT SPEC APPLICATION SPEC FINISH TIN PLATE 0.00254 [1.000100] MIN THK PER MIL-T-10727
--	--

DR 2-23-93 TA BRINKMAN CHK 2-23-93 DA PATTERSON APPD 2-23-93 DE MILLER APPD 2-23-93 JL NECKLEY PRODUCT SPEC APPLICATION SPEC FINISH TIN PLATE 0.00254 [1.000100] MIN THK PER MIL-T-10727	WEIGHT -
--	----------

AMP AMP Incorporated Harrisburg, PA 17105-3508	
TERMINAL, SLOTTED RING TONGUE, BUDGET	
SIZE	CAGE CODE
00779	00779
SCALE	DRAWING NO
8:1	323837
SHEET	1 OF 1

323837
PART NO