

RF174-07SP1-01BJ1-0300



RF174-01RP1-02RP1-0200

50 Ω RG 174 CABLE ASSEMBLIES

SPECIFICATIONS

For complete specifications see
www.samtec.com?RF174

RF Connector:

Outer Contact Material:

Ni plated Brass (BNC)
 Au plated Brass (SMB & SMA)
 Au plated BeCu (MCX & MMCX)

Center Contact Material:

Au plated Brass (BNC-P, MCX-P,
 MMCX-P & SMA-P)

Insulator Material:

PTFE
 (SMB-P & SMA-J)

Operating Temperature:

-50 °C to +90 °C

Impedance:

50 Ω

Frequency Range:

0-6 GHz

(Cable & connector dependent)

RoHS Compliant:

Yes

RG 174 Cable:

Impedance:

50 Ω

Capacitance:

101.024 pF/meter

Max Attenuation

(cable only):

1.4 dB @ 1 GHz for 1 meter

Conductor Size:

26 AWG, (0.48 mm) .019" dia.

Conductor Material:

Copper

Insulator Material:

KLPE

Shield Material:

Tin Copper

Jacket Material:

PVC

Jacket Diameter:

(2.70 mm) .106"

Jacket Color:

Black

Bend Radius:

25.4 mm

RoHS Compliant:

Yes

Mates with:

MCX, MMCX, MMCXV,
 SMA, SMB5, BNC5,
 TNC



Solutionator
 DESIGN IN A MINUTE

- Create a full system:
cable assembly and board level mates,
50 Ω and 75 Ω solutions
- Free samples available
- Visit: rf.samtec.com

Standard performance 26 AWG
 RG 174 coax cable

2.3dK

Plugs and
 Jacks

Straight or
 Right-angle

Single or
 Double Ended

CABLE TYPE


END 1
 CONNECTOR

END 2
 CONNECTOR



RF174
 = RG 174 Cable

Specify END OPTIONS from chart

-01SP1-01RP1 SHOWN



END OPTIONS	
-01SP1 = SMA Straight Plug (30 μ " (0.76 μ m) Gold on Center Contact, Gold Flash on Shell)	
-01RP1 = SMA Right-angle Plug (30 μ " (0.76 μ m) Gold on Center Contact, Gold Flash on Shell)	
-07SP1 = SMB Straight Plug (30 μ " (0.76 μ m) Gold on Center Contact, Gold Flash on Shell)	
-07RP1 = SMB Right-angle Plug (30 μ " (0.76 μ m) Gold on Center Contact, Gold Flash on Shell)	
-02SJ1 = MCX Straight Jack (30 μ " (0.76 μ m) Gold on Center Contact, Gold Flash on Shell)	


END OPTIONS	
-02RP1 = MCX Right-angle Plug (30 μ " (0.76 μ m) Gold on Center Contact, Gold Flash on Shell)	
-02SP1 = MCX Straight Plug (30 μ " (0.76 μ m) Gold on Center Contact, Gold Flash on Shell)	
-03SP1 = MMCX Straight Plug (30 μ " (0.76 μ m) Gold on Center Contact, Gold Flash on Shell)	
-03RP1 = MMCX Right-angle Plug (30 μ " (0.76 μ m) Gold on Center Contact, Gold Flash on Shell)	
-V3SP1 = MMCXV Straight Plug, High Vibration (30 μ " (0.76 μ m) Gold on Center Contact, Nickel on Shell)	
-V3RP1 = MMCXV Right-angle Plug, High Vibration (30 μ " (0.76 μ m) Gold on Center Contact, Nickel on Shell)	
-V3SJ1 = MMCXV Straight Jack, High Vibration (30 μ " (0.76 μ m) Gold on Center Contact, Nickel on Shell)	

Due to technical progress, all designs, specifications and components are subject to change without notice.


WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications.

Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.



RF174-03RP1-07RP1-0200




RF174-02RP1-02SP1-0200



RF174-04BJ2-07SP1-0100

RF174 SERIES

Heavy Gold plated



Choice of RF connector styles

Standard heat shrink wraps

ALSO AVAILABLE (MOQ Required)

- Additional stripping and tinning options
- IP67 TNC option
- Additional plating options
- Additional end connector combinations
- Knurled nuts with BNC option

Variety of Bulkhead Jacks



Single or Double ended

OTHER SOLUTIONS

- Cable connector kits (see cable components catalog pages)

OVERALL LENGTH

—“XXXX”—

= Overall Length in millimeters —0100 (100 mm) minimum
(Cable lengths larger than 1000 millimeters are not supported by S.I. Test data)

END OPTIONS		END OPTIONS		END OPTIONS																								
-04SP3 = BNC Straight Plug (10 μ" (0.25 μm) Gold on Center Contact, Nickel on Shell)		-01PN1 = SMA 4-Hole Panel Mount Jack (30 μ" (0.76 μm) Gold on Center Contact, Gold Flash on Shell)		-SING = Single Ended (End 2 Callout)																								
-05SP3 = TNC Straight Plug (10 μ" (0.25 μm) Gold on Center Contact, Nickel on Shell)		-04BJ2 = BNC Bulkhead Jack (30 μ" (0.76 μm) Gold on Center Contact, Nickel on Shell)		XXXXXX = Stripped & Tinned (End 2 Callout)																								
-07BJ1 = SMB Bulkhead Jack (30 μ" (0.76 μm) Gold on Center Contact, Gold flash on Shell)		-05BJ3 = TNC Bulkhead Jack (10 μ" (0.25 μm) Gold on Center Contact, Nickel on Shell)		STRIPPED & TINNED (Dimensions in mm) <table><tr><th>CALLOUT</th><th>A</th><th>B</th><th>C</th></tr><tr><td>-303030</td><td>3.0</td><td>3.0</td><td>3.0</td></tr><tr><td>-303040</td><td>3.0</td><td>3.0</td><td>4.0</td></tr><tr><td>-403030</td><td>4.0</td><td>3.0</td><td>3.0</td></tr><tr><td>-403040</td><td>4.0</td><td>3.0</td><td>4.0</td></tr><tr><td>-404040</td><td>4.0</td><td>4.0</td><td>4.0</td></tr></table>	CALLOUT	A	B	C	-303030	3.0	3.0	3.0	-303040	3.0	3.0	4.0	-403030	4.0	3.0	3.0	-403040	4.0	3.0	4.0	-404040	4.0	4.0	4.0
CALLOUT	A	B	C																									
-303030	3.0	3.0	3.0																									
-303040	3.0	3.0	4.0																									
-403030	4.0	3.0	3.0																									
-403040	4.0	3.0	4.0																									
-404040	4.0	4.0	4.0																									
-01BJ1 = SMA Straight Bulkhead Jack -01SB1 = SMA Straight Bulkhead Jack, Sealed -01SR1 = SMA Straight Bulkhead Jack, Sealed, Reversed Polarity -01BR1 = SMA Straight Bulkhead Jack, Reversed Polarity (30 μ" (0.76 μm) Gold on Center Contact, Gold Flash on Shell)		-06BJ2 = N Type Bulkhead Jack (30 μ" (0.76 μm) Gold on Center Contact, Nickel on Shell)		Both center conductor and braid shield are stripped, only the center conductor is tinned.																								

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications.
Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.