





PRODUCT NUMBER

SEE SHEET 2



spec ref	*	dr	Peng-Bing Fu	2013/03/21	projection	MM	size	A3	scale	3:2
tolerance std	ASME Y14.5	eng	Peng-Bing Fu	2013/04/19	chr	-	ecn no	-		
surface	✓	appr	Pei-Ming Zheng	2013/04/19	product family	PwrBlade+	rel level	Released		
linear	0.X ±0.5	FCI	5HDP + 24S +1HP+7LP	dwg no	10106262-6706001	rev	A			
angular	0° ±2°	www.fci.com	cat. no.	Product - Customer Drw	sheet 1 of 3					





Copyright FCI.

PRODUCT NO.	ROWS	HIGH POWER					SIGNAL						HP	LOW POWER								E2																																																																																																																																																																																																																																																																																																																																											
		E1	P1	P2	P3	P4	P5	1	2	3	4	5	6	P6	P7	P8	P9	P10	P11	P12	P13																																																																																																																																																																																																																																																																																																																																												
10106262-6706001LF	DCBA																																																																																																																																																																																																																																																																																																																																																																


10106262-6706001LF

DCBA



CODE	DESCRIPTION
HI	STD HIGH POWER CONTACT (3.43)
HA	METAL HOLD DOWN
LK	STD LOW POWER CONTACT (3.43)
R	STD SIGNAL CONTACT, ROW A (3.43)
S	STD SIGNAL CONTACT, ROW B (3.43)
T	STD SIGNAL CONTACT, ROW C (3.43)
U	STD SIGNAL CONTACT, ROW D (3.43)

X	OMITED
---	--------

dr	Peng-Bing Fu	2013/03/21	projection 	MM 	size	A3	scale	3:2	
eng	Peng-Bing Fu	2013/04/19			ecn no	-			
chr	-	-			rel level			Released	
appr	Pei-Ming Zheng	2013/04/19	product family		PwrBlade+				
			title			5HDP + 24S + 1HP+7LP		dwg no	
www.fci.com			cat. no.			RA STB HEADER			10106262-6706001
								rev	
								A	
www.fci.com			cat. no.			Product - Customer Drw		sheet 2 of 3	

A

B

C

D

A

B

C

D

NOTES:

- 1) "FCI", PART NUMBER AND DATE CODE TO BE MARKED ON THIS SURFACE.
THE MARK CAN BE OMITTED IF THERE IS NOT ENOUGH SPACE ON THIS SURFACE.
- 2) MATERIALS:
-HOUSING - GLASS FILLED WITH HIGH TEMP THERMOPLASTIC, UL94V-0.
-SIGNAL CONTACT - COPPER ALLOY.
-POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY.
- 3) PLATING SPECIFICATION REFER TO FCI 10116351
- 4) DENOTES CONNECTOR KEEP OUT ZONE.
- 5) DATUM AND BASIC DIMENIONS WERE ESTABLISHED BY CUSTOMER.
- 6) ALL HOLE DIAMETERS ARE FINISHED HOLE SIZES.
- 7) 1.15±0.025MM DRILLED HOLE PLATED WITH 0.00762MM MIN Sn
OVER 0.0254-0.0762MM Cu PLATING TO ACHIEVE A 1.02±0.07MM HOLE.
- 8) PRODUCT SPECIFICATION REFER TO FCI GS-12-658.
APPLICATION SPECIFICATION REFER TO FCI GS-20-141.
PRODUCT PACKAGED IN TRAYS, REFER TO FCI GS-14-1502.



Copyright FCI.

dr	Peng-Bing Fu	2013/03/21	projection	MM	size	scale
eng	Peng-Bing Fu	2013/04/19			A3	3:2
chr	-	-			ecn no	-
appr	Pei-Ming Zheng	2013/04/19	product family	PwrBlade+	rel level	Released
www.fci.com		5HDP + 24S +1HP+7LP			dwg no	rev
		RA STB HEADER			10106262-6706001	A
cat. no.			Product - Customer Drw			sheet 3 of 3