

PRELIMINARY

Notice: Some parametric limits are subject to change

MITSUBISHI LASER DIODES

ML9xx45 SERIES

1550,1520nm InGaAsP FP LASER DIODES

TYPE NAME

ML920J45S , ML920K45S, ML920Y45S
ML925B45F , ML925C45F

DESCRIPTION

ML9XX45 series are InGaAsP laser diodes which provide a stable, single transverse mode oscillation with emission wavelength of 1550nm and standard continuous light output of 5mW.

ML9XX45 are hermetically sealed devices having the photo diode for optical output monitoring. This is suitable for such applications as FTTH (Fiber to the Home) systems.

FEATURES

- 1550 or 1520nm typical emission wavelength, FP-LDs
- Low threshold current, low operating current
- Wide temperature range operation (Tc = -40 to 85deg.C)
- ϕ 5.6mm TO-CA N package
- Flat window cap : ML920J45S, ML925B45F
- Ball lens cap : ML920K45S, ML925C45F, ML920Y45S

APPLICATION

- ~155Mbps FTTH system

ABSOLUTE MAXIMUM RATINGS

Symbol	Parameter	Conditions	Ratings	Unit
Po	Light output power	CW	6[4]	mW
VRL	Laser reverse voltage	-	2	V
VRD	PD reverse voltage	-	20	V
IFD	PD forward current	-	2	mA
Tc	Operation temperature	-	-40 to +85	deg.C
Tstg	Storage temperature	-	-40 to +100	deg.C

ELECTRICAL/OPTICAL CHARACTERISTICS(Tc=25°C)

Symbol	Parameter	Test Conditions		Min.	Typ.	Max.	Unit
Ith	Threshold current	CW		—	10	30	mA
Iop	Operation current	CW, Po=5mW[3mW]		—	30	50	mA
Vop	Operating voltage	CW, Po=5mW[3mW]		—	1.1	1.5	V
η	Slope efficiency	CW, Po=5mW[3mW]		0.15[0.1]	0.25[0.2]	—	mW/mA
λc	Center wavelength	CW, Po=5mW[3mW]	-01spec	1520	1550	1580	nm
			-02spec	1495	1520	1544	
Δλ	Spectral Width	CW, Po=5mW, [3mW]RMS(-20dB)		—	1.5	3	nm
θ ∥	Beam divergence angle(parallel)	CW, Po=5mW[3mW]		—	25[11]	—	deg.
θ ⊥	Beam divergence angle (perpendicular)	CW, Po=5mW[3mW]		—	30[11]	—	deg.
tr,tf	Rise and Fall time (10%-90%)	Ib=Ith,Po=5mW [3mW], 10-90%		—	0.3	0.7	nsec
I _m	Monitor Current (PD)	CW, Po=5mW[3mW], VRD=1V,		0.1	0.5	—	mA
I _d	Dark Current (PD)	VRD=10V		—	—	0.1	μA
C _t	Capacitance (PD)	VRD=10V, f=1MHz		—	10	20	pF
Pf(Note2)	Fiber Coupling characteristics at peak coupling<3>	CW, PL=5mW[3mW],SI10/125		0.2	0.5	—	mW
Df(Note2)		CW, PL=5mW[3mW], SI10/125	ML920K45S	5.0	5.8	6.2	mm
			ML925C45F	6.0	6.5	7.0	
			ML920Y45S				

Note : <1> [] applied to the lens cap type.

Note : <2> Pf, Df are applied to the ball lens type.

Note : <3> Df is a distance between reference plane of the base to the fiber.



MITSUBISHI
ELECTRIC


Aug. 2003

MITSUBISHI LASER DIODES

ML9xx45 SERIES

1550,1520nm InGaAsP FP LASER DIODES


OUTLINE DRAWING



ML9xx45 SERIES

1550,1520nm InGaAsP FP LASER DIODES

OUTLINE DRAWING



MITSUBISHI
ELECTRIC

Aug. 2003