

Current refinements (click ☐ to remove) Search Tips

☒ Region ☒ USA ☒ Product Family ☒ HSTT Heat Shrink Bulk Reels ☒ Text Search: 'HSTT38-T'

Your search criteria matched only one product, shown below.



Flexible Polyolefin DRYSHRINK™Heat Shrink Tubing

- General Purpose heat shrink tubing for dry locations
- Applications include insulating, protecting, harnessing and identifying wires.
- Material Type: Crosslinked Polyolefin
- Shrink Ratio: 2:1
- Temperature Range:-67°F to 275°F (55°C to 135°C)
- Flammability Rating: Flame retardant EXCEPT clear
- Voltage: 600 V
- UL Recognized, CSA Certified
- Mil Spec: AMSDTL-23053/5 Class 1 (Colors) Class 2 (Clear)

|                                         |                                  |
|-----------------------------------------|----------------------------------|
| Part Number:                            | HSTT38T                          |
| RoHS Compliancy Status:                 | Compliant                        |
| Part Description:                       | Thin Wall Polyolefin Heat Shrink |
| Material:                               | Polyolefin cross-linked          |
| Color:                                  | Black                            |
| CSA Certified:                          | Yes                              |
| Military Specification:                 | AMS-DTL-23053/5 Class 1          |
| UL Recognized:                          | E122770                          |
| Flammability Rating:                    | Flame Retardant                  |
| Length Per Reel (ft.):                  | 200                              |
| Length Per Reel (m):                    | 61.1                             |
| Max. Recovered I.D. (In.):              | .187                             |
| Max. Recovered I.D. (mm):               | 4.8                              |
| Min. Expanded I.D. (In.):               | .375                             |
| Min. Expanded I.D. (mm):                | 9.5                              |
| Nominal Diameter / Size:                | .375                             |
| Nominal Recovered Wall Thickness (In.): | .025                             |
| Nominal Recovered Wall Thickness (mm):  | .6                               |
| Shrink Ratio:                           | 2:1                              |
| Temperature Range:                      | -67°F to 275°F (55°C to 135°C)   |
| Min. Order UOM:                         | RL                               |
| Min. Order Qty.:                        | 1                                |
| BOM Qty. (# of Pkgs.)                   | <input type="text" value="0"/>   |

Add to My Catalog

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.