

KBPC8005 THRU KBPC810

SINGLE-PHASE SILICON BRIDGE


Reverse Voltage - 50 to 1000 Volts

Forward Current - 8.0 Amperes

Features

- Surge overload rating - 125 amperes peak
- Low forward voltage drop
- Mounting position: Any
- Small size; simple installation
- Silver plated copper leads

BR8



DIMENSIONS					
DIM	inches		mm		Note
	Min.	Max.	Min.	Max.	
A	0.730	0.770	18.542	19.558	
B	0.250	0.300	6.35	7.63	
C	0.480	0.520	12.19	13.21	
E	0.750	-	19.1	-	
F	0.380	0.042	0.97	1.07	ϕ
G	0.140	0.150	3.56	3.81	ϕ

Maximum Ratings and Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified.

For capacitive load, derate current by 20%.

	Symbols	KBPC 8005	KBPC 801	KBPC 802	KBPC 804	KBPC 806	KBPC 808	KBPC 810	Units
Maximum repetitive peak reverse voltage	V_{RRM}	50	100	200	400	600	800	1000	Volts
Maximum RMS bridge input voltage	V_{RMS}	35	70	140	280	420	560	700	Volts
Maximum average forward rectified output current at $T_A=100^{\circ}\text{C}$ * $T_A=50^{\circ}\text{C}$ **	$I_{(AV)}$	8.0 8.0							Amps
Peak forward surge current, 8.3mS single half sine-wave superimposed on rated load	I_{FSM}	125.0							Amps
Maximum forward Voltage drop per bridge element at 4.0A peak	V_F	1.1							Volts
Maximum DC reverse current at rated DC blocking voltage per element $T_J=25^{\circ}\text{C}$ $T_A=100^{\circ}\text{C}$	I_R	10.0 1.0							uA mA
Operating temperature range	T_J	-55 to +125							°C
Storage temperature range	T_{STG}	-55 to +150							°C

Notes:

* Unit mounted on metal chassis

** Unit mounted on P.C. board

RATINGS AND CHARACTERISTIC CURVES

Fig. 1 — MAXIMUM FORWARD SURGE CURRENT




Fig. 2 — DERATING CURVE FOR OUTPUT RECTIFIED CURRENT




Fig. 3 — TYPICAL FORWARD CHARACTERISTICS




Fig. 4 — TYPICAL REVERSE CHARACTERISTICS

