

REV	DESCRIPTION	DATE
A	RELEASE	05-10-94


By accepting this proprietary Huck drawing, recipient agrees not to reproduce or disclose any part thereof to any others without the written permission of Huck International, Inc.

NOTES:

- 1

ANVIL ASSEMBLY 124139 CONSISTS OF:
ANVIL HOLDER ASSEMBLY 123982,
ANVIL INSERT 123796.
- 2

ANVIL HOLDER ASSEMBLY 123982 CONSISTS OF:
ANVIL HOLDER 123981,
RETAINER 120738.



MATERIAL:	-	SPEC: -	TOLERANCES UNLESS OTHERWISE SPECIFIED		HUCK INTERNATIONAL, INC., I.S.D. 85 GRAND STREET, P.O. BOX 2270 KINGSTON, NEW YORK 12401			
HARDNESS:	-							
HEAT TREAT:	-	SPEC: -	.XX, .XXX	±	NOSE ASSEMBLY -06 BLIND RIVET			
SURF. TREAT:	-	SPEC: -	INT. COR. RADII					
SURFACE FINISH NOT TO EXCEED		Ra	BREAK EDGES		DET: T.L.	CK:	DATE:05-10-94	SCALE: 2/1
IDENTIFICATION PER SPEC 42-311: ★ CHEMICAL ETCH			ANGLES	±	FOC.	B 99-2737		
SURFACES TO BE ☉, //, ⊕, ⊥, & ▱ WITHIN			T.I.R.	FINAL ASSY: 352 STYLE	FAC.			