



CONNECTOR ASSEMBLY
EXEMPLARY LOADED




CONTACT DIMENSIONS



DO NOT SCALE
DIMENSIONS IN mm

METRIC

THIRD ANGLE
PROJECTION




CONTACT LAYOUT

		z	a	b	c	d	e	f
1			K	K	K	K	K	T
2			K	K	K	K	K	T
3			K	K	K	K	K	T
4			K	K	K	K	K	T
5			K	K	K	K	K	T
6			K	K	K	K	K	T
7			K	K	K	K	K	T
8			K	K	K	K	K	T
9			K	K	K	K	K	T
10			K	K	K	K	K	T
11			K	K	K	K	K	T
12			K	K	K	K	K	T
13			K	K	K	K	K	T
14			K	K	K	K	K	T
15			K	K	K	K	K	T
16			K	K	K	K	K	T
17			K	K	K	K	K	T
18			K	K	K	K	K	T
19			P	P	P	P	P	T
20			P	P	P	P	P	T
21			P	P	P	P	P	T
22			P	P	P	P	P	T

PART NO.	PLATING TABLE Δ			
	UNDER-COATING $\mu\text{m Ni MIN.}$	CONTACT AREA $\mu\text{m Au MIN.}$	ACTION-PIN AREA μm	- -
352360-1	1,3	0,8	0,5-2,5 Sn/Pb	-
-	-	-	-	-
-	-	-	-	-
-	-	-	-	-
-	-	-	-	-

NOTES:

- ① FOR FINISH TYPES SEE PLATING TABLE.
- ② MATERIAL CONTACT: PHOSPHORBRONZE.
MATERIAL HOUSING: GREY GLASSFILLED POLYESTER
MATERIAL POST ALIGNMENT STRIP: UNFILLED POLYESTER.
- ③ CONNECTOR MARKED WITH PART NUMBER AND DATE CODE.
- ④ PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID,
TOTAL 132 HOLES.
- ⑤ FOR ACTUAL PIN LOADING SEE "CONTACT LAYOUT".



RECOMMENDED PCB-HOLE LAY-OUT
COMPONENT SIDE SHOWN

P.C.B. HOLE DIM. ACTION PIN

DRILLED HOLE: 0,7±0,025mm
FIN. HOLE : 0,55 TO 0,65mm
Cu-thks : 0,025 TO 0,050mm
SnPb-thks : 0,004 TO 0,010mm

[illegible]