

# Fuseholders 5 x 20 mm



- ▶ 5 x 20mm fuses
- ▶ Finger and tool release
- ▶ PC2 protection category
- ▶ Solder & 2.8mm terminals
- ▶ Proud & low profile bezels
- ▶ Snap to panel and screw fixing



6.3A 250Vac (max fuse rating\*) T-55 to T+70 (ambient)  
Maximum dissipation wattage: 1.5W



6.3A UL 94V2 UL file E92075 CSA file LR44770



RoHS compliant

These products comply with safety category PC2.

\*Users should be aware of the de-rating factors published by specialist manufacturers of fuses.

These fuseholders are fitted with combination (solder / 2.8) mid-body terminals. It has not been possible to show both views here.




## ORDER FORMAT

T 0332 RA M520

TERMINAL CODE BODY & CAP CODE PANEL HOLE CODE OPTIONS

### ► TERMINAL

**T**



Solder

### ► BODY AND CAP

**0332**

Finger release




**0333**

Tool release



**B**



2.8 x 0.5

**0340**

Tool release




**0341**

Tool release




### ► PANEL HOLE

**RA**




### DIMENSIONS (mm)

**0332** (T terminal shown)




Panel thickness 0.8-4.5mm

**RD**




**0333** (T terminal shown)




Panel thickness 0.8-4.5mm

**0340** (T terminal shown)



Panel thickness 0.8-2.0mm

**0341** (T terminal shown)



Panel thickness 0.8-4.5mm

# Fuseholders 6.3 x 32mm (1 1/4" x 1 1/4")



16A 250Vac (max fuse rating\*) T-55 to T+70 (ambient)  
Maximum dissipation wattage: 2.5W



16A UL 94V2 UL file E92075 CSA file LR44770



RoHS compliant

These products comply with safety category PC2.

\*Users should be aware of the de-rating factors published by specialist manufacturers of fuses.

Fuseholders with in-line termination have combination (4.8/6.3) terminals. It has not been possible to show both views here. Units with right angle terminals have user specified end terminals and combination mid-body terminals.

- ▶ 6.3 x 32mm fuses
- ▶ Tool release
- ▶ PC2 protection category
- ▶ 4.8, 6.3 and solder terminals
- ▶ Low profile bezel
- ▶ Snap to panel and screw fixing



## ORDER FORMAT

T 0347 RA M873

TERMINAL CODE BODY & CAP CODE PANEL HOLE CODE OPTIONS




**M873**  
Cover for C & T terminals




**A0035 00**  
In-line 6.3 x 32 (1 1/4" x 1 1/4") fuseholder  
Call factory for rating details

### ► TERMINAL




6.3 x 0.8

**D**




6.3 x 0.8  
Right angle

**T**



4.8 x 0.8  
Solder

**U**



4.8 x 0.8  
Right angle solder

### ► BODY AND CAP

**0345** (C terminal shown)



© FI UL CSA

**0345** (D terminal shown)



© FI UL CSA

**0347** (T terminal shown)



© FI UL CSA


**0347** (U terminal shown)



© FI UL CSA


### ► PANEL HOLE

**RA**



Panel thickness  
0.8 - 2.0mm for snap-in  
0.8 - 4.5mm for nut fixing


**RD**




Panel thickness  
0.8 - 2.0mm for snap-in  
0.8 - 4.5mm for nut fixing

### DIMENSIONS (mm)


**0345** (C terminal shown)



**0345** (D terminal shown)



**0347** (C terminal shown)



**0347** (D terminal shown)

