



PANTHER



SPECIFICATION

Light output	1500/350 lumens
Running time	1.5hrs & 4hrs
Charge time	8hrs
Battery	12V 7A/h dry lead acid
Bulbs	50W xenon : 20W halogen
Product size (mm)	L260 x W150 x H180
Product weight (kg)	3.10
Boxed weight (kg)	4.20
Box size (mm)	L269 x W224 x H204
Part no.	NSPANTHER

PANTHER

The PANTHER is a very powerful, robust and rechargeable searchlight, with both distance spotlight and local area floodlight beams. It is used for professional applications by emergency services, utility companies, security organisations and both military and civilian rescue teams. It is also virtually unbreakable, incorporating a toughened lens and a shock resistant polyethylene plastic casing. It can be used in all weather conditions.

Optional Extras:

- Red, amber, green and blue colour filters
- Infra-red filter
- Vehicle charging/mounting brackets
- 30W, 75W and 100W xenon bulbs for different light output
- IP65 version available
- Protective carry case
- Vehicle chargers

Rapid vehicle charger



- 1 mile beam
- High / low light beams
- 50W xenon main bulb and 20W halogen secondary bulb
- Operates for 1.5 hours on high beam and 4 hours on low beam
- Mains charger included
- Battery charging indicator (red to green)
- Detachable shoulder strap
- Adjustable stand

Optional Protective carry case

