

C1608C0G2E101J080AA (TDK item description : C1608C0G2E101JT****)

Applications



Commercial Grade



Please refer to Part No. CGA3E3C0G2E101J080AA for automotive use.


Feature

Mid

Mid Voltage (100 to 630V)

Series

C1608 [EIA CC0603]



Size

Length(L)	1.60mm +/-0.10mm
Width(W)	0.80mm +/-0.10mm
Thickness(T)	0.80mm +/-0.10mm
Terminal Width(B)	0.20mm Min.
Terminal Spacing(G)	0.30mm Min.
Recommended Land Pattern(PA)	0.70 to 1.00mm (Flow Soldering) 0.60 to 0.80mm (Reflow Soldering)
Recommended Land Pattern(PB)	0.80 to 1.00mm (Flow Soldering) 0.60 to 0.80mm (Reflow Soldering)
Recommended Land Pattern(PC)	0.60 to 0.80mm (Flow Soldering) 0.60 to 0.80mm (Reflow Soldering)
Recommended Slit Pattern(SD)	

Electrical Characteristics






Capacitance	100pF +/-5%
Rated Voltage	250Vdc
Temperature Characteristic	C0G(0+/-30ppm/degC)
Q	1000 Min.
Insulation Resistance	10000MΩ Min.

Other

Soldering Method	Reflow, Flow
AEC Q200	No
Packing	Punched (Paper)Taping [180mm Reel]
Package Quantity	4000Pcs Min.

C1608C0G2E101J080AA

Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)



Ripple Temperature Rising
no data available