



Search Results

Evaluate

- Advertisements
- PDFQuickNet Cab
- FAQ's
- Technical References
 - PDFMaintaining ..
- White Papers
 - PDFBest Practic ..

Design a Solution

- Best Practices
 - PDFVisual Inspe ..
- Specification Sheets
 - PDFQuickNet MTP ..

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click to remove) [Search Tips](#) Within Results

Text Search: 'F612D5-5M6'

Your search criteria matched only one product, shown below

F612D5-5M6Y



- Pass all TIA/EIA-568-B.3 performance requirements
- FOCIS-5 compliant
- Insertion loss per mated pair: .50dB typical; .75dB max.
- Factory terminated, assembled and 100% tested for insertion loss
- Insertion loss data recorded for every multimode cable assembly
- Lifetime traceability of test data to a Q.C. number on each cable assembly
- 2-pin alignment assures consistent repeatable performance

* MTP is a registered trademark of US Conec Ltd.

Part Number	F612D5-5M6Y
RoHS Compliancy Status	Compliant
Note	F612D5-5M6Y replaces F612D5-5M6
Part Description	Female MTP* to female MTP* twelve strand fiber optic cable assembly (one female MTP* connector on each end on ribbon inerconnect cable) – 62.5/125 μ m.
Product Type	MTP* 12 Fiber Interconnect Cable Assemblies
Length (m)	6
Fiber Compatibility	62.5/125 μ m
Fiber Type	Multimode
Connector 1 Type	MTP* Connector
Connector 2 Type	MTP* Connector
End Configurations	MTP* to MTP*
Fiber Count	12
Flammability Rating	Plenum (OFNP)
Pricing Description	MTP* MTP* Interconnect Cable Assembly 6m 62.5 μ m
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.