


PRODUCT NUMBER	DIM"N"	DIM"P"
67000-0XXLF	SEE SHEET 2/2	

WHEN NEEDED, SUFFIX LETTER "LF"
INDICATES THE PRODUCT IS RoHS
COMPLIANT, SEE NOTE 2



NOTE:

- 1 - MATERIAL HOUSING: THERMOPLASTIC POLYESTER, 30% GLASS FILLED COLOR BLACK, FLAM RETARDANT PER UL-94-V0.
- 2 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS
 - a - LABELING:
 - MEETS PACKAGING SPECS AS PER GS-14-920
 - b - LEGAL STATEMENT: SEE GS-22-008

THE PRODUCT IS NOT INTENDED TO BE EXPOSED TO A MANUFACTURING SOLDER PROCESS.


CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection mm	product family DUFLEX			
ltr	ecn no	dr	date	tolerances unless otherwise specified			title BERG DUFLEX HOUSING SINGLE ROW			
K	F06-0226	DLE	06.07.07	angles	Linear	.0±.x .00±.0x	scale N/A			
E	F00499	PNZ	00.09.13	0'±x'		.000±.00x	FCJ			
F	F04-0347	DLE	04.12.10	dr	JM COMPAGNON	90.05.29	dwg no			
G	F05-0169	DLE	05.04.07	engr	JM.PHAMVAN	90.05.30	sheet 1 of 2			
H	F05-0236	DLE	05.08.24	chr	P.NIZZI	97.06.30	67000			
J	F05-0286	DLE	05.11.07	appd	JM.P	97.06.30	A3			
sheet index		revision	K	J			type			
		sheet	1	2			CUSTOMER Drawing			

NUMBER OF POS.	NUMBER OF POS.	DIM"N"	DIM"P"	DIM"S"
67000- 002(LF)	1 x 02	2.54	5.43	0.10
67000- 003(LF)	1 x 03	5.08	7.97	0.10
67000- 004(LF)	1 x 04	7.62	10.51	0.10
67000- 005(LF)	1 x 05	10.16	13.05	0.10
67000- 006(LF)	1 x 06	12.70	15.59	0.10
67000- 007(LF)	1 x 07	15.24	18.13	0.10
67000- 008(LF)	1 x 08	17.78	20.67	0.15
67000- 009(LF)	1 x 09	20.32	23.21	0.15
67000- 010(LF)	1 x 10	22.86	25.75	0.15
67000- 011(LF)	1 x 11	25.40	28.29	0.20
67000- 012(LF)	1 x 12	27.94	30.83	0.20
67000- 013(LF)	1 x 13	30.48	33.37	0.20
67000- 014(LF)	1 x 14	33.02	35.91	0.20
67000- 015(LF)	1 x 15	35.56	38.45	0.25
67000- 016(LF)	1 x 16	38.10	40.99	0.25
67000- 017(LF)	1 x 17	40.64	43.53	0.30
67000- 018(LF)	1 x 18	43.18	46.07	0.30
67000- 019(LF)	1 x 19	45.72	48.61	0.30
67000- 020(LF)	1 x 20	48.26	51.15	0.35

NUMBER OF POS.	NUMBER OF POS.	DIM"N"	DIM"P"	DIM"S"
67000- 021(LF)	1 x 21	50.80	53.69	0.35
67000- 022(LF)	1 x 22	53.34	56.23	0.35
67000- 023(LF)	1 x 23	55.88	58.77	0.45
67000- 024(LF)	1 x 24	58.42	61.31	0.45
67000- 025(LF)	1 x 25	60.96	63.85	0.45
67000- 026(LF)	1 x 26	63.50	66.39	0.50
67000- 027(LF)	1 x 27	66.04	68.93	0.50
67000- 028(LF)	1 x 28	68.58	71.47	0.50
67000- 029(LF)	1 x 29	71.12	74.01	0.50
67000- 030(LF)	1 x 29	73.66	76.55	0.50
67000- 031(LF)	1 x 31	76.20	79.09	0.55
67000- 032(LF)	1 x 32	78.74	81.63	0.55
67000- 033(LF)	1 x 33	81.28	84.17	0.55
67000- 034(LF)	1 x 34	83.82	86.71	0.55
67000- 035(LF)	1 x 35	86.36	89.25	0.55
67000- 036(LF)	1 x 36	88.90	91.79	0.55

CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code				surface ISO 1302 ☒		tolerance ISO 406 ISO 1101 ☒		projection 		product family DUFLEX			
ltr				ecn no		dr		date		tolerances unless otherwise specified		title BERG DUFLEX HOUSING SINGLE ROW	
C				F10123		JLC		91.02.25		angles		mm	
D				F70459		PNZ		97.06.30		linear		.00±.0x	
E				F00499		PNZ		00.09.13		0°±x°		.000±.00x	
F				F04-0347		DLE		04.12.10		dr JM COMPAGNON		90.05.29	
G				F05-0169		DLE		05.04.07		engr JM.PHAMVAN		90.05.30	
H				F05-0236		DLE		05.08.24		chr P.NIZZI		97.06.30	
J				F06-0226		DLE		06.07.07		appd JM.P		97.06.30	
sheet index		revision sheet											