

Circuit Breaker for Equipment thermal, Snap-in type, Fuseholder style, 1 pole



### Description

- Snap-in type from front side (0.8...2.0mm),
- Thermal circuit breaker,
- 1-pole
- Reset type
- Cycling trip-free release
- Quick connect terminals 6.3 x 0.8 mm

### Standards

- IEC 60934
- UL 1077
- CSA C22.2 235
- GB 17701

### Applications

- Designed for standard and medical applications
- Power supplies
- Uninterruptible power supply
- Power tools
- Industrial appliances
- HVAC
- Household appliances

### Weblinks

[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [Approvals](#), [CE declaration of conformity](#), [RoHS](#), [CHINA-RoHS](#), [REACH](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [Detailed request for product](#), [Product News](#)


### Technical Data

|                                    |                                                                 |
|------------------------------------|-----------------------------------------------------------------|
| Rated Voltage AC                   | 240 V, 50 / 60 Hz                                               |
| Rated Voltage DC                   | 48 / 32 V, see approvals                                        |
| Rated current                      | 3-16 A, see approbations                                        |
| Conditional short circuit capacity | IEC: Inc, PC1, AC 240 V: 2 kA                                   |
|                                    | UL / CSA: SC, AC 240 V DC 48 / 32 V: 2 kA, C1                   |
| Degree of protection front side    | IP 40                                                           |
| Endurance minimum                  | IEC: 200% I <sub>r</sub> , cos φ 0.6: min. 50 switching cycles  |
| Endurance typical                  | 3-8 A: 150% I <sub>r</sub> , cos φ 0.9: 2500 switching cycles   |
|                                    | 10-16 A: 150% I <sub>r</sub> , cos φ 0.9: 6000 switching cycles |
| Dielectric Strength                | 1500 VAC                                                        |
| Insulation resistance              | 500 VDC > 1000 MΩ                                               |

|                     |                        |
|---------------------|------------------------|
| Ambient temperature | 3 A: -5 °C to 60 °C    |
|                     | 4 A: -5 °C to 50 °C    |
|                     | 5-16 A: -5 °C to 60 °C |
| Weight              | 9 - 13 g               |

### Dimension

T9-611



Pannel thickness s = 0.8 - 2.0 mm



## Approvals

| Approval                                                                             |              | Rated current         | Rated voltage AC | Rated voltage DC |
|--------------------------------------------------------------------------------------|--------------|-----------------------|------------------|------------------|
|  US | UL 1077      | 3 - 12 A<br>14 - 16 A | 240 V<br>240 V   | 48 V<br>32 V     |
|  US | CSA 22.2 235 | 3 - 12 A<br>14 - 16 A | 240 V<br>240 V   | 48 V<br>32 V     |
|     | IEC 60934    | 3 - 12 A<br>14 - 16 A | 240 V<br>240 V   | 48 V<br>32 V     |
|     | GB 17701     | 3 - 12 A<br>14 - 16 A | 240 V<br>240 V   | 48 V<br>32 V     |

## Typical internal resistance

| Rated Current [A] | Internal Resistance [mΩ] |
|-------------------|--------------------------|
| 3                 | 65.0                     |
| 4                 | 21.6                     |
| 5                 | 23.6                     |
| 6                 | 16.3                     |
| 7                 | 15.3                     |
| 8                 | 12.9                     |
| 10                | 7.3                      |
| 12                | 7.0                      |
| 14                | 4.8                      |
| 15                | 4.3                      |
| 16                | 3.9                      |

## Time-Current-Curves



## Effect of ambient temperature

The units are calibrated for an ambient temperature of +23°C. To determine the rated current for a lower or higher ambient temperature, use a correction factor (typical value) from the table below:

| Ambient temperature [°C] | Correction factor |
|--------------------------|-------------------|
| -5                       | 0,85              |
| +10                      | 0,95              |
| +23                      | 1,00              |
| +40                      | 1,08              |
| +60                      | 1,21              |

Example: Rated current = 10 A; Environmental temperature = 60 °C; --> Correction factor = 1.21; Resulting current = 12.1 A --> Fount to next higher rated current: 13 A

## Accessory

| Part Number | Type      | Resources / Description                |
|-------------|-----------|----------------------------------------|
| 4404.0039   | TZZ31     | Protection cover for IP 65             |
| 4400.0420   | TZZ11     | Knurled nut nickel-plated              |
| 4400.0559   | TZZ11-414 | Knurled nut black                      |
| 4400.0425   | TZZ12     | Additional hexagonal nut nickel-plated |
| 4404.0072   | TZZ51     | Additional hexagonal nut PA 66         |

## Variants

| Mounting                         | Front printing                             | Rated current | Order Number |
|----------------------------------|--------------------------------------------|---------------|--------------|
| Snap-in mounting from front side | Rated current printed on front             | 3.0 A         | 4404.0018    |
| Snap-in mounting from front side | Rated current printed on front             | 4.0 A         | 4404.0001    |
| Snap-in mounting from front side | Rated current printed on front             | 5.0 A         | 4404.0007    |
| Snap-in mounting from front side | Rated current printed on front             | 6.0           | 4404.0002    |
| Snap-in mounting from front side | Rated current printed on front             | 7.0 A         | 4404.0009    |
| Snap-in mounting from front side | Rated current printed on front             | 8.0 A         | 4404.0003    |
| Snap-in mounting from front side | Rated current printed on front             | 10.0 A        | 4404.0004    |
| Snap-in mounting from front side | Rated current printed on front             | 12.0 A        | 4404.0005    |
| Snap-in mounting from front side | Rated current printed on front             | 14.0 A        | 4404.0008    |
| Snap-in mounting from front side | Rated current printed on front             | 15.0 A        | 4404.0010    |
| Snap-in mounting from front side | Rated current printed on front             | 16.0 A        | 4404.0006    |
| Snap-in mounting from front side | Rated current printed on front 90° shifted | 4.0 A         | 4404.0066    |
| Snap-in mounting from front side | Rated current printed on front 90° shifted | 5.0 A         | 4404.0067    |
| Snap-in mounting from front side | Rated current printed on front 90° shifted | 6.0           | 4404.0068    |
| Snap-in mounting from front side | Rated current printed on front 90° shifted | 8.0 A         | 4404.0069    |
| Snap-in mounting from front side | Rated current printed on front 90° shifted | 10.0 A        | 4404.0059    |
| Snap-in mounting from front side | Rated current printed on front 90° shifted | 12.0 A        | 4404.0061    |
| Snap-in mounting from front side | Rated current printed on front 90° shifted | 15.0 A        | 4404.0071    |
| Snap-in mounting from front side | Rated current printed on front 90° shifted | 16.0 A        | 4404.0062    |
| Snap-in mounting from front side | Rated current not printed on front         | 3.0 A         | 4404.0088    |
| Snap-in mounting from front side | Rated current not printed on front         | 4.0 A         | 4404.0089    |
| Snap-in mounting from front side | Rated current not printed on front         | 5.0 A         | 4404.0090    |
| Snap-in mounting from front side | Rated current not printed on front         | 6.0           | 4404.0091    |
| Snap-in mounting from front side | Rated current not printed on front         | 7.0 A         | 4404.0065    |
| Snap-in mounting from front side | Rated current not printed on front         | 8.0 A         | 4404.0092    |
| Snap-in mounting from front side | Rated current not printed on front         | 10.0 A        | 4404.0093    |
| Snap-in mounting from front side | Rated current not printed on front         | 12.0 A        | 4404.0063    |

| Mounting                         | Front printing                     | Rated current | Order Number              |
|----------------------------------|------------------------------------|---------------|---------------------------|
| Snap-in mounting from front side | Rated current not printed on front | 14.0 A        | <a href="#">4404.0094</a> |
| Snap-in mounting from front side | Rated current not printed on front | 15.0 A        | <a href="#">4404.0095</a> |
| Snap-in mounting from front side | Rated current not printed on front | 16.0 A        | <a href="#">4404.0087</a> |

Availability for all products can be searched real-time:<http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

**Packaging Unit** 100 Pcs