


# Amphenol® /Matrix® MS/Standard MIL-DTL-5015 Cylindrical Connectors

12-026-4



# Amphenol

This catalog covers the Amphenol® /Matrix® MIL-DTL-5015 Family of Connectors which incorporate rear release crimp contacts. MIL-C-5015 has been replaced by MIL-DTL-5015 for all Amphenol/Matrix rear release crimp type connectors. These connectors can be ordered through Amphenol, by military or equivalent proprietary part numbers.

Should more information be required concerning the connectors covered in this publication, or if special application needs arise, please contact:

Amphenol Corporation  
Amphenol Aerospace  
40-60 Delaware Avenue  
Sidney, New York 13838-1395  
Telephone 607-563-5011  
Fax: 607-563-5157  
[www.amphenol-aerospace.com](http://www.amphenol-aerospace.com)

The MIL-DTL-5015 crimp rear release type connector covered in this catalog, completes the MS/Standard family of connectors, so that now Amphenol can provide users with the broadest range of product available in the marketplace.

Catalog 12-020, Amphenol® MIL-DTL-5015 and MIL-5015 Type Standard Cylindrical Connectors, is also available upon request. This catalog covers the MIL-5015 cylindrical connectors with solder contacts. It also covers the MIL-5015 type connectors with proprietary crimp contacts in a very broad range of insert patterns - up to 280 different arrangements. Within these connector styles, MIL-C-5015 has been replaced as follows: Environmental classes F and R are updated to and produced in strict accordance to MIL-DTL-5015. Classes A, C and E are still produced, but are no longer listed on the qualified products listing (QPL).

Also, ask for these additional Amphenol Product Catalogs:

Amphenol Industrial Connector Brochure, SL-381, for an overview of the industrial family of connectors.  
Amphenol Brochure SL-100, which provides an overview of all products, military and industrial, offered through Amphenol Aerospace.

Visit our website [www.amphenol-aerospace.com](http://www.amphenol-aerospace.com) for this catalog and other catalogs of Amphenol products.

**TABLE OF CONTENTS**

**Amphenol® /Matrix® MS/Standard Cylindrical MIL-DTL-5015 Connectors with Crimp Rear Release Contacts**

Introduction, Table of Contents. . . . .1

General Description, Features and Benefits. . . . .2

Class Descriptions, Performance Specifications . . . .3

Shell Styles, Dimensional Data:

    Wall Mounting Receptacle . . . . .4

    Cable Connecting Receptacle . . . . .5

    Box Mounting Receptacle, . . . . .6

    Jam Nut Receptacle. . . . .7

    Straight Plug. . . . .8

    Straight Plug with Self-Locking Coupling Nut. . . .9

    Quick Disconnect Plugs,  
    with/without Lanyards. . . . .10

Insert Arrangement Chart. . . . .11, 12

Insert Alternate Positions . . . . .13

Insert Arrangement Patterns. . . . .14 - 24

Contact Information, Sealing Plugs,  
Crimping and Insertion/Removal Tools. . . . .25

Protection Caps . . . . .26-28

How to Order . . . . .29

Additional MS/Standard Connectors  
offered by Amphenol. . . . .30

Sales Office Listing

Amphenol Aerospace operates Quality Systems that are Certified to ISO-9001 and AS-9100 by third party Registrars.

# Amphenol<sup>®</sup>/Matrix<sup>®</sup> MS/Standard Cylindrical MIL-DTL-5015 Connectors with crimp rear release contacts



**MS3450**  
wall mounting receptacle

**MS3451**  
cable connecting receptacle

**MS3452**  
box mounting receptacle



**MS3454**  
jam nut receptacle



**MS3456**  
plug with threaded coupling



**MS3459**  
plug with self-locking coupling nut



**Proprietary quick disconnect plug with/without lanyard**

## Amphenol broadens their MS/Standard family of connectors with the MIL-DTL-5015 Crimp Rear Release Series.

This series provides an alternative to the older MIL-C-5015 solder type. It bridges the gap between an old connector standard and the environmental and high performance needs of current technologies.

### DESIGN CHARACTERISTICS

- Medium to heavy weight cylindrical
- MS345( ) series intermateable with existing MIL-DTL-5015 solder or crimp versions on existing equipment
- Captive coupling nut mechanism, utilizes retaining rings in combination with "L" washers to prevent inadvertent disassembly
- Multiple interlock systems ensure permanent insert retention
- Positive control of dielectric separation with guaranteed ease of contact insertion
- Positive contact retention provided by a closely toleranced damage-proof metal retention clip
- Completely sealed against environmental extremes with -
  - individual contact seals (conical risers on pin interface)
  - interfacial seals between contacts
  - peripheral gasket shell-to-shell seals
  - redundant rear wire seals and insert-to-shell seals

### CUSTOMER OPTIONS

- Seven mounting styles, in shell sizes 8 to 48\*
- Threaded coupling or self-locking plug (MS3459) with an internal ratcheting mechanism to prevent unmating due to vibration and shock, eliminating the need for safety wiring
- Proprietary quick disconnect plug, with or without lanyard available
- Classes include aluminum or stainless steel shells, or firewall capability
- MS and Proprietary versions available
- Some styles are supplied to McDonnell Douglas Specification BAN 7025, DC60 Series
- Accommodation of contact sizes 0 to 16
- Over 100 insert arrangement patterns available, accommodating from a minimum of 1 to a maximum of 85 circuits
- Alternate positioning available
- Thermocouple pin and socket contacts are available\*\*

NOTE: MIL-C-5015 is superseded to MIL-DTL-5015 for all Amphenol/Matrix rear release crimp type contacts.

\* Consult Amphenol, Sidney, NY for availability of shell sizes 44 and 48.

\*\* Consult Amphenol, Sidney, NY for information on thermocouple contacts.

# Amphenol<sup>®</sup>/Matrix<sup>®</sup> IS/Standard Cylindrical MIL-DTL-5015 Connectors

## class descriptions, performance specifications

### CLASS DESCRIPTIONS

| Military MIL-DTL-5015 |                                                                                                            |
|-----------------------|------------------------------------------------------------------------------------------------------------|
| Class L*              | aluminum shell, electroless nickel finish, fluid resistant insert                                          |
| Class W               | aluminum shell, cadmium olive drab finish, fluid resistant insert                                          |
| Class LS              | stainless steel shell, passivated, fluid resistant insert                                                  |
| Class KT**            | firewall, steel shell, cadmium olive drab finish, non-flammable hard dielectric and fluid resistant insert |
| Class KS              | firewall, stainless steel shell, passivated, non-flammable hard dielectric and fluid resistant insert      |

\* Class L inactivates older Class U (aluminum, electroless nickel)

\*\* Class KT (ferrous alloy, cadmium/olive drab) inactivates older Class K (ferrous alloy, electroless nickel)

| Amphenol/Matrix |                                                                                                            |
|-----------------|------------------------------------------------------------------------------------------------------------|
| Class A         | aluminum shell, black anodize finish, fluid resistant insert                                               |
| Class F         | aluminum shell, electroless nickel finish, fluid resistant insert                                          |
| Class W         | aluminum shell, cadmium/olive drab finish, fluid resistant insert                                          |
| Class FS        | stainless steel shell, passivated, fluid resistant insert                                                  |
| Class KT        | firewall, steel shell, cadmium olive drab finish, non-flammable hard dielectric and fluid resistant insert |
| Class KS        | firewall, stainless steel shell, passivated, non-flammable hard dielectric and fluid resistant insert      |

### PERFORMANCE SPECIFICATIONS

#### VOLTAGE RATING

| Altitude    | Inst. | A    | D    | E    | B    | C    |
|-------------|-------|------|------|------|------|------|
| Sea Level   | 1000  | 2000 | 2800 | 3500 | 4500 | 7000 |
| 50,000 ft.  | 400   | 600  | 675  | 750  | 825  | 975  |
| 70,000 ft.  | 260   | 360  | 400  | 440  | 480  | 560  |
| 110,000 ft. | 200   | 200  | 200  | 200  | 200  | 200  |

#### SHOCK

Wired, mated connectors are subjected to one shock in each of three mutually perpendicular axes with pulse of an approximate half sine wave of 50g magnitude for a duration of 11 milliseconds. All contacts wired in series circuit with 100 ±10 milliamperes of current flow.

#### OPERATING TEMPERATURE RANGE

Classes L, LS and KS have temperature range of –55°C (–75°F) to 200°C (392°F)

Classes W and KT have temperature range of –55°C (–75°F) to 175°C (347°F)

#### ENVIRONMENTAL SEAL

Wired, mated connectors with the specified accessory attached will meet the altitude immersion test specified in MIL-DTL-5015.

#### DURABILITY

Minimum of 100 mating cycles.


# MS/Standard

## MS3450

### wall mounting receptacle

Receptacle Shell, Flange Wall Mount,  
Threaded Coupling

Military No. MS3450  
Amphenol/Matrix No. 9440



To complete order number see how to order, page 29.

| Shell<br>Size* | A<br>±.031 | B     | C Dia.<br>+.010<br>-.005 |            | D Max.                      |                             | E<br>Dia.<br>Max. | F         | G<br>Min. | H<br>Thread<br>Class 2A | J<br>Thread<br>Class 2A | K    | L<br>Dia.<br>±.010 |
|----------------|------------|-------|--------------------------|------------|-----------------------------|-----------------------------|-------------------|-----------|-----------|-------------------------|-------------------------|------|--------------------|
|                |            |       | Class<br>A, F, R,<br>W   | Class<br>K | Size<br>16 & 12<br>Contacts | Size<br>8, 4, 0<br>Contacts |                   |           |           |                         |                         |      |                    |
| 8S             | .875       | .594  | .120                     | .150       | 2.031                       | —                           | .305              | .593/.562 | .290      | .5000-20 UNEF           | .5000-28 UNEF           | .083 | .562               |
| 10S            | 1.000      | .719  | .120                     | .150       | 2.031                       | —                           | .405              | .593/.562 | .290      | .6250-24 UNEF           | .6250-24 UNEF           | .083 | .688               |
| 10SL           | 1.000      | .719  | .120                     | .150       | 2.031                       | —                           | .405              | .593/.562 | .290      | .6250-24 UNEF           | .6250-24 UNEF           | .083 | .688               |
| 12             | 1.094      | .812  | .120                     | .150       | 2.125                       | —                           | .549              | .781/.750 | .290      | .7500-20 UNEF           | .7500-20 UNEF           | .083 | .812               |
| 12S            | 1.094      | .812  | .120                     | .150       | 2.031                       | —                           | .549              | .593/.562 | .290      | .7500-20 UNEF           | .7500-20 UNEF           | .083 | .812               |
| 14             | 1.188      | .906  | .120                     | .150       | 2.125                       | —                           | .665              | .781/.750 | .290      | .8750-20 UNEF           | .8750-20 UNEF           | .083 | .938               |
| 14S            | 1.188      | .906  | .120                     | .150       | 2.031                       | —                           | .665              | .593/.562 | .290      | .8750-20 UNEF           | .8750-20 UNEF           | .083 | .938               |
| 16             | 1.281      | .969  | .120                     | .150       | 2.125                       | 2.500                       | .790              | .781/.750 | .290      | 1.0000-20 UNEF          | 1.0000-20 UNEF          | .083 | 1.062              |
| 16S            | 1.281      | .969  | .120                     | .150       | 2.031                       | —                           | .790              | .593/.562 | .290      | 1.0000-20 UNEF          | 1.0000-20 UNEF          | .083 | 1.062              |
| 18             | 1.375      | 1.062 | .120                     | .177       | 2.125                       | 2.500                       | .869              | .781/.750 | .290      | 1.0625-18 UNEF          | 1.1250-18 UNEF          | .125 | 1.188              |
| 20             | 1.500      | 1.156 | .120                     | .177       | 2.125                       | 2.500                       | .994              | .781/.750 | .290      | 1.1875-18 UNEF          | 1.2500-18 UNEF          | .125 | 1.312              |
| 22             | 1.625      | 1.250 | .120                     | .177       | 2.125                       | 2.500                       | 1.119             | .781/.750 | .290      | 1.3125-18 UNEF          | 1.3750-18 UNEF          | .125 | 1.438              |
| 24             | 1.750      | 1.375 | .147                     | .177       | 2.125                       | 2.500                       | 1.244             | .843/.812 | .290      | 1.4375-18 UNEF          | 1.5000-18 UNEF          | .125 | 1.562              |
| 28             | 2.000      | 1.562 | .147                     | .177       | 2.125                       | 2.500                       | 1.465             | .843/.812 | .467      | 1.7500-18 UNS           | 1.7500-18 UNS           | .125 | 1.812              |
| 32             | 2.250      | 1.750 | .173                     | .209       | 2.125                       | 2.500                       | 1.715             | .906/.875 | .467      | 2.0000-18 UNS           | 2.0000-18 UNS           | .125 | 2.062              |
| 36             | 2.500      | 1.938 | .173                     | .209       | 2.125                       | 2.500                       | 1.930             | .906/.875 | .467      | 2.2500-16 UN            | 2.2500-16 UN            | .125 | 2.312              |
| 40             | 2.750      | 2.188 | .173                     | .209       | 2.125                       | 2.500                       | 2.145             | .906/.875 | .467      | 2.5000-16 UN            | 2.5000-16 UN            | .125 | 2.562              |

\* Consult Amphenol, Sidney, NY for availability of shell sizes 44 and 48.


# MS/Standard

## MS3451

### cable connecting receptacle

#### Receptacle Shell, Cable Connecting, Threaded Coupling

Military No. MS3451  
Amphenol/Matrix No. 9441



To complete order number see how to order, page 29.

| Shell Size | A           | B Dia.<br>±.031 | C         | D Max.                      |                             | E Dia.<br>Max. | F<br>±.015 | G<br>Min. | H<br>Thread<br>Class 2A | J<br>Thread<br>Class 2A |
|------------|-------------|-----------------|-----------|-----------------------------|-----------------------------|----------------|------------|-----------|-------------------------|-------------------------|
|            |             |                 |           | Size<br>16 & 12<br>Contacts | Size<br>8, 4, 0<br>Contacts |                |            |           |                         |                         |
| 8S         | .504/.496   | .729            | .577/.562 | 2.031                       | —                           | .305           | .083       | .290      | .5000-20 UNEF           | .5000-28 UNEF           |
| 10S        | .629/.621   | .854            | .577/.562 | 2.031                       | —                           | .405           | .083       | .290      | .6250-24 UNEF           | .6250-24 UNEF           |
| 10SL       | .629/.621   | .854            | .577/.562 | 2.031                       | —                           | .405           | .083       | .290      | .6250-24 UNEF           | .6250-24 UNEF           |
| 12         | .754/.746   | .974            | .765/.750 | 2.125                       | —                           | .549           | .083       | .290      | .7500-20 UNEF           | .7500-20 UNEF           |
| 12S        | .754/.746   | .974            | .577/.562 | 2.031                       | —                           | .549           | .083       | .290      | .7500-20 UNEF           | .7500-20 UNEF           |
| 14         | .879/.871   | 1.099           | .765/.750 | 2.125                       | —                           | .665           | .083       | .290      | .8750-20 UNEF           | .8750-20 UNEF           |
| 14S        | .879/.871   | 1.099           | .577/.562 | 2.031                       | —                           | .665           | .083       | .290      | .8750-20 UNEF           | .8750-20 UNEF           |
| 16         | 1.005/.996  | 1.224           | .765/.750 | 2.125                       | 2.500                       | .790           | .083       | .290      | 1.0000-20 UNEF          | 1.0000-20 UNEF          |
| 16S        | 1.005/.996  | 1.224           | .577/.562 | 2.031                       | —                           | .790           | .083       | .290      | 1.0000-20 UNEF          | 1.0000-20 UNEF          |
| 18         | 1.131/1.121 | 1.349           | .765/.750 | 2.125                       | 2.500                       | .869           | .125       | .290      | 1.0625-18 UNEF          | 1.1250-18 UNEF          |
| 20         | 1.256/1.246 | 1.474           | .765/.750 | 2.125                       | 2.500                       | .994           | .125       | .290      | 1.1875-18 UNEF          | 1.2500-18 UNEF          |
| 22         | 1.381/1.371 | 1.599           | .765/.750 | 2.125                       | 2.500                       | 1.119          | .125       | .290      | 1.3125-18 UNEF          | 1.3750-18 UNEF          |
| 24         | 1.506/1.496 | 1.715           | .827/.812 | 2.125                       | 2.500                       | 1.244          | .125       | .290      | 1.4375-18 UNEF          | 1.5000-18 UNEF          |
| 28         | 1.756/1.746 | 1.974           | .827/.812 | 2.125                       | 2.500                       | 1.465          | .125       | .467      | 1.7500-18 UNS           | 1.7500-18 UNS           |
| 32         | 2.007/1.996 | 2.224           | .890/.870 | 2.125                       | 2.500                       | 1.715          | .125       | .467      | 2.0000-18 UNS           | 2.0000-18 UNS           |
| 36         | 2.257/2.246 | 2.474           | .890/.870 | 2.125                       | 2.500                       | 1.930          | .125       | .467      | 2.2500-16 UN            | 2.2500-16 UN            |
| 40         | 2.511/2.456 | 2.724           | .890/.870 | 2.125                       | 2.500                       | 2.145          | .125       | .467      | 2.5000-16 UN            | 2.5000-16 UN            |

\* Consult Amphenol, Sidney, NY for availability of shell sizes 44 and 48.

# MS/Standard

## MS3452

### box mounting receptacle

#### Receptacle Shell, Flange Box Mount, Threaded Coupling

Military No. MS3452  
Amphenol/Matrix No. 9442



To complete order number see how to order, page 29.

| Shell<br>Size* | A<br>±.031 | B     | C<br>Dia. | D Max.                      |                             | E<br>Dia.<br>±.016 | F         | G<br>±.015 | J<br>Thread<br>Class 2A | L<br>Dia.<br>±.010 |
|----------------|------------|-------|-----------|-----------------------------|-----------------------------|--------------------|-----------|------------|-------------------------|--------------------|
|                |            |       |           | Size<br>16 & 12<br>Contacts | Size<br>8, 4, 0<br>Contacts |                    |           |            |                         |                    |
| 8S             | .875       | .594  | .130/.115 | 1.662                       | —                           | .500               | .578/.562 | .083       | .5000-28 UNEF           | .562               |
| 10S            | 1.000      | .719  | .130/.115 | 1.662                       | —                           | .625               | .578/.562 | .083       | .6250-24 UNEF           | .688               |
| 10SL           | 1.000      | .719  | .130/.115 | 1.662                       | —                           | .625               | .578/.562 | .083       | .6250-24 UNEF           | .688               |
| 12             | 1.094      | .812  | .130/.115 | 1.662                       | —                           | .750               | .765/.750 | .083       | .7500-20 UNEF           | .812               |
| 12S            | 1.094      | .812  | .130/.115 | 1.662                       | —                           | .750               | .578/.562 | .083       | .7500-20 UNEF           | .812               |
| 14             | 1.188      | .906  | .130/.115 | 1.662                       | —                           | .875               | .765/.750 | .083       | .8750-20 UNEF           | .938               |
| 14S            | 1.188      | .906  | .130/.115 | 1.662                       | —                           | .875               | .577/.562 | .083       | .8750-20 UNEF           | .938               |
| 16             | 1.281      | .969  | .130/.115 | 1.662                       | 1.937                       | 1.000              | .765/.750 | .083       | 1.0000-20 UNEF          | 1.062              |
| 16S            | 1.281      | .969  | .130/.115 | 1.662                       | —                           | 1.000              | .577/.562 | .083       | 1.0000-20 UNEF          | 1.062              |
| 18             | 1.375      | 1.062 | .130/.115 | 1.662                       | 1.937                       | 1.062              | .765/.750 | .125       | 1.1250-18 UNEF          | 1.188              |
| 20             | 1.500      | 1.156 | .130/.115 | 1.662                       | 1.937                       | 1.187              | .765/.750 | .125       | 1.2500-18 UNEF          | 1.312              |
| 22             | 1.625      | 1.250 | .130/.115 | 1.662                       | 1.937                       | 1.312              | .765/.750 | .125       | 1.3750-18 UNEF          | 1.438              |
| 24             | 1.750      | 1.375 | .157/.142 | 1.662                       | 1.937                       | 1.437              | .827/.812 | .125       | 1.5000-18 UNEF          | 1.562              |
| 28             | 2.000      | 1.562 | .157/.142 | 1.662                       | 1.937                       | 1.750              | .827/.812 | .125       | 1.7500-18 UNS           | 1.812              |
| 32             | 2.250      | 1.750 | .183/.168 | 1.662                       | 1.937                       | 2.000              | .988/.875 | .125       | 2.0000-18 UNS           | 2.062              |
| 36             | 2.500      | 1.938 | .183/.168 | 1.662                       | 1.937                       | 2.250              | .988/.875 | .125       | 2.2500-16 UN            | 2.312              |
| 40             | 2.750      | 2.188 | .183/.168 | 1.662                       | 1.937                       | 2.500              | .988/.875 | .125       | 2.5000-16 UN            | 2.562              |

\* Consult Amphenol, Sidney, NY for availability of shell sizes 44 and 48.

# MS/Standard

## MS3454

### jam nut receptacle

#### Receptacle Shell, Jam Nut Mount, Threaded Coupling

**Military No. MS3454**  
**Amphenol/Matrix No. 9444**



To complete order number see how to order, page 29.

| Shell<br>Size* | A<br>±.010 | B<br>±.005 | C<br>Dia.<br>±.005 | D Max.                      |                             | E<br>Dia.<br>Max. | F<br>±.005 | G<br>Min. | H<br>Thread<br>Class 2A | J<br>Thread<br>Class 2A | Panel Cutout<br>Dimensions |                          |
|----------------|------------|------------|--------------------|-----------------------------|-----------------------------|-------------------|------------|-----------|-------------------------|-------------------------|----------------------------|--------------------------|
|                |            |            |                    | Size<br>16 & 12<br>Contacts | Size<br>8, 4, 0<br>Contacts |                   |            |           |                         |                         | L<br>±.005                 | M Dia.<br>+.015<br>-.000 |
| 8S             | .687       | 1.187      | 1.272              | 2.031                       | —                           | .305              | .720       | .290      | .5000-20 UNEF           | .5000-28 UNEF           | .323                       | .505                     |
| 10S            | .812       | 1.312      | 1.397              | 2.031                       | —                           | .405              | .720       | .290      | .6250-24 UNEF           | .6250-24 UNEF           | .385                       | .630                     |
| 10SL           | .812       | 1.312      | 1.397              | 2.031                       | —                           | .405              | .720       | .290      | .6250-24 UNEF           | .6250-24 UNEF           | .385                       | .630                     |
| 12             | .937       | 1.437      | 1.522              | 2.125                       | —                           | .549              | .970       | .290      | .7500-20 UNEF           | .7500-20 UNEF           | .448                       | .755                     |
| 12S            | .937       | 1.437      | 1.522              | 2.031                       | —                           | .549              | .720       | .290      | .7500-20 UNEF           | .7500-20 UNEF           | .448                       | .755                     |
| 14             | 1.125      | 1.562      | 1.647              | 2.125                       | —                           | .665              | .970       | .290      | .8750-20 UNEF           | .8750-20 UNEF           | .510                       | .880                     |
| 14S            | 1.125      | 1.562      | 1.647              | 2.031                       | —                           | .665              | .720       | .290      | .8750-20 UNEF           | .8750-20 UNEF           | .510                       | .880                     |
| 16             | 1.250      | 1.687      | 1.772              | 2.125                       | 2.500                       | .790              | .970       | .290      | 1.0000-20 UNEF          | 1.0000-20 UNEF          | .573                       | 1.005                    |
| 16S            | 1.250      | 1.687      | 1.772              | 2.031                       | —                           | .790              | .720       | .290      | 1.0000-20 UNEF          | 1.0000-20 UNEF          | .573                       | 1.005                    |
| 18             | 1.375      | 1.812      | 1.897              | 2.125                       | 2.500                       | .869              | .970       | .290      | 1.0625-18 UNEF          | 1.1250-18 UNEF          | .635                       | 1.130                    |
| 20             | 1.500      | 1.937      | 2.022              | 2.125                       | 2.500                       | .994              | .970       | .290      | 1.1875-18 UNEF          | 1.2500-18 UNEF          | .698                       | 1.255                    |
| 22             | 1.625      | 2.156      | 2.241              | 2.125                       | 2.500                       | 1.119             | .970       | .290      | 1.3125-18 UNEF          | 1.3750-18 UNEF          | .760                       | 1.380                    |
| 24             | 1.750      | 2.281      | 2.366              | 2.125                       | 2.500                       | 1.244             | .970       | .290      | 1.4375-18 UNEF          | 1.5000-18 UNEF          | .823                       | 1.505                    |
| 28             | 2.000      | 2.531      | 2.616              | 2.125                       | 2.500                       | 1.465             | .970       | .467      | 1.7500-18 UNS           | 1.7500-18 UNS           | .948                       | 1.755                    |
| 32             | 2.375      | 2.781      | 2.866              | 2.125                       | 2.500                       | 1.715             | .970       | .467      | 2.0000-18 UNS           | 2.0000-18 UNS           | 1.073                      | 2.005                    |
| 36             | 2.625      | 3.031      | 3.116              | 2.125                       | 2.500                       | 1.930             | .970       | .467      | 2.2500-16 UN            | 2.2500-16 UN            | 1.198                      | 2.255                    |
| 40             | 2.875      | 3.281      | 3.366              | 2.125                       | 2.500                       | 2.145             | .970       | .467      | 2.5000-16 UN            | 2.5000-16 UN            | 1.323                      | 2.505                    |

\* Consult Amphenol, Sidney, NY for availability of shell sizes 44 and 48.


# MS/Standard

## MS3456

### straight plug

#### Plug Shell, Threaded Coupling

Military No. MS3456  
Amphenol/Matrix No. 9446



To complete order number see how to order, page 29.

| Shell Size* | A Dia. Max. | B Dia. ±.005 | C Max.                |                       | D Min. | E Dia. Max. | H Thread Class 2A | J Thread Class 2B |
|-------------|-------------|--------------|-----------------------|-----------------------|--------|-------------|-------------------|-------------------|
|             |             |              | Size 16 & 12 Contacts | Size 8, 4, 0 Contacts |        |             |                   |                   |
| 8S          | .844        | .360         | 2.031                 | —                     | .290   | .305        | .5000-20 UNF      | .5000-28 UNEF     |
| 10S         | .969        | .435         | 2.031                 | —                     | .290   | .405        | .6250-24 UNEF     | .6250-24 UNEF     |
| 10SL        | .969        | .441**       | 2.031                 | —                     | .290   | .405        | .6250-24 UNEF     | .6250-24 UNEF     |
| 12          | 1.062       | .550         | 2.125                 | —                     | .290   | .549        | .7500-20 UNEF     | .7500-20 UNEF     |
| 12S         | 1.062       | .550         | 2.031                 | —                     | .290   | .549        | .7500-20 UNEF     | .7500-20 UNEF     |
| 14          | 1.156       | .670         | 2.125                 | —                     | .290   | .665        | .8750-20 UNEF     | .8750-20 UNEF     |
| 14S         | 1.156       | .670         | 2.031                 | —                     | .290   | .665        | .8750-20 UNEF     | .8750-20 UNEF     |
| 16          | 1.250       | .800         | 2.125                 | 2.500                 | .290   | .790        | 1.0000-20 UNEF    | 1.0000-20 UNEF    |
| 16S         | 1.250       | .800         | 2.031                 | —                     | .290   | .790        | 1.0000-20 UNEF    | 1.0000-20 UNEF    |
| 18          | 1.344       | .925         | 2.125                 | 2.500                 | .290   | .869        | 1.0625-18 UNEF    | 1.1250-18 UNEF    |
| 20          | 1.469       | 1.045        | 2.125                 | 2.500                 | .290   | .994        | 1.1875-18 UNEF    | 1.2500-18 UNEF    |
| 22          | 1.594       | 1.170        | 2.125                 | 2.500                 | .290   | 1.119       | 1.3125-18 UNEF    | 1.3750-18 UNEF    |
| 24          | 1.719       | 1.295        | 2.125                 | 2.500                 | .290   | 1.244       | 1.4375-18 UNEF    | 1.5000-18 UNEF    |
| 28          | 1.969       | 1.515        | 2.125                 | 2.500                 | .467   | 1.465       | 1.7500-18 UNS     | 1.7500-18 UNS     |
| 32          | 2.219       | 1.765        | 2.125                 | 2.500                 | .467   | 1.715       | 2.0000-18 UNS     | 2.0000-18 UNS     |
| 36          | 2.469       | 1.975        | 2.125                 | 2.500                 | .467   | 1.930       | 2.2500-16 UN      | 2.2500-16 UN      |
| 40          | 2.719       | 2.225        | 2.125                 | 2.500                 | .467   | 2.145       | 2.5000-16 UN      | 2.5000-16 UN      |

\* Consult Amphenol, Sidney, NY for availability of shell sizes 44 and 48.

\*\* Tolerance on this dimension is +.000 —.006


# MS/Standard

## MS3459

### straight plug with self-locking coupling nut

Plug Shell, Self-Locking,  
Threaded Coupling

Military No. MS3459  
Amphenol/Matrix No. 9816



To complete order number see how to order, page 29.

| Shell Size* | A Dia. Max. | B Dia. $\pm .005$ | C Max.                |                       | D Min. | E Dia. Max. | H Thread Class 2A | J Thread Class 2B |
|-------------|-------------|-------------------|-----------------------|-----------------------|--------|-------------|-------------------|-------------------|
|             |             |                   | Size 16 & 12 Contacts | Size 8, 4, 0 Contacts |        |             |                   |                   |
| 8S          | .963        | .360              | 1.510                 | —                     | .290   | .305        | .5000-20 UNEF     | .5000-28 UNEF     |
| 10S         | 1.088       | .435              | 1.510                 | —                     | .290   | .405        | .6250-24 UNEF     | .6250-24 UNEF     |
| 10SL        | 1.088       | .441**            | 1.510                 | —                     | .290   | .405        | .6250-24 UNEF     | .6250-24 UNEF     |
| 12          | 1.213       | .550              | 1.780                 | —                     | .290   | .549        | .7500-20 UNEF     | .7500-20 UNEF     |
| 12S         | 1.213       | .550              | 1.510                 | —                     | .290   | .549        | .7500-20 UNEF     | .7500-20 UNEF     |
| 14          | 1.358       | .670              | 1.780                 | —                     | .290   | .665        | .8750-20 UNEF     | .8750-20 UNEF     |
| 14S         | 1.358       | .670              | 1.510                 | —                     | .290   | .665        | .8750-20 UNEF     | .8750-20 UNEF     |
| 16          | 1.463       | .800              | 1.780                 | 2.500                 | .290   | .790        | 1.0000-20 UNEF    | 1.0000-20 UNEF    |
| 16S         | 1.463       | .800              | 1.510                 | —                     | .290   | .790        | 1.0000-20 UNEF    | 1.0000-20 UNEF    |
| 18          | 1.588       | .925              | 1.850                 | 2.500                 | .290   | .869        | 1.0625-18 UNEF    | 1.1250-18 UNEF    |
| 20          | 1.713       | 1.045             | 1.850                 | 2.500                 | .290   | .994        | 1.1875-18 UNEF    | 1.2500-18 UNEF    |
| 22          | 1.788       | 1.170             | 1.850                 | 2.500                 | .290   | 1.119       | 1.3125-18 UNEF    | 1.3750-18 UNEF    |
| 24          | 1.963       | 1.295             | 1.850                 | 2.500                 | .290   | 1.244       | 1.4375-18 UNEF    | 1.5000-18 UNEF    |
| 28          | 2.213       | 1.515             | 1.850                 | 2.500                 | .467   | 1.465       | 1.7500-18 UNS     | 1.7500-18 UNS     |
| 32          | 2.463       | 1.765             | 1.850                 | 2.500                 | .467   | 1.715       | 2.0000-18 UNS     | 2.0000-18 UNS     |
| 36          | 2.713       | 1.975             | 1.850                 | 2.500                 | .467   | 1.930       | 2.2500-16 UN      | 2.2500-16 UN      |
| 40          | 2.963       | 2.225             | 1.850                 | 2.500                 | .467   | 2.145       | 2.5000-16 UN      | 2.5000-16 UN      |

\* Consult Amphenol, Sidney, NY for availability of shell sizes 44 and 48.

\*\* Tolerance on this dimension is  $+.000 - .006$

# MS/Standard

## 9817, 9818

### quick disconnect plug, with/without lanyard

#### Plug Shell, Quick Disconnect, Push-pull Coupling

Amphenol/Matrix No. 9817 with lanyard

Amphenol/Matrix No. 9818 without lanyard



9818 Connector

9817 Connector with Lanyard

To complete order number see how to order, page 29.

| Shell Size* | A Dia. Max. | B Dia. | C Max.                |                       | D Min. | E Dia. Max. | H Thread Class 2A | Amphenol/ Matrix Part Number for Adapter Ring |
|-------------|-------------|--------|-----------------------|-----------------------|--------|-------------|-------------------|-----------------------------------------------|
|             |             |        | Size 16 & 12 Contacts | Size 8, 4, 0 Contacts |        |             |                   |                                               |
| 8S          | 1.087       | .360   | 2.031                 | —                     | .290   | .305        | .5000-20 UNF      | 2500-008-0X08                                 |
| 10S         | 1.224       | .435   | 2.031                 | —                     | .290   | .405        | .6250-24 UNEF     | 2500-008-0X10                                 |
| 10SL        | 1.224       | .441   | 2.031                 | —                     | .290   | .405        | .6250-24 UNEF     | 2500-008-0X10                                 |
| 12          | 1.355       | .550   | 2.125                 | —                     | .290   | .549        | .7500-20 UNEF     | 2500-008-0X12                                 |
| 12S         | 1.355       | .550   | 2.031                 | —                     | .290   | .549        | .7500-20 UNEF     | 2500-008-0X13                                 |
| 14          | 1.482       | .670   | 2.125                 | —                     | .290   | .665        | .8750-20 UNEF     | 2500-008-0X14                                 |
| 14S         | 1.482       | .670   | 2.031                 | —                     | .290   | .665        | .8750-20 UNEF     | 2500-008-0X15                                 |
| 16          | 1.609       | .800   | 2.125                 | 2.500                 | .290   | .790        | 1.0000-20 UNEF    | 2500-008-0X16                                 |
| 16S         | 1.609       | .800   | 2.031                 | —                     | .290   | .790        | 1.0000-20 UNEF    | 2500-008-0X17                                 |
| 18          | 1.817       | .925   | 2.125                 | 2.500                 | .290   | .869        | 1.0625-18 UNEF    | 2500-008-0X18                                 |
| 20          | 1.942       | 1.045  | 2.125                 | 2.500                 | .290   | .994        | 1.1875-18 UNEF    | 2500-008-0X20                                 |
| 22          | 2.075       | 1.170  | 2.125                 | 2.500                 | .290   | 1.119       | 1.3125-18 UNEF    | 2500-008-0X22                                 |
| 24          | 2.203       | 1.295  | 2.125                 | 2.500                 | .290   | 1.244       | 1.4375-18 UNEF    | 2500-008-0X24                                 |
| 28          | 2.516       | 1.515  | 2.125                 | 2.500                 | .467   | 1.465       | 1.7500-18 UNS     | 2500-008-0X28                                 |
| 32          | 2.735       | 1.765  | 2.125                 | 2.500                 | .467   | 1.715       | 2.0000-18 UNS     | 2500-008-0X32                                 |
| 36          | 3.015       | 1.975  | 2.125                 | 2.500                 | .467   | 1.930       | 2.2500-16 UN      | 2500-008-0X36                                 |
| 40          | 3.306       | 2.225  | 2.125                 | 2.500                 | .467   | 2.145       | 2.5000-16 UN      | 2500-008-0X40                                 |

\* Consult Amphenol, Sidney, NY for availability of shell sizes 44 and 48.

#### Receptacle Adapter Ring

Required to mate the quick disconnect plug with receptacle.

Not furnished with the quick disconnect plug and must be ordered separately.

Note: Use Lockite Material on the threads for a permanent installation to the shell.



#### How to Order Adapter Ring

##### Part Number

2500-008-0 X XX

Shell Size (varies from connector shell size designation, see last column of table at left)

Finish  
 0 - Electroless Nickel  
 1 - Black Anodize  
 2 - Cadmium/olive drab  
 3 - Stainless steel, passivated

# MS/Standard insert arrangements

| Insert Arrangement | Service Rating | Total Contacts | Contact Size |   |   |    |    |
|--------------------|----------------|----------------|--------------|---|---|----|----|
|                    |                |                | 0            | 4 | 8 | 12 | 16 |
| 8S-1               | A              | 1              |              |   |   |    | 1  |
| 10S-2              | A              | 1              |              |   |   |    | 1  |
| 10SL-3             | A              | 3              |              |   |   |    | 3  |
| 10SL-4             | A              | 2              |              |   |   |    | 2  |
| 12S-1              | A              | 2              |              |   |   |    | 2  |
| 12S-2              | A              | 2              |              |   |   |    | 2  |
| 12S-3              | A              | 2              |              |   |   |    | 2  |
| 12S-4              | D              | 1              |              |   |   |    | 1  |
| 12-5               | D              | 1              |              |   |   | 1  |    |
| 14S-1**            | A              | 3              |              |   |   |    | 3  |
| 14S-2              | Inst.          | 4              |              |   |   |    | 4  |
| 14-3               | A              | 1              |              |   | 1 |    |    |
| 14S-5              | Inst.          | 5              |              |   |   |    | 5  |
| 14S-6              | Inst.          | 6              |              |   |   |    | 6  |
| 14S-7              | A              | 3              |              |   |   |    | 3  |
| 14S-9**            | A              | 2              |              |   |   |    | 2  |
| 14S-10             | Inst.          | 4              |              |   |   |    | 4  |
| 14S-11             | Inst.          | 4              |              |   |   |    | 4  |
| 14S-12             | A              | 3              |              |   |   |    | 3  |
| 14S-13             | A              | 3              |              |   |   |    | 3  |
| 16S-1              | A              | 7              |              |   |   |    | 7  |
| 16-2*              | E              | 1              |              |   |   | 1  |    |
| 16S-3*             | B              | 1              |              |   |   |    | 1  |
| 16S-4*             | D              | 2              |              |   |   |    | 2  |
| 16-7*              | A              | 3              |              |   | 1 |    | 2  |
| 16S-8              | A              | 5              |              |   |   |    | 5  |
| 16-9               | A              | 4              |              |   |   | 2  | 2  |
| 16-10              | A              | 3              |              |   |   | 3  |    |
| 16-11              | A              | 2              |              |   |   | 2  |    |
| 16-12              | A              | 1              |              | 1 |   |    |    |
| 16-13              | A              | 2              |              |   |   | 2  |    |
| 18-1               | A/Inst.        | 10             |              |   |   |    | 10 |
| 18-4               | D              | 4              |              |   |   |    | 4  |
| 18-5               | D              | 3              |              |   |   | 2  | 1  |
| 18-6*              | D              | 1              |              | 1 |   |    |    |
| 18-7*              | B              | 1              |              |   | 1 |    |    |
| 18-8               | A              | 8              |              |   |   | 1  | 7  |
| 18-9               | Inst.          | 7              |              |   |   | 2  | 5  |
| 18-10**            | A              | 4              |              |   |   | 4  |    |
| 18-11              | A              | 5              |              |   |   | 5  |    |
| 18-12*             | A              | 6              |              |   |   |    | 6  |
| 18-13              | A              | 4              |              |   | 1 | 3  |    |
| 18-14*             | A              | 2              |              | 1 |   |    | 1  |
| 18-15*             | A              | 4              |              |   |   | 4  |    |
| 18-16*             | C              | 1              |              |   |   | 1  |    |
| 18-17              | Inst.          | 7              |              |   |   | 2  | 5  |
| 18-18              | Inst.          | 7              |              |   |   | 2  | 5  |
| 18-19**            | A              | 10             |              |   |   |    | 10 |
| 18-22**            | D              | 3              |              |   |   |    | 3  |

| Insert Arrangement | Service Rating | Total Contacts | Contact Size |   |   |    |    |
|--------------------|----------------|----------------|--------------|---|---|----|----|
|                    |                |                | 0            | 4 | 8 | 12 | 16 |
| 18-23              | A/Inst.        | 10             |              |   |   |    | 10 |
| 18-24              | A/Inst.        | 10             |              |   |   |    | 10 |
| 18-27              | D              | 3              |              |   |   | 2  | 1  |
| 18-28              | D              | 3              |              |   |   | 2  | 1  |
| 20-2               | D              | 1              | 1            |   |   |    |    |
| 20-4               | D              | 4              |              |   |   | 4  |    |
| 20-7               | D/A            | 8              |              |   |   |    | 8  |
| 20-8               | Inst.          | 6              |              |   | 2 |    | 4  |
| 20-9*              | D/A            | 8              |              |   |   | 1  | 7  |
| 20-14              | A              | 5              |              |   | 2 | 3  |    |
| 20-15              | A              | 7              |              |   |   | 7  |    |
| 20-16              | A              | 9              |              |   |   | 2  | 7  |
| 20-17              | A              | 6              |              |   |   | 5  | 1  |
| 20-18              | A              | 9              |              |   |   | 3  | 6  |
| 20-19              | A              | 3              |              |   | 3 |    |    |
| 20-21              | A              | 9              |              |   |   | 1  | 8  |
| 20-22              | A              | 6              |              |   | 3 |    | 3  |
| 20-24              | A              | 4              |              |   | 2 |    | 2  |
| 20-27              | A              | 14             |              |   |   |    | 14 |
| 20-29              | A              | 17             |              |   |   |    | 17 |
| 20-32              | D/A            | 8              |              |   |   |    | 8  |
| 20-33              | A              | 11             |              |   |   |    | 11 |
| 22-2               | D              | 3              |              |   | 3 |    |    |
| 22-4**             | A              | 4              |              |   | 2 | 2  |    |
| 22-5               | D              | 6              |              |   |   | 2  | 4  |
| 22-6*              | D              | 3              |              |   | 2 |    | 1  |
| 22-7*              | E              | 1              | 1            |   |   |    |    |
| 22-9*              | E              | 3              |              |   |   | 3  |    |
| 22-10*             | E              | 4              |              |   |   |    | 4  |
| 22-11*             | B              | 2              |              |   |   |    | 2  |
| 22-12*             | D              | 5              |              |   | 2 |    | 3  |
| 22-14              | A              | 19             |              |   |   |    | 19 |
| 22-15*             | E/A            | 6              |              |   |   | 5  | 1  |
| 22-17*             | D/A            | 9              |              |   |   | 1  | 8  |
| 22-18*             | D/A            | 8              |              |   |   |    | 8  |
| 22-19              | A              | 14             |              |   |   |    | 14 |
| 22-21              | A              | 3              | 1            |   |   |    | 2  |
| 22-22              | A              | 4              |              |   | 4 |    |    |
| 22-23              | D/A            | 8              |              |   |   | 8  |    |
| 22-27*             | D/A            | 9              |              |   | 1 |    | 8  |
| 22-30              | A              | 19             |              |   |   |    | 19 |
| 22-32              | D              | 6              |              |   |   | 2  | 4  |
| 22-36*             | D/A            | 8              |              |   |   | 8  |    |
| 24-1**             | D              | 2              | 1            |   |   | 1  |    |
| 24-2               | D              | 7              |              |   |   | 7  |    |
| 24-4*              | D              | 4              | 1            |   |   |    | 3  |
| 24-5**             | A              | 16             |              |   |   |    | 16 |
| 24-6*              | D/A            | 8              |              |   |   | 8  |    |

\* Consult Amphenol, Sidney, NY for availability

\*\* Inactive for new design

# MS/Standard insert arrangements

| Insert Arrangement | Service Rating | Total Contacts | Contact Size |   |   |    |    |
|--------------------|----------------|----------------|--------------|---|---|----|----|
|                    |                |                | 0            | 4 | 8 | 12 | 16 |
| 24-7               | A              | 16             |              |   |   | 2  | 14 |
| 24-10              | A              | 7              |              |   | 7 |    |    |
| 24-11              | A              | 9              |              |   | 3 | 6  |    |
| 24-12              | A              | 5              |              | 2 |   | 3  |    |
| 24-15              | A              | 16             |              |   |   |    | 16 |
| 24-16*             | D/A            | 7              |              |   | 1 | 3  | 3  |
| 24-20              | D              | 11             |              |   |   | 2  | 9  |
| 24-21*             | D              | 10             |              |   | 1 |    | 9  |
| 24-22              | D              | 4              |              |   | 4 |    |    |
| 24-24              | A              | 16             |              |   |   |    | 16 |
| 24-27*             | E              | 7              |              |   |   |    | 7  |
| 24-28              | Inst.          | 24             |              |   |   |    | 24 |
| 24-80*             | Inst.          | 23             |              |   |   |    | 23 |
| 28-1               | D/A            | 9              |              |   | 3 | 6  |    |
| 28-2               | D              | 14             |              |   |   | 2  | 12 |
| 28-3*              | E              | 3              |              |   | 3 |    |    |
| 28-4*              | E/D            | 9              |              |   |   | 2  | 7  |
| 28-5*              | D              | 5              |              | 2 |   | 1  | 2  |
| 28-8*              | E/D/A          | 12             |              |   |   | 2  | 10 |
| 28-9               | D              | 12             |              |   |   | 6  | 6  |
| 28-10              | D/A            | 7              |              | 2 | 2 | 3  |    |
| 28-11              | A              | 22             |              |   |   | 4  | 18 |
| 28-12              | A              | 26             |              |   |   |    | 26 |
| 28-13              | A              | 26             |              |   |   |    | 26 |
| 28-15              | A              | 35             |              |   |   |    | 35 |
| 28-16*             | A              | 20             |              |   |   |    | 20 |
| 28-17              | B/D/A          | 15             |              |   |   |    | 15 |
| 28-18*             | C/D/A/Inst.    | 12             |              |   |   |    | 12 |
| 28-19*             | B/D/A          | 10             |              |   |   | 4  | 6  |
| 28-20              | A              | 14             |              |   |   | 10 | 4  |
| 28-21              | A              | 37             |              |   |   |    | 37 |
| 28-22              | D              | 6              |              | 3 |   |    | 3  |
| 32-1               | E/D            | 5              | 2            |   |   | 3  |    |
| 32-2*              | E              | 5              |              | 3 |   |    | 2  |
| 32-3*              | D              | 9              | 1            | 2 |   | 2  | 4  |
| 32-6               | A              | 23             |              | 2 | 3 | 2  | 16 |
| 32-7               | Inst./A        | 35             |              |   |   | 7  | 28 |
| 32-9               | D              | 14             |              | 2 |   |    | 12 |
| 32-13              | D              | 23             |              |   |   | 5  | 18 |
| 32-15              | D              | 8              | 2            |   |   | 6  |    |
| 32-16              | A              | 23             |              | 2 | 3 | 2  | 16 |
| 32-17              | D              | 4              |              | 4 |   |    |    |
| 32-19*             | E/D            | 5              | 2            |   |   | 3  |    |
| 32-20              | A              | 23             |              | 2 | 3 | 2  | 16 |

| Insert Arrangement | Service Rating | Total Contacts | Contact Size |   |   |    |    |
|--------------------|----------------|----------------|--------------|---|---|----|----|
|                    |                |                | 0            | 4 | 8 | 12 | 16 |
| 32-22*             | A              | 54             |              |   |   |    | 54 |
| 32-63              | D              | 5              |              | 5 |   |    |    |
| 32-73              | A              | 46             |              |   |   |    | 46 |
| 36-3               | D              | 6              | 3            |   |   | 3  |    |
| 36-5               | A              | 4              | 4            |   |   |    |    |
| 36-6               | A              | 6              | 2            | 4 |   |    |    |
| 36-7               | A              | 47             |              |   |   | 7  | 40 |
| 36-8               | A              | 47             |              |   |   | 1  | 46 |
| 36-9               | A              | 31             |              | 1 | 2 | 14 | 14 |
| 36-10              | A              | 48             |              |   |   |    | 48 |
| 36-11              | A              | 48             |              |   |   |    | 48 |
| 36-12              | A              | 48             |              |   |   |    | 48 |
| 36-15              | D/A            | 35             |              |   |   |    | 35 |
| 36-16              | A              | 47             |              |   |   | 7  | 40 |
| 36-17              | A              | 47             |              |   |   | 7  | 40 |
| 36-18              | A              | 31             |              | 1 | 2 | 14 | 14 |
| 36-21              | A              | 31             |              | 1 | 2 | 14 | 14 |
| 36-52              | A              | 52             |              |   |   |    | 52 |
| 36-66*             | A              | 56             |              |   |   | 4  | 52 |
| 40-1               | D              | 30             |              |   |   | 6  | 24 |
| 40-2*              | D              | 23             |              |   |   |    | 23 |
| 40-3*              | D              | 23             |              | 1 |   | 4  | 18 |
| 40-4*              | D              | 23             |              | 2 | 3 | 2  | 16 |
| 40-5*              | A              | 15             | 3            | 2 | 4 | 6  |    |
| 40-6*              | D              | 26             | 1            |   |   | 1  | 24 |
| 40-7*              | A/D            | 22             | 2            |   |   | 2  | 18 |
| 40-9               | A              | 47             |              |   | 1 | 22 | 24 |
| 40-10*             | A              | 29             |              | 4 | 9 |    | 16 |
| 40-11*             | D              | 25             | 1            | 1 | 1 | 4  | 18 |
| 40-56*             | A              | 85             |              |   |   |    | 85 |
| 40-62*             | A              | 60             |              |   |   |    | 60 |

\* Consult Amphenol, Sidney, NY for availability

\*\* Inactive for new design


# MS/Standard

## insert alternate positioning

To avoid cross-plugging problems in applications requiring the use of more than one connector of the same size and arrangement, alternate rotations are available as indicated in the accompanying charts.

As shown in the diagram below, the front face of the pin insert is rotated within the shell in a clockwise direction from the normal shell key. The socket insert would be rotated counter-clockwise the same number of degrees in respect to the normal shell key.

The charts give the W, X, Y, Z positions for the alternate rotations available for the insert arrangements of the rear release MIL-DTL-5015 series of connectors. If an insert arrangement number is not given, then there is no available alternate rotation for that pattern.



The following insert arrangements have the same alternate insert rotations for W, X, Y and Z, which are:

| Degrees |     |     |     |
|---------|-----|-----|-----|
| W       | X   | Y   | Z   |
| 80      | 110 | 250 | 280 |

|       |       |       |       |       |       |
|-------|-------|-------|-------|-------|-------|
| 16-7  | 20-22 | 24-4  | 28-4  | 28-21 | 40-3  |
| 18-5  | 22-6  | 24-5  | 28-8  | 32-1  | 40-4  |
| 18-9  | 22-12 | 24-6  | 28-9  | 32-3  | 40-5  |
| 18-13 | 22-14 | 24-7  | 28-10 | 32-6  | 40-6  |
| 18-14 | 22-15 | 24-12 | 28-11 | 32-9  | 40-7  |
| 20-7  | 22-17 | 24-16 | 28-15 | 32-13 | 40-11 |
| 20-8  | 22-18 | 24-20 | 28-16 | 32-22 |       |
| 20-9  | 22-19 | 24-21 | 28-17 | 36-7  |       |
| 20-14 | 22-21 | 24-28 | 28-19 | 36-8  |       |
| 20-16 | 24-1  | 28-1  | 28-20 | 40-2  |       |

| Insert Arrangement | Degrees |     |     |     |
|--------------------|---------|-----|-----|-----|
|                    | W       | X   | Y   | Z   |
| 12S-3              | 70      | 145 | 215 | 290 |
| 14S-2              | —       | 120 | 240 | —   |
| 14S-5              | —       | 110 | —   | —   |
| 14S-7              | 90      | 180 | 270 | —   |
| 14S-9              | 70      | 145 | 215 | 290 |
| 16S-1              | 80      | —   | —   | 280 |
| 16S-4              | 35      | 110 | 250 | 325 |
| 16S-8              | —       | 170 | 265 | —   |
| 16-9               | 35      | 110 | 250 | 325 |
| 16-10              | 90      | 180 | 270 | —   |
| 16-11              | 35      | 110 | 250 | 325 |
| 16-13              | 35      | 110 | 250 | 325 |
| 18-1               | 70      | 145 | 215 | 290 |
| 18-4               | 35      | 110 | 250 | 325 |
| 18-8               | 70      | —   | —   | 290 |
| 18-10              | —       | 120 | 240 | —   |
| 18-11              | —       | 170 | 265 | —   |
| 18-12              | 80      | —   | —   | 280 |
| 18-15              | —       | 120 | 240 | —   |
| 18-19              | —       | 120 | 240 | —   |
| 18-22              | 70      | 145 | 215 | 290 |
| 20-4               | 45      | 110 | 250 | —   |
| 20-15              | 80      | —   | —   | 280 |

| Insert Arrangement | Degrees |     |     |     |
|--------------------|---------|-----|-----|-----|
|                    | W       | X   | Y   | Z   |
| 20-17              | 90      | 180 | 270 | —   |
| 20-18              | 35      | 110 | 250 | 325 |
| 20-19              | 90      | 180 | 270 | —   |
| 20-21              | 35      | 110 | 250 | 325 |
| 20-24              | 35      | 110 | 250 | 325 |
| 20-27              | 35      | 110 | 250 | 325 |
| 20-29              | 80      | —   | —   | 280 |
| 22-2               | 70      | 145 | 215 | 290 |
| 22-4               | 35      | 110 | 250 | 325 |
| 22-5               | 35      | 110 | 250 | 325 |
| 22-9               | 70      | 145 | 215 | 290 |
| 22-10              | 35      | 110 | 250 | 325 |
| 22-11              | 35      | 110 | 250 | 325 |
| 22-22              | —       | 110 | 250 | —   |
| 22-23              | 35      | —   | 250 | —   |
| 22-27              | 80      | —   | 250 | 280 |
| 22-36              | 90      | —   | 270 | —   |
| 24-2               | 80      | —   | —   | 280 |
| 24-10              | 80      | —   | —   | 280 |
| 24-11              | 35      | 110 | 250 | 325 |
| 24-22              | 45      | 110 | 250 | —   |
| 24-27              | 80      | —   | —   | 280 |
| 24-80              | 35      | 145 | 240 | 300 |

| Insert Arrangement | Degrees |     |     |     |
|--------------------|---------|-----|-----|-----|
|                    | W       | X   | Y   | Z   |
| 28-2               | 35      | 110 | 250 | 325 |
| 28-3               | 70      | 145 | 215 | 290 |
| 28-5               | 35      | 110 | 250 | 325 |
| 28-12              | 90      | 180 | 270 | —   |
| 28-18              | 70      | 145 | 215 | 290 |
| 28-22              | 70      | 145 | 215 | 290 |
| 32-2               | 70      | 145 | 215 | 290 |
| 32-7               | 80      | 125 | 235 | 280 |
| 32-15              | 35      | 110 | 250 | 280 |
| 32-17              | 45      | 110 | 250 | —   |
| 32-73              | 36      | —   | —   | —   |
| 36-3               | 70      | 145 | 215 | 290 |
| 36-5               | —       | 120 | 240 | —   |
| 36-6               | 35      | 110 | 250 | 325 |
| 36-9               | 80      | 125 | 235 | 280 |
| 36-10              | 80      | 125 | 235 | 280 |
| 36-15              | 60      | 125 | 245 | 305 |
| 36-52              | 72      | 144 | 216 | 288 |
| 36-66              | 110     | 250 | 260 | 280 |
| 40-1               | 65      | 130 | 235 | 300 |
| 40-9               | 65      | 125 | 255 | 310 |
| 40-10              | 65      | 125 | 255 | 310 |
| 40-56              | 72      | 144 | 216 | 288 |
| 40-62              | 30      | 130 | 220 | 290 |

# MS/Standard contact arrangements

front face of pin insert or rear face of socket insert illustrated

|                           |             |              |               |               |              |              |              |
|---------------------------|-------------|--------------|---------------|---------------|--------------|--------------|--------------|
|                           |             |              |               |               |              |              |              |
| <b>Insert Arrangement</b> | <b>8S-1</b> | <b>10S-2</b> | <b>10SL-3</b> | <b>10SL-4</b> | <b>12S-1</b> | <b>12S-2</b> | <b>12S-3</b> |
| <b>Service Rating</b>     | <b>A</b>    | <b>A</b>     | <b>A***</b>   | <b>A</b>      | <b>A</b>     | <b>A</b>     | <b>A</b>     |
| <b>Number of Contacts</b> | <b>1</b>    | <b>1</b>     | <b>3</b>      | <b>2</b>      | <b>2</b>     | <b>2</b>     | <b>2</b>     |
| <b>Contact Size</b>       | <b>16</b>   | <b>16</b>    | <b>16</b>     | <b>16</b>     | <b>16</b>    | <b>16</b>    | <b>16</b>    |

|                           |              |              |                |              |             |              |              |
|---------------------------|--------------|--------------|----------------|--------------|-------------|--------------|--------------|
|                           |              |              |                |              |             |              |              |
| <b>Insert Arrangement</b> | <b>12S-4</b> | <b>12S-5</b> | <b>14S-1**</b> | <b>14S-2</b> | <b>14-3</b> | <b>14S-5</b> | <b>14S-6</b> |
| <b>Service Rating</b>     | <b>D</b>     | <b>D</b>     | <b>A</b>       | <b>Inst.</b> | <b>A</b>    | <b>Inst.</b> | <b>Inst.</b> |
| <b>Number of Contacts</b> | <b>1</b>     | <b>1</b>     | <b>3</b>       | <b>4</b>     | <b>1</b>    | <b>5</b>     | <b>6</b>     |
| <b>Contact Size</b>       | <b>16</b>    | <b>12</b>    | <b>16</b>      | <b>16</b>    | <b>8</b>    | <b>16</b>    | <b>16</b>    |

|                           |              |                |               |               |               |               |
|---------------------------|--------------|----------------|---------------|---------------|---------------|---------------|
|                           |              |                |               |               |               |               |
| <b>Insert Arrangement</b> | <b>14S-7</b> | <b>14S-9**</b> | <b>14S-10</b> | <b>14S-11</b> | <b>14S-12</b> | <b>14S-13</b> |
| <b>Service Rating</b>     | <b>A</b>     | <b>A</b>       | <b>Inst.</b>  | <b>Inst.</b>  | <b>A</b>      | <b>A</b>      |
| <b>Number of Contacts</b> | <b>3</b>     | <b>2</b>       | <b>4</b>      | <b>4</b>      | <b>3</b>      | <b>3</b>      |
| <b>Contact Size</b>       | <b>16</b>    | <b>16</b>      | <b>16</b>     | <b>16</b>     | <b>16</b>     | <b>16</b>     |

|                           |              |              |               |               |              |              |
|---------------------------|--------------|--------------|---------------|---------------|--------------|--------------|
|                           |              |              |               |               |              |              |
| <b>Insert Arrangement</b> | <b>16S-1</b> | <b>16-2*</b> | <b>16S-3*</b> | <b>16S-4*</b> | <b>16-7*</b> | <b>16S-8</b> |
| <b>Service Rating</b>     | <b>A</b>     | <b>E</b>     | <b>B</b>      | <b>D</b>      | <b>A</b>     | <b>A</b>     |
| <b>Number of Contacts</b> | <b>7</b>     | <b>1</b>     | <b>1</b>      | <b>2</b>      | <b>1 2</b>   | <b>5</b>     |
| <b>Contact Size</b>       | <b>16</b>    | <b>12</b>    | <b>16</b>     | <b>16</b>     | <b>8 16</b>  | <b>16</b>    |

\* Consult Amphenol, Sidney, NY for availability.

\*\* Inactive for new design

\*\*\* Service rating Inst. Class K

|           |           |          |          |          |
|-----------|-----------|----------|----------|----------|
|           |           |          |          |          |
| <b>16</b> | <b>12</b> | <b>8</b> | <b>4</b> | <b>0</b> |

**CONTACT LEGEND**

# MS/Standard contact arrangements

front face of pin insert or rear face of socket insert illustrated

|                    |                                                                                     |                                                                                     |                                                                                     |                                                                                      |                                                                                       |                                                                                       |
|--------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
|                    |    |    |    |    |    |    |
| Insert Arrangement | 16-9                                                                                | 16-10                                                                               | 16-11                                                                               | 16-12                                                                                | 16-13                                                                                 | 18-1                                                                                  |
| Service Rating     | A                                                                                   | A                                                                                   | A                                                                                   | A                                                                                    | A                                                                                     | B, C, F, G = A; Bal. = Inst.                                                          |
| Number of Contacts | 2 2                                                                                 | 3                                                                                   | 2                                                                                   | 1                                                                                    | 2††                                                                                   | 10                                                                                    |
| Contact Size       | 12 16                                                                               | 12                                                                                  | 12                                                                                  | 4                                                                                    | 12                                                                                    | 16                                                                                    |
|                    |    |    |    |    |    |    |
| Insert Arrangement | 18-4                                                                                | 18-5                                                                                | 18-6*                                                                               | 18-7*                                                                                | 18-8                                                                                  | 18-9                                                                                  |
| Service Rating     | D                                                                                   | D                                                                                   | D                                                                                   | B                                                                                    | A                                                                                     | Inst.                                                                                 |
| Number of Contacts | 4                                                                                   | 2 1                                                                                 | 1                                                                                   | 1                                                                                    | 1 7                                                                                   | 2 5                                                                                   |
| Contact Size       | 16                                                                                  | 12 16                                                                               | 4                                                                                   | 8                                                                                    | 12 16                                                                                 | 12 16                                                                                 |
|                    |  |  |  |  |  |  |
| Insert Arrangement | 18-10**                                                                             | 18-11                                                                               | 18-12*                                                                              | 18-13                                                                                | 18-14*                                                                                | 18-15*                                                                                |
| Service Rating     | A                                                                                   | A                                                                                   | A                                                                                   | A                                                                                    | A                                                                                     | A                                                                                     |
| Number of Contacts | 4                                                                                   | 5                                                                                   | 6                                                                                   | 1 3                                                                                  | 1 1                                                                                   | 4††                                                                                   |
| Contact Size       | 12                                                                                  | 12                                                                                  | 16                                                                                  | 8 12                                                                                 | 4 16                                                                                  | 12                                                                                    |
|                    |  |  |  |  |  |  |
| Insert Arrangement | 18-16*                                                                              | 18-17                                                                               | 18-18                                                                               | 18-19**                                                                              | 18-22**                                                                               | 18-23                                                                                 |
| Service Rating     | C                                                                                   | Inst.                                                                               | Inst.                                                                               | A                                                                                    | D                                                                                     | B, C, F, G = A; Bal. = Inst.                                                          |
| Number of Contacts | 1                                                                                   | 2 5                                                                                 | 2 5                                                                                 | 10                                                                                   | 3                                                                                     | 10                                                                                    |
| Contact Size       | 12                                                                                  | 12 16                                                                               | 12 16                                                                               | 16                                                                                   | 16                                                                                    | 16                                                                                    |

\* Consult Amphenol, Sidney, NY for availability.  
 \*\* Inactive for new design  
 † one alumel contact and one chromel contact  
 †† A, C = Iron; B, D = Constantan

CONTACT LEGEND

⊕

●

●

○

⊗

16

12





8






4







0

# MS/Standard contact arrangements

front face of pin insert or rear face of socket insert illustrated

|                    |                                                                                   |                                                                                   |                                                                                   |                                                                                    |                                                                                     |                                                                                     |
|--------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|                    |  |  |  |  |  |  |
| Insert Arrangement | 18-24                                                                             | 18-27                                                                             | 18-28                                                                             | 20-2                                                                               | 20-4                                                                                | 20-7                                                                                |
| Service Rating     | B, C, F, G = A; Bal. = Inst.                                                      | D                                                                                 | D                                                                                 | D                                                                                  | D                                                                                   | A, B, G, H = D; C, D, E, F = A                                                      |
| Number of Contacts | 10                                                                                | 2 1                                                                               | 2 1                                                                               | 1                                                                                  | 4                                                                                   | 8                                                                                   |
| Contact Size       | 16                                                                                | 12 16                                                                             | 12 16                                                                             | 0                                                                                  | 12                                                                                  | 16                                                                                  |

|                    |                                                                                    |                                                                                    |                                                                                    |                                                                                     |                                                                                      |                                                                                      |
|--------------------|------------------------------------------------------------------------------------|------------------------------------------------------------------------------------|------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|
|                    |  |  |  |  |  |  |
| Insert Arrangement | 20-8*                                                                              | 20-9*                                                                              | 20-14                                                                              | 20-15                                                                               | 20-16                                                                                | 20-17                                                                                |
| Service Rating     | Inst.                                                                              | H = D; Bal. = A                                                                    | A                                                                                  | A                                                                                   | A                                                                                    | A                                                                                    |
| Number of Contacts | 2 4                                                                                | 1 7                                                                                | 2 3                                                                                | 7                                                                                   | 2 7                                                                                  | 5 1                                                                                  |
| Contact Size       | 8 16                                                                               | 12 16                                                                              | 8 12                                                                               | 12                                                                                  | 12 16                                                                                | 12 16                                                                                |

|                    |                                                                                     |                                                                                     |                                                                                     |                                                                                      |                                                                                       |                                                                                       |
|--------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
|                    |  |  |  |  |  |  |
| Insert Arrangement | 20-18                                                                               | 20-19                                                                               | 20-21                                                                               | 20-22                                                                                | 20-24                                                                                 | 20-27                                                                                 |
| Service Rating     | A                                                                                   | A                                                                                   | A                                                                                   | A                                                                                    | A                                                                                     | A                                                                                     |
| Number of Contacts | 3 6                                                                                 | 3                                                                                   | 1 8                                                                                 | 3 3                                                                                  | 2 2                                                                                   | 14                                                                                    |
| Contact Size       | 12 16                                                                               | 8                                                                                   | 12 16                                                                               | 8 16                                                                                 | 8 16                                                                                  | 16                                                                                    |

\* Consult Amphenol, Sidney, NY for availability.

CONTACT LEGEND

⊕

◐

◑

○

⊗

16

12

8

4

0

# MS/Standard contact arrangements

front face of pin insert or rear face of socket insert illustrated

|                    |                       |                          |       |      |        |       |
|--------------------|-----------------------|--------------------------|-------|------|--------|-------|
|                    |                       |                          |       |      |        |       |
|                    | 260° Rotation of 20-7 |                          |       |      |        |       |
| Insert Arrangement | 20-29                 | 20-32                    | 20-33 | 22-2 | 22-4** | 22-5  |
| Service Rating     | A                     | A, B, G, H = D; Bal. = A | A     | D    | A      | D     |
| Number of Contacts | 17                    | 8                        | 11    | 3    | 2 2    | 2 4   |
| Contact Size       | 16                    | 16                       | 16    | 8    | 8 12   | 12 16 |

|                    |        |       |       |        |        |        |
|--------------------|--------|-------|-------|--------|--------|--------|
|                    |        |       |       |        |        |        |
| Insert Arrangement | 22-6** | 22-7* | 22-9* | 22-10* | 22-11* | 22-12* |
| Service Rating     | D      | E     | E     | E      | B      | D      |
| Number of Contacts | 2 1    | 1     | 3     | 4      | 2      | 2 3    |
| Contact Size       | 8 16   | 0     | 12    | 16     | 16     | 8 16   |

|                    |       |                 |                 |                       |       |       |
|--------------------|-------|-----------------|-----------------|-----------------------|-------|-------|
|                    |       |                 |                 |                       |       |       |
| Insert Arrangement | 22-14 | 22-15*          | 22-17*          | 22-18*                | 22-19 | 22-21 |
| Service Rating     | A     | D = 3; Bal. = A | A = D; Bal. = A | C, D, E = A; Bal. = D | A     | A     |
| Number of Contacts | 19    | 5 1             | 1 8             | 8                     | 14    | 1 2   |
| Contact Size       | 16    | 12 16           | 12 16           | 16                    | 16    | 0 16  |

\* Consult Amphenol, Sidney, NY for availability.  
 \*\* Inactive for new design

CONTACT LEGEND

⊕

⊖

⦿

○

⊗

16

12

8

4

0

# MS/Standard contact arrangements

front face of pin insert or rear face of socket insert illustrated

|                    |                                                                                   |                                                                                   |                                                                                   |                                                                                     |                                                                                     |
|--------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|                    |  |  |  |  |  |
| Insert Arrangement | 22-22                                                                             | 22-23                                                                             | 22-27*                                                                            | 22-30                                                                               | 22-32                                                                               |
| Service Rating     | A                                                                                 | H = D; Bal. = A                                                                   | J = D; Bal. = A                                                                   | A                                                                                   | D                                                                                   |
| Number of Contacts | 4                                                                                 | 8                                                                                 | 1 8                                                                               | 19                                                                                  | 2 4                                                                                 |
| Contact Size       | 8                                                                                 | 12                                                                                | 8 16                                                                              | 16                                                                                  | 12 16                                                                               |

|                    |                                                                                    |                                                                                    |                                                                                    |                                                                                      |                                                                                      |
|--------------------|------------------------------------------------------------------------------------|------------------------------------------------------------------------------------|------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|
|                    |  |  |  |  |  |
| Insert Arrangement | 22-36*                                                                             | 24-1**                                                                             | 24-2                                                                               | 24-4*                                                                                | 24-5**                                                                               |
| Service Rating     | H = D; Bal. = A                                                                    | D                                                                                  | D                                                                                  | D                                                                                    | A                                                                                    |
| Number of Contacts | 8                                                                                  | 1 1                                                                                | 7                                                                                  | 1 3                                                                                  | 16                                                                                   |
| Contact Size       | 12                                                                                 | 0 12                                                                               | 12                                                                                 | 0 16                                                                                 | 16                                                                                   |

|                    |                                                                                     |                                                                                     |                                                                                     |                                                                                       |                                                                                       |
|--------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
|                    |  |  |  |  |  |
| Insert Arrangement | 24-6*                                                                               | 24-7                                                                                | 24-10                                                                               | 24-11                                                                                 | 24-12                                                                                 |
| Service Rating     | A, G, H = D; Bal. = A                                                               | A                                                                                   | A                                                                                   | A                                                                                     | A                                                                                     |
| Number of Contacts | 8                                                                                   | 2 14                                                                                | 7                                                                                   | 3 6                                                                                   | 2 3                                                                                   |
| Contact Size       | 12                                                                                  | 12 16                                                                               | 8                                                                                   | 8 12                                                                                  | 4 12                                                                                  |













\* Consult Amphenol, Sidney, NY for availability.  
 \*\* Inactive for new design



CONTACT LEGEND
16
12
8
4
0

# MS/Standard contact arrangements

front face of pin insert or rear face of socket insert illustrated

|                    |                                                                                     |                                                                                     |                                                                                      |                                                                                       |                                                                                       |
|--------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
|                    |    |    |    |    |    |
| Insert Arrangement | 24-15                                                                               | 24-16*                                                                              | 24-20                                                                                | 24-21*                                                                                | 24-22                                                                                 |
| Service Rating     | A                                                                                   | A, B, F, G = D; C, D, E = A                                                         | D                                                                                    | D                                                                                     | D                                                                                     |
| Number of Contacts | 16                                                                                  | 1 3 3                                                                               | 2 9                                                                                  | 1 9                                                                                   | 4                                                                                     |
| Contact Size       | 16                                                                                  | 8 12 16                                                                             | 12 16                                                                                | 8 16                                                                                  | 8                                                                                     |
|                    |   |   |   |   |   |
| Insert Arrangement | 24-24                                                                               | 24-27*                                                                              | 24-28                                                                                | 24-80*                                                                                | 28-1                                                                                  |
| Service Rating     | A                                                                                   | E                                                                                   | Inst.                                                                                | Inst.                                                                                 | A, J, E = D; Bal. = A                                                                 |
| Number of Contacts | 16                                                                                  | 7                                                                                   | 24                                                                                   | 23                                                                                    | 3 6                                                                                   |
| Contact Size       | 16                                                                                  | 16                                                                                  | 16                                                                                   | 16                                                                                    | 8 12                                                                                  |
|                    |  |  |  |  |  |
| Insert Arrangement | 28-2                                                                                | 28-3*                                                                               | 28-4*                                                                                | 28-5*                                                                                 | 28-8*                                                                                 |
| Service Rating     | D                                                                                   | E                                                                                   | G, P, S = E; Bal. = D                                                                | D                                                                                     | L, M = E; B = D; Bal. = A                                                             |
| Number of Contacts | 2 12                                                                                | 3                                                                                   | 2 7                                                                                  | 2 1 2                                                                                 | 2 10                                                                                  |
| Contact Size       | 12 16                                                                               | 8                                                                                   | 12 16                                                                                | 4 12 16                                                                               | 12 16                                                                                 |

\* Consult Amphenol, Sidney, NY for availability.

CONTACT LEGEND











16

12











8

4

0

# MS/Standard contact arrangements

front face of pin insert or rear face of socket insert illustrated

|                    |                                                                                     |                                                                                     |                                                                                       |                                                                                       |
|--------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
|                    |    |    |     |    |
| Insert Arrangement | 28-9                                                                                | 28-10                                                                               | 28-11                                                                                 | 28-12                                                                                 |
| Service Rating     | D                                                                                   | G = D, Bal. = A                                                                     | A                                                                                     | A                                                                                     |
| Number of Contacts | 6 6                                                                                 | 2 2 3                                                                               | 4 18                                                                                  | 26                                                                                    |
| Contact Size       | 12 16                                                                               | 4 8 12                                                                              | 12 16                                                                                 | 16                                                                                    |
|                    |   |   |    |   |
| Insert Arrangement | 28-13                                                                               | 28-15                                                                               | 28-16**                                                                               | 28-17                                                                                 |
| Service Rating     | A                                                                                   | A                                                                                   | A                                                                                     | R = B; M, N, P = D; Bal. = A                                                          |
| Number of Contacts | 26                                                                                  | 35                                                                                  | 20                                                                                    | 15                                                                                    |
| Contact Size       | 16                                                                                  | 16                                                                                  | 16                                                                                    | 16                                                                                    |
|                    |  |  |  |  |
| Insert Arrangement | 28-18*                                                                              | 28-19*                                                                              | 28-20                                                                                 | 28-21                                                                                 |
| Service Rating     | M = C; G, H, J, K, L = D; A, B = A; Bal. = Inst.                                    | H, M = B; A, B = D; Bal. = A                                                        | A                                                                                     | A                                                                                     |
| Number of Contacts | 12                                                                                  | 4 6                                                                                 | 10 4                                                                                  | 37                                                                                    |
| Contact Size       | 16                                                                                  | 12 16                                                                               | 12 16                                                                                 | 16                                                                                    |

\* Consult Amphenol, Sidney, NY for availability.  
 \*\* Inactive for new design

CONTACT LEGEND

⊕

⬤

⬤

○

⊗

16

12

8

4

0

# MS/Standard contact arrangements

front face of pin insert or rear face of socket insert illustrated

|                    |       |                       |       |           |
|--------------------|-------|-----------------------|-------|-----------|
|                    |       |                       |       |           |
| Insert Arrangement | 28-22 | 32-1                  | 32-2* | 32-3*     |
| Service Rating     | D     | A = E; B, C, D, E = D | E     | D         |
| Number of Contacts | 3 3   | 2 3                   | 3 2   | 1 2 2 4   |
| Contact Size       | 4 16  | 0 12                  | 4 16  | 0 4 12 16 |

|                    |           |                              |      |       |
|--------------------|-----------|------------------------------|------|-------|
|                    |           |                              |      |       |
| Insert Arrangement | 32-6      | 32-7                         | 32-9 | 32-13 |
| Service Rating     | A         | A, B, h, j = Inst.; Bal. = A | D    | D     |
| Number of Contacts | 2 3 2 16  | 7 28                         | 2 12 | 5 18  |
| Contact Size       | 4 8 12 16 | 12 16                        | 4 16 | 12 16 |

|                    |       |           |       |                 |
|--------------------|-------|-----------|-------|-----------------|
|                    |       |           |       |                 |
| Insert Arrangement | 32-15 | 32-16     | 32-17 | 32-19*          |
| Service Rating     | D     | A         | D     | A = E, Bal. = D |
| Number of Contacts | 2 6   | 2 3 2 16  | 4     | 2 3             |
| Contact Size       | 0 12  | 4 8 12 16 | 4     | 0 12            |

\* Consult Amphenol, Sidney, NY for availability.

CONTACT LEGEND

⊕

●

⦿

○

⊗

16

12


8

4


0

# MS/Standard contact arrangements

front face of pin insert or rear face of socket insert illustrated














\* Consult Amphenol, Sidney, NY for availability.



# MS/Standard contact arrangements

front face of pin insert or rear face of socket insert illustrated

|                    |                                                                                     |                                                                                     |                                                                                       |                                                                                      |
|--------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|
|                    |    |    |     |   |
|                    | 110° Rotation<br>of 36-10                                                           |                                                                                     | 100° Rotation<br>of 36-7                                                              | 110° Rotation<br>of 36-7                                                             |
| Insert Arrangement | 36-12                                                                               | 36-15                                                                               | 36-16                                                                                 | 36-17                                                                                |
| Service Rating     | A                                                                                   | M = D, Bal. = A                                                                     | A                                                                                     | A                                                                                    |
| Number of Contacts | 48                                                                                  | 35                                                                                  | 7 40                                                                                  | 7 40                                                                                 |
| Contact Size       | 16                                                                                  | 16                                                                                  | 12 16                                                                                 | 12 16                                                                                |
|                    |   |   |    |  |
|                    | 100° Rotation<br>of 36-9                                                            | 260° Rotation<br>of 36-9                                                            |                                                                                       |                                                                                      |
| Insert Arrangement | 36-18                                                                               | 36-21                                                                               | 36-52                                                                                 | 36-66*                                                                               |
| Service Rating     | A                                                                                   | A                                                                                   | A                                                                                     | A                                                                                    |
| Number of Contacts | 1 2 14 14                                                                           | 1 2 14 14                                                                           | 52                                                                                    | 4 52                                                                                 |
| Contact Size       | 4 8 12 16                                                                           | 4 8 12 16                                                                           | 16                                                                                    | 12 16                                                                                |
|                    |  |  |  |                                                                                      |
| Insert Arrangement | 40-1                                                                                | 40-2*                                                                               | 40-3*                                                                                 |                                                                                      |
| Service Rating     | D                                                                                   | D                                                                                   | D                                                                                     |                                                                                      |
| Number of Contacts | 6 24                                                                                | 23                                                                                  | 1 4 18                                                                                |                                                                                      |
| Contact Size       | 12 16                                                                               | 16                                                                                  | 4 12 16                                                                               |                                                                                      |

\* Consult Amphenol, Sidney, NY for availability.

CONTACT LEGEND

⊕

⬤

⦿

○

⊗

16

12

8


4

0


# MS/Standard contact arrangements

front face of pin insert or rear face of socket insert illustrated


Insert Arrangement  
Service Rating  
Number of Contacts  
Contact Size




**40-4\***  
**D**  
**2 3 2 16**  
**4 8 12 16**



**40-5\***  
**A**  
**3 2 4 6**  
**0 4 8 12**




**40-6\***  
**D**  
**1 1 24**  
**0 12 16**




Insert Arrangement  
Service Rating  
Number of Contacts  
Contact Size


**40-7\***  
**P, Q, U, V, W, X = A; Bal. = D**  
**2 2 18**  
**0 12 16**



**40-9**  
**A**  
**1 22 24**  
**8 12 16**




**40-10\***  
**A**  
**4 9 16**  
**4 8 16**




Insert Arrangement  
Service Rating  
Number of Contacts  
Contact Size

**40-11\***  
**D**  
**1 1 1 4 18**  
**0 4 8 12 16**



**40-56\***  
**A**  
**85**  
**16**



**40-62\***  
**A**  
**60**  
**16**

\* Consult Amphenol, Sidney, NY for availability.

CONTACT LEGEND

⊕

⦿

⦿

○

⊗

16

12

8

4

0

# MS/Standard

## contact information, sealing plugs, crimping and insertion/removal tools

### MS/STANDARD CRIMP REAR RELEASE CONTACTS

| Contact Size | Wire Range |                 | Socket Contacts      |                             | Pin Contacts         |                             |
|--------------|------------|-----------------|----------------------|-----------------------------|----------------------|-----------------------------|
|              | AWG        | mm <sup>2</sup> | Military Part Number | Amphenol/Matrix Part Number | Military Part Number | Amphenol/Matrix Part Number |
| 16S*         | 20–16      | 0.5–1.4         | M39029/30-217        | M5100-033-1601L             | M39029/29-212        | M5000-029-0016L             |
| 16           | 20–16      | 0.5–1.4         | M39029/30-218        | M5100-033-1602L             | M39029/29-212        | M5000-029-0016L             |
| 12           | 14–12      | 2–3             | M39029/30-219        | M5100-033-0012              | M39029/29-213        | M5000-029-0012              |
| 8            | 10–8†      | 5–8.5           | M39029/30-220        | M5100-033-0008              | M39029/29-214        | M5000-029-0008              |
| 4            | 6–4†       | 13–21           | M39029/30-221        | M5100-033-0004              | M39029/29-215        | M5000-029-0004              |
| 0            | 2–0†       | 34–60           | M39029/30-222        | M5100-033-0000              | M39029/29-216        | M5000-029-0000              |

\* Shorter wire barrel

Note: For information on thermocouple contacts, consult Amphenol, Sidney, NY.

† Use MS3348 bushing kit to accommodate smaller wire.

### CONTACT CURRENT RATING AND RETENTION

| Contact Size** | Current Rating |                         | Contact Retention |       |
|----------------|----------------|-------------------------|-------------------|-------|
|                | Amperes Max.   | Voltage Crop Millivolts | Axial Load        |       |
|                |                |                         | lb.               | N     |
| 16             | 13             | 50                      | 25                | 111.2 |
| 12             | 23             | 50                      | 30                | 133.4 |
| 8              | 46             | 25                      | 50                | 222.4 |
| 4              | 80             | 14                      | 60                | 266.9 |
| 0              | 150            | 12                      | 75                | 333.6 |

\*\* Organize individual circuits to maintain heat rise within operating temperature requirements.

### SEALING PLUGS

| Contact Size | Sealing Plugs        |                             |
|--------------|----------------------|-----------------------------|
|              | Military Part Number | Amphenol/Matrix Part Number |
| 16S          | MS27488-16-1         | 10-405996-161               |
| 16           | MS27488-16-1         | 10-405996-161               |
| 12           | MS27488-12-1         | 10-405996-121               |
| 8            | MS27488-8-1          | 10-405996-081               |
| 4            | MS27488-4-1          | 10-405996-041               |
| 0            | MS27488-0-1          | 10-405996-001               |

### CRIMPING TOOLS

| Contact Size | Wire Range |                 | Finished Wire Dia. Range |            | Color Code  | Crimping Tool Part Number | Turret or Positioner Part Number |
|--------------|------------|-----------------|--------------------------|------------|-------------|---------------------------|----------------------------------|
|              | AWG        | mm <sup>2</sup> | Inch                     | mm         |             |                           |                                  |
| 16S          | 20–16      | 0.5–1.4         | .053–.103                | 1.34–2.62  | Red/White   | M22520/1-01               | M22520/1-02                      |
| 16           | 20–16      | 0.5–1.4         | .053–.103                | 1.34–2.62  | Blue/White  | M22520/1-01               | M22520/1-02                      |
| 12           | 14–12      | 2–3             | .085–.158                | 2.15–4.01  | Yell./White | M22520/1-01               | M22520/1-02                      |
| 8            | 10–8       | 5–8.5           | .132–.255                | 3.35–6.48  | White/Red   | M22520/23-01              | M22520/23-02                     |
| 4            | 6–4        | 13–21           | .237–.370                | 6.01–9.40  | White/Blue  | M22520/23-01              | M22520/23-04                     |
| 0            | 2–0        | 34–60           | .360–.550                | 9.14–13.97 | White/Yell. | M22520/23-01              | M22520/23-05                     |

### INSERTION/REMOVAL TOOLS

| Contact Size | Color Code  | Military Part Number | Amphenol/Matrix Part Number |
|--------------|-------------|----------------------|-----------------------------|
| 16           | Blue/White  | M81969/14-03         | 10-538988-016               |
| 12           | Yell./White | M81969/14-04         | 10-538988-012               |
| 8            | White/Red   | M81969/14-06         | 6500-018-0008               |
| 4            | White/Blue  | M81969/14-07         | 6500-018-0004               |
| 0            | White/Yell. | M81969/14-08         | 6500-018-0000               |

Amphenol installation instructions, L-2106, gives information on insertion, removal and crimping of contacts for Matrix MIL-DTL-5015 connectors.

# MS/Standard Accessories

## protection caps – plug

### PLUG PROTECTION CAP 10-329391-XX\*



| Assembly Number | A Thread Class 2A | B Dia. +.010<br>-.000 | C Approx. | L Max. |
|-----------------|-------------------|-----------------------|-----------|--------|
| 10-329391-10    | .625-24UNEF       | .516                  | 3.5       | 1.312  |
| 10-329391-11    | .625-24UNEF       | .641                  | 3.5       | 1.312  |
| 10-329391-12    | .750-20UNEF       | .641                  | 3.5       | 1.500  |
| 10-329391-14    | .875-20UNEF       | .766                  | 3.5       | 1.500  |
| 10-329391-16    | 1.000-20UNEF      | .891                  | 3.5       | 1.500  |
| 10-329391-18    | 1.125-18UNEF      | 1.016                 | 3.5       | 1.500  |
| 10-329391-20    | 1.250-18UNEF      | 1.141                 | 4.0       | 1.500  |
| 10-329391-22    | 1.375-18UNEF      | 1.266                 | 4.0       | 1.500  |
| 10-329391-24    | 1.500-18UNEF      | 1.391                 | 4.5       | 1.500  |
| 10-329391-28    | 1.750-18UNS       | 1.641                 | 4.5       | 1.500  |
| 10-329391-32    | 2.000-18UNS       | 1.891                 | 5.0       | 1.500  |
| 10-329391-36    | 2.250-16UN        | 2.078                 | 5.0       | 1.500  |
| 10-329391-40    | 2.500-16UN        | 2.328                 | 5.0       | 1.500  |
| 10-329391-44    | 2.750-16UN        | 2.641                 | 6.0       | 1.500  |

### PLUG PROTECTION CAP 10-229125-XX\*



| Assembly Number | A Thread Class 2A | C Approx. | D Ref. | L Max. |
|-----------------|-------------------|-----------|--------|--------|
| 10-229125-10    | .625-24NEF        | 3.0       | .140   | 1.233  |
| 10-229125-12    | .750-20UNEF       | 3.5       | .140   | 1.421  |
| 10-229125-14    | .875-20UNEF       | 3.5       | .140   | 1.421  |
| 10-229125-16    | 1.000-20UNEF      | 3.5       | .140   | 1.421  |
| 10-229125-18    | 1.125-18NEF       | 3.5       | .140   | 1.421  |
| 10-229125-20    | 1.250-18NEF       | 3.5       | .193   | 1.421  |
| 10-229125-22    | 1.375-18NEF       | 3.5       | .193   | 1.421  |
| 10-229125-24    | 1.500-18NEF       | 4.5       | .193   | 1.421  |
| 10-229125-28    | 1.750-18NS        | 4.5       | .193   | 1.421  |
| 10-229125-32    | 2.000-18NS        | 5.0       | .193   | 1.421  |
| 10-229125-36    | 2.250-16UN        | 5.0       | .193   | 1.421  |
| 10-229125-40    | 2.500-16UN        | 5.0       | .193   | 1.421  |

### PLUG PROTECTION CAP MS25042-XXDA\*



| MS Number    | A Thread Class 2A | B Dia. +.010<br>-.005 | C Approx. | L Max. |
|--------------|-------------------|-----------------------|-----------|--------|
| MS25042-8DA  | .500-28UNEF       | .156                  | 4.00      | .969   |
| MS25042-10DA | .625-24UNEF       | .156                  | 4.00      | .969   |
| MS25042-12DA | .750-20UNEF       | .156                  | 4.50      | 1.156  |
| MS25042-14DA | .875-20UNEF       | .156                  | 4.50      | 1.156  |
| MS25042-16DA | 1.000-20UNEF      | .156                  | 4.50      | 1.156  |
| MS25042-18DA | 1.125-18UNEF      | .156                  | 4.50      | 1.156  |
| MS25042-20DA | 1.250-18UNEF      | .187                  | 5.00      | 1.156  |
| MS25042-22DA | 1.375-18UNEF      | .187                  | 5.00      | 1.156  |
| MS25042-24DA | 1.500-18UNEF      | .187                  | 5.50      | 1.156  |
| MS25042-28DA | 1.750-18UNS       | .187                  | 7.75      | 1.156  |
| MS25042-32DA | 2.000-18UNS       | .218                  | 7.75      | 1.156  |
| MS25042-36DA | 2.250-16UN        | .218                  | 7.75      | 1.156  |
| MS25042-40DA | 2.500-16UN        | .218                  | 7.75      | 1.156  |

\* Protective caps are illustrated with sash chains and are available with beaded chains or without chains. Optional terminations are also available. Consult Amphenol, Sidney, NY when ordering.

# MS/Standard Accessories


## protection caps – receptacle

### RECEPTACLE PROTECTION CAP 10-329392-XX\*



| Assembly Number | A Thread Class 2B | B Dia. Min. | C Approx. | D Dia. Max. | L Max. |
|-----------------|-------------------|-------------|-----------|-------------|--------|
| 10-329392-10    | .625-24UNEF       | .516        | 3.5       | .875        | .793   |
| 10-329392-12    | .750-20UNEF       | .641        | 3.5       | 1.000       | .793   |
| 10-329392-14    | .875-20UNEF       | .766        | 3.5       | 1.125       | .793   |
| 10-329392-16    | 1.000-20UNEF      | .891        | 3.5       | 1.250       | .793   |
| 10-329392-18    | 1.125-18UNEF      | 1.016       | 3.5       | 1.375       | 1.024  |
| 10-329392-20    | 1.250-18UNEF      | 1.141       | 4.0       | 1.500       | 1.024  |
| 10-329392-22    | 1.375-18UNEF      | 1.266       | 4.0       | 1.625       | 1.024  |
| 10-329392-24    | 1.500-18UNEF      | 1.391       | 4.5       | 1.750       | 1.024  |
| 10-329392-28    | 1.750-18UNS       | 1.641       | 4.5       | 2.000       | 1.024  |
| 10-329392-32    | 2.000-18UNS       | 1.891       | 5.0       | 2.250       | 1.024  |
| 10-329392-36    | 2.250-16UN        | 2.078       | 5.0       | 2.500       | 1.024  |
| 10-329392-40    | 2.500-16UN        | 2.328       | 5.0       | 2.656       | 1.024  |
| 10-329392-44    | 2.750-16UN        | 2.641       | 6.0       | 2.938       | 1.024  |

### RECEPTACLE PROTECTION CAP 10-422905-XXX\*



| Assembly Number | A Thread Class 2B | B Ref. | C Approx. | D Dia. Max. | L Max. |
|-----------------|-------------------|--------|-----------|-------------|--------|
| 10-422905-103   | .625-24UNEF       | .140   | 3.0       | .875        | .812   |
| 10-422905-123   | .750-20UNEF       | .140   | 3.5       | 1.000       | .812   |
| 10-422905-143   | .875-20UNEF       | .140   | 3.5       | 1.125       | .812   |
| 10-422905-163   | 1.000-20UNEF      | .140   | 3.5       | 1.250       | .812   |
| 10-422905-183   | 1.125-18UNEF      | .193   | 3.5       | 1.375       | 1.031  |
| 10-422905-203   | 1.250-18UNEF      | .193   | 4.0       | 1.500       | 1.031  |
| 10-422905-223   | 1.375-18UNEF      | .193   | 4.0       | 1.625       | 1.031  |
| 10-422905-243   | 1.500-18UNEF      | .193   | 4.5       | 1.750       | 1.031  |
| 10-422905-283   | 1.750-18UNS       | .193   | 4.5       | 2.000       | 1.031  |
| 10-422905-323   | 2.000-18UNS       | .193   | 5.0       | 2.250       | 1.031  |
| 10-422905-363   | 2.250-16UN        | .193   | 5.0       | 2.500       | 1.031  |
| 10-422905-403   | 2.500-16UN        | .193   | 5.0       | 2.656       | 1.031  |

### RECEPTACLE PROTECTION CAP MS25043-XXDA\*



| MS Number    | A Thread Class 2B | B +.010<br>-.005 | C Approx. | D Dia. Max. | L Max. |
|--------------|-------------------|------------------|-----------|-------------|--------|
| MS25043-8DA  | .500-28UNEF       | .140             | 4.00      | .688        | .750   |
| MS25043-10DA | .625-24UNEF       | .140             | 4.00      | .815        | .750   |
| MS25043-12DA | .750-20UNEF       | .140             | 4.50      | 1.000       | .750   |
| MS25043-14DA | .875-20UNEF       | .140             | 4.50      | 1.125       | .750   |
| MS25043-16DA | 1.000-20UNEF      | .140             | 4.50      | 1.188       | .750   |
| MS25043-18DA | 1.125-18UNEF      | .140             | 4.50      | 1.344       | .750   |
| MS25043-20DA | 1.250-18UNEF      | .140             | 5.00      | 1.469       | .750   |
| MS25043-22DA | 1.375-18UNEF      | .140             | 5.00      | 1.594       | .750   |
| MS25043-24DA | 1.500-18UNEF      | .171             | 5.50      | 1.719       | .750   |
| MS25043-28DA | 1.750-18UNS       | .171             | 7.75      | 1.969       | .812   |
| MS25043-32DA | 2.000-18UNS       | .187             | 7.75      | 2.219       | .812   |
| MS25043-36DA | 2.250-16UN        | .187             | 7.75      | 2.469       | .812   |
| MS25043-40DA | 2.500-16UN        | .187             | 7.75      | 2.719       | .812   |

\* Protective caps are illustrated with sash chains and are available with beaded chains or without chains. Optional terminations are also available. Consult Amphenol, Sidney, NY when ordering.

# MS/Standard Accessories

## dust caps

### 10-70500 RECEPTACLE DUST CAP

for external threads



| MS Shell Size | Order Number | A Dia. Nominal Thread | C Dia. $\pm.031$ | L¹ $\pm.062$ |
|---------------|--------------|-----------------------|------------------|--------------|
| 8S            | 10-70500-8   | .500                  | .750             | .500         |
| 10S           | 10-70500-10  | .625                  | .875             | .500         |
| 10SL          | 10-70500-10  | .625                  | .875             | .500         |
| 12S           | 10-70500-12  | .750                  | 1.000            | .500         |
| 12            | 10-70500-12  | .750                  | 1.000            | .500         |
| 14S           | 10-70500-14  | .875                  | 1.125            | .500         |
| 14            | 10-70500-14  | .875                  | 1.125            | .500         |
| 16S           | 10-70500-16  | 1.000                 | 1.250            | .500         |
| 16            | 10-70500-16  | 1.000                 | 1.250            | .500         |
| 18            | 10-70500-18  | 1.125                 | 1.375            | .562         |
| 20            | 10-70500-20  | 1.250                 | 1.500            | .562         |
| 22            | 10-70500-22  | 1.375                 | 1.625            | .562         |
| 24            | 10-70500-24  | 1.500                 | 1.750            | .562         |
| 28            | 10-70500-28  | 1.750                 | 1.938            | .562         |
| 32            | 10-70500-32  | 2.000                 | 2.250            | .562         |
| 36            | 10-70500-36  | 2.250                 | 2.500            | .625         |
| 40            | 10-70500-40  | 2.500                 | 2.750            | .625         |

### 10-70506 PLUG DUST CAP

for internal threads



| MS Shell Size | Order Number | B Dia. Min. | L² $\pm.125$ |
|---------------|--------------|-------------|--------------|
| 8S            | 10-70506-8S  | .469        | .625         |
| 10S           | 10-70506-10S | .587        | .625         |
| 10SL          | 10-70506-10S | .587        | .625         |
| 12S           | 10-70506-12  | .704        | .625         |
| 12            | 10-70506-12  | .704        | .625         |
| 14S           | 10-70506-14  | .828        | .625         |
| 14            | 10-70506-14  | .828        | .625         |
| 16S           | 10-70506-16  | .953        | .625         |
| 16            | 10-70506-16  | .953        | .625         |
| 18            | 10-70506-18  | 1.072       | .625         |
| 20            | 10-70506-20  | 1.197       | .625         |
| 22            | 10-70506-22  | 1.322       | .625         |
| 24            | 10-70506-24  | 1.447       | .625         |
| 28            | 10-70506-28  | 1.697       | .625         |
| 32            | 10-70506-32  | 1.947       | .625         |
| 36            | 10-70506-36  | 2.190       | .625         |
| 40            | 10-70506-40  | 2.440       | .625         |

# MS/Standard how to order

## HOW TO ORDER BY MILITARY PART NUMBER MIL-DTL-5015 CONNECTORS WITH REAR RELEASE CRIMP CONTACTS

|           |             |          |            |          |          |          |          |
|-----------|-------------|----------|------------|----------|----------|----------|----------|
| <u>MS</u> | <u>3456</u> | <u>L</u> | <u>16S</u> | <u>–</u> | <u>8</u> | <u>P</u> | <u>W</u> |
| <u>1</u>  | <u>2</u>    | <u>3</u> | <u>4</u>   | <u>5</u> | <u>6</u> | <u>7</u> |          |

1. Connector Type  
MS designates Military Standard
2. Connector Style  
THREADED COUPLING CONNECTORS  
3450 wall mounting receptacle  
3451 cable connecting receptacle  
3452 box mounting receptacle  
3454 jam nut receptacle  
3456 straight plug  
3459 straight plug with self-locking coupling nut
3. Service Class  
L aluminum shell, electroless nickel finish, fluid resistant insert  
W aluminum shell, cadmium olive drab finish, fluid resistant insert  
LS stainless steel shell, passivated, fluid resistant insert  
KT firewall, steel shell, cadmium olive drab finish, non-flammable hard dielectric and fluid resistant insert  
KS firewall, stainless steel shell, passivated, non-flammable hard dielectric and fluid resistant insert  
  
Note: Class L inactivates older Class U.  
Class K is inactive and has been replaced by Class KT for all applications.
- 4., 5. Shell size and insert arrangement - See tables on pages 11 and 12 and pattern drawings that follow.
6. Contact Types  
P designates pin  
S designates socket  
A designates less pins  
B designates less sockets  
  
Note: Use A & B only when other than a full complement of power contacts is to be installed.
7. Insert Rotation  
“W”, “X”, “Y”, “Z” designate that insert is rotated in its shell from normal position. No letter required for normal (no rotation) position. See page 13 for description of alternate positions.

## HOW TO ORDER BY PROPRIETARY PART NUMBER MIL-DTL-5015 CONNECTORS WITH REAR RELEASE CRIMP CONTACTS

|            |          |          |            |          |          |          |          |            |
|------------|----------|----------|------------|----------|----------|----------|----------|------------|
| <u>944</u> | <u>6</u> | <u>F</u> | <u>16S</u> | <u>–</u> | <u>8</u> | <u>P</u> | <u>W</u> | <u>***</u> |
| <u>1</u>   | <u>2</u> | <u>3</u> | <u>4</u>   | <u>5</u> | <u>6</u> | <u>7</u> | <u>8</u> |            |

1. Connector Type  
944 designates Amphenol®/Matrix® Series Number
2. Connector Style  
THREADED COUPLING CONNECTORS  
9440 wall mounting receptacle  
9441 cable connecting receptacle  
9442 box mounting receptacle  
9444 jam nut receptacle  
9446 straight plug  
9816 straight plug with self-locking coupling nut  
9817 quick disconnect plug with lanyard  
9818 quick disconnect plug without lanyard
3. Service Class  
A aluminum shell, black anodize finish, fluid resistant insert (not MIL-Spec)  
F aluminum shell, electroless nickel finish, fluid resistant insert  
W aluminum shell, cadmium olive drab finish, fluid resistant insert  
FS stainless steel shell, passivated, fluid resistant insert  
RS fluid resistant insert  
KT firewall, steel shell, cadmium/olive drab finish, non-flammable hard dielectric and fluid resistant insert  
KS firewall, stainless steel shell, passivated, non-flammable hard dielectric and fluid resistant insert
- 4., 5. Shell size and insert arrangement - See tables on pages 11 and 12 and pattern drawings that follow.
6. Contact Types  
P designates pin  
S designates socket
7. Insert Rotation  
“W”, “X”, “Y”, “Z” designate that insert is rotated in its shell from normal position. No letter required for normal (no rotation) position. See page 13 for description of alternate positions.
8. Modification Number  
Consult Amphenol, Sidney, NY for information.  
For strain reliefs use the following modification codes:  
(189) E-nut M85049/31 configuration  
(190) Straight strain relief M85049/52 configuration  
(191) 90° strain relief M85049/51 configuration

# Additional MS/Standard Connectors offered by Amphenol



**MS/Standard 3100 Series, MIL-5015 Type Connectors**

## **MIL-DTL-5015 and MIL-5015 Type Standard Cylindrical Connectors with solder or crimp (non-rear release) contacts**

Amphenol has long been the accepted leader in providing MS/Standard MIL-5015 type connectors. These connectors represent well-proven electrical capability at an economical cost for most equipment where durability is important.

The MS/Standard family of connectors (3100 Series) is a very broad range of product with the following features:

- medium to heavy weight cylindrical with resilient inserts
- environmental resistant
- threaded couplings, single key/keyway shell polarization
- operating voltage to 3000 VAC (RMS) at sea level
- 5 shell styles, 19 shell sizes, 280 contact arrangements
- solder or crimp contacts (non-rear-release type), sizes 16–0 accepting 22–0 AWG
- coaxial or thermocouple contact options
- alternate insert positioning
- hermetic configurations available
- zinc alloy plating (cadmium-free) available

The 3100 Series has five classes of connectors to meet different requirements. Within these connector styles, MIL-C-5015 has been replaced as follows: Environmental classes F and R are updated to and produced in strict accordance to MIL-DTL-5015. Classes A, C and E are still produced, but are no longer listed on the qualified products listing (QPL).

Class designations and brief descriptions are as follows:

- A – Solid Shell – for general, non-environmental applications.
- C – Pressurized – for use on pressurized bulkheads or pressure barriers; limits air leakage regardless of type and class of plug mated with them.
- E/F – Environmental Resisting with Strain Relief – designed for applications where the connector will be exposed to moisture, vibration, and rapid changes in pressure and temperature.
- R – Lightweight Environmental Resisting – shorter in length, lighter in weight than the E & F classes, the MS-R offers a high degree of reliability under adverse conditions: recommended for new design applications.

Ask for Amphenol catalog 12-020 which gives detailed information on this family of connectors.

## **MIL-5015 Modifications**

In order to supplement standard MS shell styles and provide a greater variety of styles for the electrical connector user, there are several MS and MS Modified cylindrical connectors offered by Amphenol. These types include flange mount plugs, thru bulkhead receptacles, jam nut receptacles, connectors for potting and connectors designed specifically to terminate jacketed cable.

Ask for Amphenol catalog 12-021 for detailed information.

## **97 Series, MIL-5015 Type Connectors**

The low cost, general duty connector used extensively in the machine tool industry, welding industry and numerous other industrial applications, is the Amphenol® 97 Series. Offered in non-environmental styles, these connectors have hard dielectric inserts and threaded coupling. They are Underwriters Laboratories Recognized and Canadian Standards Association Certified.

Recent addition to this family is the 97E environmental styles, still an economical choice. The 97E can be used in a variety of industrial applications where environmental sealing is required, such as automotive and robotics.

Ask for Amphenol catalog 12-022 for detailed information.



**97 Series, MIL-5015 Type Connectors**