











APPLICABLE P.C.B DIMENSION (REF.)
適合基板寸法 (参考)

NOTE 1. COPLANARITY OF SMT TERMINAL SHALL BE 0.1 MAXIMUM.
NOTE 2. MATING DIMENSIONS CONSIST OF
"Universal Serial Bus Type-C Cable and Connector Specification Revision 1.1"
NOTE 3. THE SHELL LENGTH IS LESS THAN THE MINIMUM SPECIFIED BY THE USB TYPE C STANDARD.
AS SUCH IT CANNOT INDEPENDENTLY BE GUARANTEED TO MEET ALL TYPE C MECHANICAL REQUIREMENTS.
REFERENCE THE USB TYPE C SPECIFICATION RELEASE 1.1, SECTION 3.2.1, NOTE 7.
NOTE 4. VACUUM AREA.
NOTE 5. LOT NO. IS MARKED AS SHOWN IN BELOW FIGURE MARKING.
(EX.) 5 Y 0 3
-5 :MANUFACTURE YEAR. (LAST 1 DIGIT OF A.D.)
-Y :MANUFACTURE MONTH. (JAN. TO SEP. :1 TO 9, OCT. :0, NOV. :X, DEC. :Y)
-03:MANUFACTURE DAY. (1 TO 31)

TABLE1. PIN ASSIGNMENT (FRONT VIEW)

Pin No.	A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
	GND	TX1+	TX1-	V _{BUS}	CC1	D+	D-	SBU1	V _{BUS}	RX2-	RX2+	GND
Pin No.	B12	RX1+	RX1-	V _{BUS}	SBU2	D-	D+	CC2	V _{BUS}	TX2-	TX2+	GND
	GND	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1

8	CAP	1	THERMOPLASTIC RESIN	COLOR:BLACK	
7	GND PLATE	2	STAINLESS STEEL	NICKEL PLATING	
6	MID PLATE 2	1	STAINLESS STEEL	NICKEL PLATING	
5	MID PLATE 1	1	STAINLESS STEEL	NICKEL PLATING	
4	SHELL	1	STAINLESS STEEL	NICKEL PLATING	
3	INSULATOR 2	2	THERMOPLASTIC RESIN	COLOR:BLACK	
2	INSULATOR 1	1	THERMOPLASTIC RESIN	COLOR:BLACK	
1	CONTACT	24	COPPER ALLOY	CONTACT AREA NICKEL: $2\mu\text{m}$ MIN. PALLADIUM-NICKEL: $0.75\mu\text{m}$ MIN. GOLD FLASH: $0.05\mu\text{m}$ MIN. SOLDER TAILS: NICKEL: $2\mu\text{m}$ MIN. GOLD FLASH: $0.03\mu\text{m}$ MIN.	
符号	名 称 DESCRIPTION	个 数 QTY	材 料 MATERIAL	仕 工 FINISH	備 考 REMARKS

NO.	DESCRIPTION	QTY.	MATERIAL	FINISH	REMARKS	
仕様書 (SPECIFICATION) JACS-30368※		第1版 (ORIGINAL DATE) 20/JAN/2016		尺度 (SCALE) 5:1	シリーズ (SERIES) DX07	日本航空電子工業株式会社
一般公差 (GENERAL TOLERANCE)		製図 DR.		名称 (TITLE) DX07S024WJ1	 JAPAN AVIATION ELECTRONICS INDUSTRY, LTD.	SIZE A2
寸法 (DIMENSION)		担当 CHK. S. YAMAGUCHI				
角度 (ANGLES)		套開 APPD. M. SASAKI				
±0.8 × ±0.4 ×× ±0.1 ××××		承認 APPD. T. MASUMOTO				
単位 (UNIT) : mm						
				質量 (MASS)	図面番号 (DRAWING NO.) SJ117219	版数 (VER.) 1
						