

JMGSCD - 6PW Product Details

Share

Print

Email



JMGSCD - 6PW
(1 - 1617150 - 9)

TE Internal Number: 1 - 1617150 - 9

Active

Military/Aerospace High Performance Relays

[Not EU RoHS or ELV Compliant](#)

Product Highlights:

- ?

MGSD .100 Grid Relay Series
- ?

Input Voltage = 6 VDC
- ?

Contact Arrangement = 2 Form C, DPDT, 2 C/O
- ?

Contact - Rated Current = 1 A
- ?

Non Polarized, Monostable Coil - Magnetic System

[View all Features](#)

Quick Links

- ?

[Check Pricing & Availability](#)
- ?

[Search for Tooling](#)
- ?

[Product Feature Selector](#)
- ?

[Contact Us About This Product](#)

Documentation & Additional Information	
Product Drawings: ? None Available Catalog Pages/Data Sheets: ? RELAY (PDF, English) Product Specifications: ? None Available Application Specifications: ? None Available Instruction Sheets: ? None Available CAD Files: ? None Available	Additional Information: ? Product Line Information Related Products: ? Tooling
List all Documents	

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: ? Series = MGSD .100 Grid Relay ? Termination Type = Long Leads Electrical Characteristics: ? Input Voltage (VDC) = 6 ? Contact - Rated Current (A) = 1 ? Coil Polarity Protection Diode = Without ? Transistor Driver = Without ? Coil Resistance (?) = 200 ? MOSFET Driver = Without ? Coil Power Measurement = Milliwatts ? Coil - Rated Power (mW) = 180 ? Actuating System = DC ? Shock = 75 G's, 6ms ? Vibration = 30G's, 10 to 3000Hz Contact Features: ? Mounting Options = PC Board ? Enclosure Type = Hermetically Sealed ? Pin Configuration = .175" Dia. Mounting Pad	Configuration Features: ? Contact Arrangement = 2 Form C, DPDT, 2 C/O ? Coil - Magnetic System = Non Polarized, Monostable ? Coil Suppression Diode = With Industry Standards: ? Government/Industry Qualification = Yes ? Government/Industry Part Number = M39016/42 -050P ? RoHS/ELV Compliance = Not ELV/RoHS compliant ? Lead Free Solder Processes = Not suitable for lead free processing ? Approved Standards = M39016 Qualified, P Level Conditions for Usage: ? Temperature Range (°C) = -65 – +125 Other: ? Brand = CII

Contact Features:

?

Mounting Options = PC Board

?

Enclosure Type = Hermetically Sealed

?

Pin Configuration = .175" Dia. Mounting Pad

Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

