

The miniature ECX-16 is a very compact SMD Tuning Fork Crystal. Low ESR part recommended by STMicroelectronics for the STM32 Microcontrollers.

ECX-16

32.768 KHz

SMD Tuning Fork Crystal

[Request a Sample](#)

ECX-16 SMD CRYSTAL



- Low Power RTC Applications such as STM32 [AN2867](#)
- 1.6 x 1.0 mm Footprint
- Extended Temp. Range
- RoHS Compliant
- Applications: Automotive, COTS, Industrial, IOT

DIMENSIONS (mm)




Figure 1) Top, Side, and Bottom views

OPERATING CONDITIONS / ELECTRICAL CHARACTERISTICS

PARAMETERS	CONDITIONS	ECX-16			UNITS
		MIN	TYP	MAX	
Frequency			32.768		KHz
Frequency Tolerance	@ +25°C			± 20 *	ppm
Load Capacitance	Specify in P/N		12.5		pF
Drive Level	DL			0.5	μW
Equivalent Series Resistance	R1			90K	Ω
Motional Capacitance			6.5		fF
Turnover Temperature		+20	+25	+30	°C
Temperature Coefficient		-0.02	-0.03	-0.040	ppm/°C ²
Shunt Capacitance	Co		1.3		pF
Aging (First Year)	@ +25°C ±3°C			±3	ppm
Operating Temperature	Topr	-40		+85	°C
Storage Temperature	Tstg	-55		+125	°C





Figure 2) Suggested Land Pattern


PAD CONNECTIONS

1	In/Out
2	Out/In

PART NUMBERING GUIDE: Example ECS-.327-12.5-16-TR

ECS - FREQUENCY ABBREVIATION		LOAD CAPACITANCE	PACKAGE	CUSTOM OPTIONS Tolerance	PACKAGING
ECS	.327 = 32.768 KHz	12.5 = 12.5 pF 9 = 9 pF 7 = 7 pF 5 = 5 pF	-16 = ECX-16	Blank = ±20 ppm * C = ± 10 ppm	TR = Tape & Reel

POCKET TAPE DIMENSIONS (mm)



A	B	C	D	F	J	L	M	Reel Dia.	Qty/Reel
1.85	1.25	8.0	3.5	4.0	0.5	0.25	0.65	180	5000

SOLDER PROFILE

Peak solder Temp +260°C Max 10 sec Max.

2 Cycles Max.

MSL 1, Lead Finish Au



Figure 1) Suggested Reflow Profile