

LOC	DIST	REVISIONS					
CM	53	P	LTR	DESCRIPTION	DATE	DWN	APVD
			C	REVISED PER ECR-13-007626	09AUG13	KH	TM

- 1
- MATES WITH APPROPRIATE UNIVERSAL MATE-N-LOK™ CAP OR HEADER.
- 2
- SMALL NICKS ARE PERMITTED ON THE CIRCUIT TOWERS WHICH COULD INCREASE THE INITIAL HOUSING MATING FORCE BY UP TO 4.4 NEWTONS (1.0 LBS). NO INDIVIDUAL NICKED TOWER SHALL INCREASE THIS FORCE BY OVER 2.2 NEWTONS (.5 LBS).
- 3
- DIMENSION INDICATED IS AS MOLDED. ADDITIONAL GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR.
- 4
- FOUR RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION. NO RIBS OR SIX RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION, OPTIONAL.
- 5
- UNDERWRITES RECOGNIZED COMPONENT LOGO AND CSA CERTIFICATION LOGO TO BE LOCATED ONCE EACH SIDE OF HOUSING.
- 6
- 150° C TEMPERATURE RATING FOR THIS HOUSING IS FOR SHORT TERM DURATION MAX OPERATING TEMPERATURE REMAINS 125° C.
- 7
- SPECIAL PACKAGING.
- 8
- PHOSPHOR BRONZE CONTACTS SHOULD ALWAYS BE USED WITH THIS HOUSING.
- 9
- SHOWN FOR CONVENIENCE, LOGO MAY BE ON ANY EXTERNAL SURFACE.





D

C

B

A

27.43	1.080
14.73	.580
13.97	.550
11.68	.460
7.62	.300
0.38	.015
0.13	.005
MM	IN
CONVERSION TABLE	



DETAIL A
OPTIONAL CONSTRUCTIONS

9	BLACK	8-794814-1
	BLACK	794814-1
	COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 15MAY01	TE Connectivity	
		CHK S. RIDGILL 15MAY01		
DIMENSIONS:		APVD S. RIDGILL 15MAY01	NAME	
mm		PRODUCT SPEC	PLUG, 2 CIRCUIT, UNIVERSAL MATE-N-LOK™	
		APPLICATION SPEC		
		WEIGHT	SIZE	RESTRICTED TO
MATERIAL NYLON, UL 94V-2, HIGH TEMP		FINISH -	A100779C794814	-
		CUSTOMER DRAWING		SCALE 4:1 SHEET 1 OF 1 REV C