











TOOL NUMBER  -1 7	WIRE SIZE mm ² [AWG] 	INSULATION DIAMETER mm [in.] 	INSUL. ADJ. 	FLIP LOCATOR 	STRIP LENGTH mm [in.] 	CRIMP HEIGHT mm [in.] 	CONTACT PART NUMBERS 		CONTACT DESCRIPTION	APPLIC. SPECIF.
							LOOSE PIECE 	STRIP FORM 		
91563-1 91563-3	0.20-0.56 [24-20]	1.50-2.20 [.059-.087]	YES	NO	4.0-4.5 [.157-.177]	0.98 ± 0.05 [.039 ± .002]	171699-[] 	171630-[] 	ECONOSEAL "J" II, .070 Series Contacts	114-5082
	0.20-0.56 [24-20]					1.02 ± 0.05 [.040 ± .002]	173600-[] 	171631-[] 		
91573-1 91573-3 	0.50-0.89 [20-18]	2.00-2.60 [.079-.102]	NO	NO	3.5-4.5 [.138-.177]	1.20-1.35 [.047-.053]	175027-[] 175030-[]	173631-[]  173645-[] 	.070 Series Contacts	114-5091 114-5092 114-5091-9 114-5092-9
	1.25-1.42 [16]					1.45-1.60 [.057-.063]				
91580-1 91580-3	0.20-0.22 [24]	1.20-1.50 [.047-.059]	NO	NO	3.5-4.5 [.138-.177]	1.00-1.10 [.039-.043]	175026-[] 175029-[]	173630-[]  173633-[] 	.070 Series Contacts	114-5091-9 114-5092-9
	0.30-0.35 [22]	1.20-1.60 [.047-.063]				1.05-1.18 [.041-.046]				
91583-1 91583-3	0.50-0.89 [20-18]	2.00-2.70 [.079-.106]	YES	NO	4.5-5.0 [.177-.197]	1.20-1.32 [.047-.0512]	173707-[] 	171662-[] 	ECONOSEAL "J" II, .070 Series Contacts	114-5082
	1.25-1.42 [16]					1.38-1.52 [.054-.060]				
91585-1 91585-3	0.50-0.89 [20-18]	2.00-2.70 [.079-.106]	YES	NO	4.5-5.0 [.177-.197]	1.20-1.32 [.047-.052]	173706-[] 	171661-[] 	ECONOSEAL "J" II, .070 Series Contacts	114-5082
	1.25-1.42 [16]					1.38-1.52 [.054-.060]				


 LIST OF APPLIED CONTACT PART NUMBERS MAY NOT BE COMPLETE AND IS SUBJECT TO CHANGE. FOR CURRENT INFORMATION ON TERMINAL PART NUMBERS, CONTACT THE TOOLING ASSISTANCE CENTER : 1-800-722-1111.

2. AMP, CERTI-CRIMP and ECONOSEAL ARE TRADEMARKS.

 TERMINAL MUST BE PRE-FORMED BEFORE IT CAN BE CRIMPED.

 .070 TYPE RUBBER PLUG 172746-[] OR 178210-[] IS USED WHEN CRIMPING THIS PRODUCT.

 .070 TYPE RUBBER PLUG 176886-[] OR 172888-[] IS USED WHEN CRIMPING THIS PRODUCT.




 POSITION CONTACT BETWEEN CRIMPS SO LOCATOR / INSULATION STOP ENTERS THE CONTACT. PUSH THE CONTACT TOWARD THE LOCATOR AS SHOWN IN FIGURE 1. HOLDING CONTACT IN PLACE, SQUEEZE TOOL HANDLES TOGETHER UNTIL INSULATION BARREL ANVIL STARTS ENTRY INTO INSULATION CRIMPER. DO NOT DEFORM INSULATION BARRREL OR WIRE BARREL AT THIS MOMENT.

 -1 IS A COMPLETE CERTICRIMP II HAND TOOL ASSEMBLY.
-3 IS A CERTICRIMP II HEAD SUB-ASSEMBLY.

8. THE HAND TOOL INSTRUCTION SHEET, ALSO KNOWN AS AN "IS", FOR MOST CERTI-CRIMP II TOOLS USE IS 408-8547. IF THE TOOL HAS A FLIP LOCATOR USE IS 408-10414.

CERTI-CRIMP II DATA SHEET

								OTHERWISE SPECIFIED:				B.A.WOLFE				22FEB2012				 TE Connectivity			
								mm				0 PLC ± -											
												1 PLC ± -											
												2 PLC ± -											
												3 PLC ± -											
												4 PLC ± -											
								ANGLES ± -								NAME							
																CERTI-CRIMP II TOOL DATA SHEET							
																ECONOSEAL J-11 & .070 SERIES CONTACTS							
P LTR				REVISION RECORD				DATE				DWN				APVD				SCALE			
																				SIZE			
																				DRAWING NO			
																				1583009			
																				SHEET			
																				1 OF 2			
																				REV			
																				B4			

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES (TE). IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TE PERSONNEL, WITHOUT AUTHORIZATION FROM TE (www.te.com).

LOC A
DIST 00

DWN	21FEB2012	MATERIAL	HEAT TREAT
M. YOUNGER		-	-
CHK	22FEB2012		-
B.A.WOLFE		 TE Connectivity	
APVD	22FEB2012		
B.A. WOLFE			
NAME			
CERTI-CRIMP II TOOL DATA SHEET ECONOSEAL J-1 & .070 SERIES CONTACTS			
SCALE	SIZE	DRAWING NO	SHEET
-	A1	1583009	2 of 2
			REV B4