




Wire Protection & Management > Interconnect Devices > Shielded Terminators



Compatible Cable Bundle Diameter (Max): 4.2 mm [.165 in]
Compatible Wire Bundle Diameter (Max): 4.2 mm [.165 in]
Interconnect Device Shield Cable Type: Multi-Conductors Unshielded, Single

Features

Product Type Features

Interconnect Device Shield Cable Type	Multi-Conductors Unshielded, Single
---------------------------------------	-------------------------------------

Body Features

Insert Type	Meltable Sealing Ring
-------------	-----------------------

Contact Features

Ferrule Plating Material	Electroless Nickel
--------------------------	--------------------

Dimensions

Compatible Cable Bundle Diameter (Max)	4.2 mm[.165 in]
Compatible Wire Bundle Diameter (Max)	4.2 mm[.165 in]

Usage Conditions

Salt Spray Resistance	500 Hr
Operating Temperature Range	-65 – 175 °C[-85 – 347 °F]

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量超出标准 Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250)



Candidate List Declared Against: JAN 2024
(240)
SVHC > Threshold:
Cd (3% in Plating)
Pb (.3% in Body)

Article Safe Usage Statements:
Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Out of Scope - excluded from Halogen requirements
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Also in the Series | RAYCHEM HET




Shielded Terminators(9)

Customers Also Bought


TE Part #ZPF00000000002027
182-0701-06



TE Part #ZPF00000000003607
724-0007-22



TE Part #878504-000
202K153-25-01-0



TE Part #5053144070
RNF-100-3/8-0-SP



TE Part #ZPF000000000002013
[182-0661-06](#)

TE Part #ZPF000000000003605
[724-0007-20](#)

TE Part #321045
[TERMINAL,PIDG R 16-14 1/4](#)

TE Part #327638
[SPLICE BUTT PIDG 12-10/16-14](#)

TE Part #1577620-1
[TERMINAL RT PIDG PEEK STRATO 24-22 AWG](#)

TE Part #A56594-000
[TMS-SCE-2X-1/4-S1-9](#)

Documents

Product Drawings

[HET-A-03B](#)

English

Datasheets & Catalog Pages

[Circular Backshells](#)

English

Product Specifications

[Ferrule and Heat-Shrinkable Sleeve for HET-A-03X and HET-A-3X-TAK on Unshielded Cable](#)

English