

SA5.0A Series

500 Watt Peak Power MiniMOSORB™ Zener Transient Voltage Suppressors

Unidirectional*

The SA5.0A series is designed to protect voltage sensitive components from high voltage, high energy transients. They have excellent clamping capability, high surge capability, low zener impedance and fast response time. The SA5.0A series is supplied in ON Semiconductor's exclusive, cost-effective, highly reliable Surmetic™ axial leaded package and is ideally-suited for use in communication systems, numerical controls, process controls, medical equipment, business machines, power supplies and many other industrial/consumer applications.

Specification Features:

- Working Peak Reverse Voltage Range – 5 to 170 V
- Peak Power – 500 Watts @ 1 ms
- ESD Rating of Class 3 (>16 KV) per Human Body Model
- Maximum Clamp Voltage @ Peak Pulse Current
- Low Leakage < 1 μ A above 8.5 V
- UL 497B for Isolated Loop Circuit Protection
- Maximum Temperature Coefficient Specified
- Response Time is typically < 1 ns

Mechanical Characteristics:

CASE: Void-free, Transfer-molded, Thermosetting plastic

FINISH: All external surfaces are corrosion resistant and leads are readily solderable

MAXIMUM LEAD TEMPERATURE FOR SOLDERING: 230°C,
1/16" from the case for 10 seconds

POLARITY: Cathode indicated by polarity band.

MOUNTING POSITION: Any

MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Peak Power Dissipation (Note 1) @ $T_L \leq 25^\circ\text{C}$	P_{PK}	500	Watts
Steady State Power Dissipation @ $T_L \leq 75^\circ\text{C}$, Lead Length = 3/8" Derated above $T_L = 75^\circ\text{C}$	P_D	3.0 30	Watts mW/°C
Thermal Resistance, Junction-to-Lead	$R_{\theta JL}$	33.3	°C/W
Forward Surge Current (Note 2) @ $T_A = 25^\circ\text{C}$	I_{FSM}	70	Amps
Operating and Storage Temperature Range	T_J, T_{stg}	- 55 to +175	°C




1. Nonrepetitive current pulse per Figure 4 and derated above $T_A = 25^\circ\text{C}$ per Figure 2.
2. 1/2 sine wave (or equivalent square wave), PW = 8.3 ms, duty cycle = 4 pulses per minute

*Please see SA5.0CA – SA170CA for Bidirectional devices.



ON Semiconductor®

<http://onsemi.com>



L = Assembly Location
SAxxxA = ON Device Code
YY = Year
WW = Work Week

ORDERING INFORMATION

Device	Package	Shipping
SAxxxA	Axial Lead	1000 Units/Box
SAxxxARL*	Axial Lead	5000/Tape & Reel


*SA8.0A, SA130A, and SA160A Not Available in 5000/Tape & Reel.

Devices listed in **bold, italic** are ON Semiconductor **Preferred** devices. **Preferred** devices are recommended choices for future use and best overall value.

SA5.0A Series

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted, $V_F = 3.5\text{ V Max. @ } I_F \text{ (Note 6) } = 35\text{ A}$)

Symbol	Parameter
I_{PP}	Maximum Reverse Peak Pulse Current
V_C	Clamping Voltage @ I_{PP}
V_{RWM}	Working Peak Reverse Voltage
I_R	Maximum Reverse Leakage Current @ V_{RWM}
V_{BR}	Breakdown Voltage @ I_T
I_T	Test Current
ΘV_{BR}	Maximum Temperature Variation of V_{BR}
I_F	Forward Current
V_F	Forward Voltage @ I_F



SA5.0A Series

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted, $V_F = 3.5\text{ V Max.}$ @ I_F (Note 6) = 35 A)

Device	Device Marking	V_{RWM} (Note 3)	I_R @ V_{RWM}	Breakdown Voltage				V_C @ I_{PP} (Note 5)		θV_{BR}
				V_{BR} (Note 4) (Volts)			@ I_T	V_C	I_{PP}	
		Volts	μA	Min	Nom	Max	mA	Volts	A	mV/ $^\circ\text{C}$
SA5.0A	SA5.0A	5	600	6.4	6.7	7	10	9.2	54.3	5
SA6.0A	SA6.0A	6	600	6.67	7.02	7.37	10	10.3	48.5	5
SA7.0A	SA7.0A	7	150	7.78	8.19	8.6	10	12	41.7	6
SA7.5A	SA7.5A	7.5	50	8.33	8.77	9.21	1	12.9	38.8	7
SA8.0A*	SA8.0A*	8	25	8.89	9.36	9.83	1	13.6	36.7	7
SA8.5A	SA8.5A	8.5	5	9.44	9.92	10.4	1	14.4	34.7	8
SA9.0A	SA9.0A	9	1	10	10.55	11.1	1	15.4	32.5	9
SA10A	SA10A	10	1	11.1	11.7	12.3	1	17	29.4	10
SA11A	SA11A	11	1	12.2	12.85	13.5	1	18.2	27.4	11
SA12A	SA12A	12	1	13.3	14	14.7	1	19.9	25.1	12
SA13A	SA13A	13	1	14.4	15.15	15.9	1	21.5	23.2	13
SA14A	SA14A	14	1	15.6	16.4	17.2	1	23.2	21.5	14
SA15A	SA15A	15	1	16.7	17.6	18.5	1	24.4	20.6	16
SA16A	SA16A	16	1	17.8	18.75	19.7	1	26	19.2	17
SA17A	SA17A	17	1	18.9	19.9	20.9	1	27.6	18.1	19
SA18A	SA18A	18	1	20	21.05	22.1	1	29.2	17.2	20
SA20A	SA20A	20	1	22.2	23.35	24.5	1	32.4	15.4	23
SA22A	SA22A	22	1	24.4	25.65	26.9	1	35.5	14.1	25
SA24A	SA24A	24	1	26.7	28.1	29.5	1	38.9	12.8	28
SA26A	SA26A	26	1	28.9	30.4	31.9	1	42.1	11.9	30
SA28A	SA28A	28	1	31.1	32.75	34.4	1	45.4	11	31
SA30A	SA30A	30	1	33.3	35.05	36.8	1	48.4	10.3	36
SA33A	SA33A	33	1	36.7	38.65	40.6	1	53.3	9.4	39
SA36A	SA36A	36	1	40	42.1	44.2	1	58.1	8.6	41
SA40A	SA40A	40	1	44.4	46.55	49.1	1	64.5	7.8	46
SA43A	SA43A	43	1	47.8	50.3	52.8	1	69.4	7.2	50
SA45A	SA45A	45	1	50	52.65	55.3	1	72.7	6.9	52
SA48A	SA48A	48	1	53.3	56.1	58.9	1	77.4	6.5	56
SA51A	SA51A	51	1	56.7	59.7	62.7	1	82.4	6.1	61
SA58A	SA58A	58	1	64.4	67.8	71.2	1	93.6	5.3	70
SA60A	SA60A	60	1	66.7	70.2	73.7	1	96.8	5.2	71
SA64A	SA64A	64	1	71.1	74.85	78.6	1	103	4.9	76
SA70A	SA70A	70	1	77.8	81.9	86	1	113	4.4	85
SA78A	SA78A	78	1	86.7	91.25	95.8	1	126	4.0	95
SA90A	SA90A	90	1	100	105.5	111	1	146	3.4	110
SA100A	SA100A	100	1	111	117	123	1	162	3.1	123
SA110A	SA110A	110	1	122	128.5	135	1	177	2.8	133
SA120A	SA120A	120	1	133	140	147	1	193	2.5	146
SA130A*	SA130A*	130	1	144	151.5	159	1	209	2.4	158
SA150A	SA150A	150	1	167	176	185	1	243	2.1	184
SA160A*	SA160A*	160	1	178	187.5	197	1	259	1.9	196
SA170A	SA170A	170	1	189	199	209	1	275	1.8	208

NOTES:

- MiniMOSORB™ transients suppressor is normally selected according to the maximum working peak reverse voltage (V_{RWM}), which should be equal to or greater than the dc or continuous peak operating voltage level.
- V_{BR} measured at pulse test current I_T at an ambient temperature of 25°C .
- Surge current waveform per Figure 4 and derate per Figures 1 and 2.
- 1/2 sine wave (or equivalent square wave), $PW = 8.3\text{ ms}$, duty cycle = 4 pulses per minute
- *Not Available in the 5000/Tape & Reel.

SA5.0A Series




Figure 1. Pulse Rating Curve




Figure 2. Pulse Derating Curve




Figure 3. Capacitance versus Breakdown Voltage




Figure 4. Pulse Waveform




Figure 5. Steady State Power Derating

SA5.0A Series

UL RECOGNITION*

The entire series including the bidirectional CA suffix has *Underwriters Laboratory Recognition* for the classification of protectors (QVGV2) under the UL standard for safety 497B and File #E 116110. Many competitors only have one or two devices recognized or have recognition in a non-protective category. Some competitors have no recognition at all. With the UL497B recognition, our parts successfully passed several tests including Strike Voltage

Breakdown test, Endurance Conditioning, Temperature test, Dielectric Voltage-Withstand test, Discharge test and several more.


Whereas, some competitors have only passed a flammability test for the package material, we have been recognized for much more to be included in their protector category.

*Applies to SA5.0A, CA – SA170A, CA.

Transient Voltage Suppressors – Axial Leaded

500 Watt Peak Power MiniMOSORB™

MINI MOSORB
CASE 59-09
ISSUE S



NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCH.
3. 59-04 OBSOLETE, NEW STANDARD 59-09.
4. 59-03 OBSOLETE, NEW STANDARD 59-10.
5. ALL RULES AND NOTES ASSOCIATED WITH JEDEC DO-41 OUTLINE SHALL APPLY.
6. POLARITY DENOTED BY CATHODE BAND.
7. LEAD DIAMETER NOT CONTROLLED WITHIN F DIMENSION.

DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.228	0.299	5.80	7.60
B	0.102	0.142	2.60	3.60
D	0.028	0.034	0.71	0.86
K	1.000	---	25.44	---

Notes

SA5.0A Series

MiniMOSORB and Surmetic are trademarks of Semiconductor Components Industries, LLC.

ON Semiconductor and  are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer.

PUBLICATION ORDERING INFORMATION

Literature Fulfillment:

Literature Distribution Center for ON Semiconductor
P.O. Box 5163, Denver, Colorado 80217 USA
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada
Email: ONlit@hibbertco.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada

JAPAN: ON Semiconductor, Japan Customer Focus Center
4-32-1 Nishi-Gotanda, Shinagawa-ku, Tokyo, Japan 141-0031
Phone: 81-3-5740-2700
Email: r14525@onsemi.com

ON Semiconductor Website: <http://onsemi.com>

For additional information, please contact your local Sales Representative.