





THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION

© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

REVISIONS

P	F	ZONE/LTR	DESCRIPTION	DATE	APPROVED
2		D	REVISED; ECN AA-8120	3/28/90	LHS



1. MATERIAL: HOUSING - PBT POLYESTER, GRAY
TERMINAL - .0138 THICK PHOSPORUS BRONZE PLATED
WITH .00005 THICK HARD GOLD IN LOCALIZED
GOLD PLATE AREA AND .00008 THICK TIN-LEAD IN
SOLDER AREA OVER .00005 THICK NICKEL UNDERPLATE.
2. FOR APPLICATION INFORMATION SEE AMP SPECIFICATION
114-2048.
3. FOR PERFORMANCE REQUIREMENTS SEE AMP
SPECIFICATION 108-1163.
4. ALL DIMENSIONS SHOWN ARE MAXIMUM UNLESS
OTHERWISE SPECIFIED.

WAS 86-1056-7-1

554990-1

PART NO

AMP | AMP INCORPORATED
Harrisburg, Pa. 17105

NAME PRINTED CIRCUIT MODULAR JACK
ASSEMBLY, TOP ENTRY, 6 POSITION,
FLANGELESS, W/PANEL STOPS,
RIGHT LATCH

SIZE FSCM NO DRAWING NO

C 00779 554990

SCALE 4:1 SHEET 1 OF 1

UNLESS OTHERWISE
SPECIFIED DIMENSIONS
ARE IN INCHES.
TOLERANCES ON:
DECIMALS ±
ANGLES

MATERIAL



FINISH



CONTRACT NO

DR 5/7/86

CHK 5/12/86

APPD 5/12/86

APPD 5/12/86

DSGN APPD

OTHER APPD