




- KEY SHOWN IN POSITION "B"



DAUGHTERCARD HOLE PATTERN
(CONNECTOR SIDE)

NOTES:

1. MATERIALS: HOUSING - LIQUID CRYSTAL POLYMER (LCP) GLASS-FILLED, UL94V-0
TERMINALS - HIGH PERFORMANCE COPPER ALLOY
2. FINISH: SELECTIVE GOLD IN CONTACT AREA.
SELECTIVE MATTE TIN ON PCB TAILS. NICKEL OVERALL.
3. REFER TO MOLEX PRODUCT SPECIFICATION PS-75710-999 FOR PERFORMANCE SPECS.
4. PRODUCT IS PACKAGED PER PK-70873-609.
5. THIS PART CONFORMS TO CLASS B REQUIREMENTS OF COSMETIC SPEC PS-45499-002.
6. GUIDED PARTS TO BE SHIPPED WITH 2-32 TYPE AB
SELF-TAPPING SCREW P/N 73726-0000.
7. FOR GROUNDED GUIDE MODULES USE DIA 2.45+/-0.10 (PTH), DIA 2.58 (DRILL),
AND DIA 4.50 (PAD).
8. MAPS (MOLEX ADVANCED PLATING SYSTEM)

LEAD FREE CONVERSION EC NO: UCP2013-4721 FORM NAME: I-PHLE 2013/04/01 CHKD BY: WOLFE 2013/04/01 APPR: MILLER 2013/07/15	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION							
					MM ONLY		3:1	METRIC								
				mm	INCH	DRAWN BY	DATE	TITLE I-TRAC DAUGHTERCARD 11 ROW SIGNAL MODULE GUIDE RIGHT SALES DWG molex								
			4 PLACES	± ---	± ---	JLAURX	2/17/05									
			3 PLACES	± ---	± ---	CHECKED BY	DATE									
			2 PLACES	± 0.13	± ---	NMARTIN	2/17/05									
			1 PLACE	± 0.25	± ---	APPROVED BY	DATE									
			0 PLACE	±	± ---	CBIXLER	2/17/05	DOCUMENT NO. SD-75710-004								
			ANGULAR ± 1/2°		MATERIAL NO.		SHEET NO. 1 OF 2									
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS										SEE CHART			
REV	SIZE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														

75710-****

MODULE TYPE -- TAIL PLATING TYPE
GUIDE RIGHT -- MATTE TIN (FORMERLY TIN/LEAD) = 4
GUIDE RIGHT -- MATTE TIN = 5

POLARIZATION KEY ORIENTATION

0 = NO KEY

1 = A

2 = B

3 = C

4 = D

5 = E

6 = F

7 = G

8 = H

OF COLUMNS/PLATING

05 = 5 COL 30 GOLD

06 = 6 COL 30 GOLD

08 = 8 COL 30 GOLD

10 = 10 COL 30 GOLD

55 = 5 COL W/ESD 30 GOLD

56 = 6 COL W/ESD 30 GOLD

58 = 8 COL W/ESD 30 GOLD

50 = 10 COL W/ESD 30 GOLD

25 = 5 COL 10 GOLD (MAPS)

26 = 6 COL 10 GOLD (MAPS)

28 = 8 COL 10 GOLD (MAPS)

20 = 10 COL 10 GOLD (MAPS)

65 = 5 COL W/ESD 10 GOLD (MAPS)

66 = 6 COL W/ESD 10 GOLD (MAPS)

68 = 8 COL W/ESD 10 GOLD (MAPS)

60 = 10 COL W/ESD 10 GOLD (MAPS)

MATERIAL NUMBER	# OF COLUMNS	DIM "A" MAX	DIM "B"
75710-***5	5	25.90	14.80
75710-***6	6	29.60	18.50
75710-***8	8	37.00	25.90
75710-***0	10	44.40	33.30

SEE SHEET 1 EC NO: UCP2013-4121 DRAWN BY: JLAURX CHKD: MWOLFE APPR: SMILLER 2013/04/01 2013/04/01 2013/07/15	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 1:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
		DESCRIPTION REV	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	SIZE C	MATERIAL NO. SEE CHART	DOCUMENT NO. SD-75710-004	SHEET NO. 2 OF 2	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	