



DIMENSIONS:

A	4.375" ±0.063
B	7.500" ±0.125
C	5.300" ±0.063
D	3.500" ±0.063
E	5.906" ±0.063
G	0.281" x 0.625" ±0.015



NOTE: ALL LEADS 8" OUT MIN.



75 WATT
20Hz - 20kHz
±1db MAX.(1kHz REF.)
300mA MAX. DC BIAS

ELECTRICAL DATA:

TESTS	CONDITIONS	ACCEPTANCE CRITERIA	
I _{ex}	@ 240V, 60Hz, BRN - BLU	12mA	Max.
Sec. N.L.V	@ 240V, 60Hz, BRN - BLU		
	BLK - GRN =	6.720V	±2%
	BLK - YEL =	9.600V	±2%
	BLK - RED =	13.44V	±2%
DCR	@ 20°C, BRN - BLU =	240.0 Ω	±20%
	@ 20°C, BLK - RED =	0.950 Ω	±20%
HIPOT	PRIMARY - SECONDARY	4250VDC, 1 SEC	

REV.#	REVISION	DATE	HAMMOND ELECTRONIC DIVISION			
0	RELEASED.	C.I. 08/17/15	52 RANKIN PLACE,			
1	ADDED P AND B+ TO SCHEMATIC DIAGRAM.	C.I. 07/05/17	WATERLOO, ONTARIO, N2J 3Z5			
			DWG. BY: C. ILIE	CHK'D BY:	TITLE: SINGLE ENDED	DWG. NO.
			DATE: 08/17/15	APP'D. BY:	"CLASSIC" TUBE OUTPUT	1642SE
				DIMENSIONS: IN(X) MM()	ULTRA-LINEAR TRANSFORMER	



PH # (519) 886-6181
FAX # (519) 886-9540