




PRODUCT NO.	MATING LENGTH		TAIL LENGTH		BEND DIM		PIN TO SIDE		BODY WIDTH				LF OPTION
	DIM F	DIM F	DIM G	DIM G	DIM H	DIM H	DIM J	DIM J	DIM K	DIM K	RETENTION		
	ENGLISH	METRIC	ENGLISH	METRIC	ENGLISH	METRIC	ENGLISH	METRIC	ENGLISH	METRIC	LOCATION	NOTES	
78941-XXX	0.120	3.05	0.120	3.05	0.060	1.52	0.070	1.78	0.240	6.10	F MATE & G TAIL	4	NOTE 5 & 7



SEE NOTE 1



SEE NOTE 1



SEE NOTE 1

NOTE:

- FOR PRODUCT GEOMETRY, LEAD FREE AND GENERAL INFORMATION SEE DRAWINGS 93195 AND 93196. (e.i. 78941-XXYHLF NEW LF NUMBER)
- ANY NUMBER OF POSITIONS FROM 4 (2X2) THRU 72 (2X36).
- PACKAGED IN POLYBAGS ONLY.
- ±.010/0.25 TOL ON DIM "F" APPLIES TO THIS PART.
- ADD SUFFIX "HLF" AT THE END OF PART NUMBER FOR LEAD FREE OPTION.

6. PART NUMBERS WITH "H" SUFFIX WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 20 SECONDS IN WAVE SOLDER, INFRA-RED OR VAPOR PHASE SOLDER PROCESS.

PART NUMBERS WITHOUT "H" SUFFIX WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR WAVE SOLDER PROCESS.

- THESE PRODUCTS MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.

8. PLATING OPTIONS:
MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.

mat'l. code				surface		tolerance	projection	product family				
-				ISO 1302		ISO 406 ISO 1101		BERGSTIK				
ltr	ecn	no	dr	date	tolerances unless otherwise specified			title				
G	V41115	HTB		7/25/94	angles	linear		BERGSTIK® II HDR. D/R				
H	V41571	HTB		10/24/94				.100 R/A SELF-RET				
J	V50299	HTB		3/16/95	0°±2'			scale 1:1				
K	V20832	GIP		7/11/02	dr	T.BREWBAKER	10/24/94		dwg no		sheet 1 of 1	size
L	V21814	TAB		5/08/03	enr	T. HANNA	10/24/94		78941		A3	
M	M05-0027	MHT		4/21/05	chr	T. HANNA	10/24/94					
N	M06-0269	AEA		7/19/06	appd	T. HANNA	10/24/94					
sheet	revision											
index	sheet	1										