

**Harvatek Surface Mount LED Data Sheet  
HT-F195 InGaN Series**

|                                                                                                |                               |               |                 |                      |
|------------------------------------------------------------------------------------------------|-------------------------------|---------------|-----------------|----------------------|
| Official Product                                                                               | Product: HT-F195 InGaN Series |               |                 | Data Sheet No.       |
| Tentative Product                                                                              | *****                         |               |                 | HT-F195 InGaN Series |
| Specifications are subject to change without notice. Data and drawings herein are copyrighted. |                               | Oct. 12, 2005 | Version of 1.01 | Page 1/20            |

|                                                                  |           |
|------------------------------------------------------------------|-----------|
| <b>DISCLAIMER .....</b>                                          | <b>3</b>  |
| <b>PRODUCT SPECIFICATIONS .....</b>                              | <b>4</b>  |
| <b>ATTENTION: ELECTROSTATIC DISCHARGE (ESD) PROTECTION .....</b> | <b>4</b>  |
| <b>LABEL SPECIFICATIONS .....</b>                                | <b>5</b>  |
| <b>PRODUCT CHARACTERISTICS .....</b>                             | <b>9</b>  |
| <b>ABSOLUTE MAXIMUM RATINGS .....</b>                            | <b>9</b>  |
| <b>ELECTRO-OPTICAL CHARACTERISTICS .....</b>                     | <b>9</b>  |
| <b>PACKAGE OUTLINE DIMENSION .....</b>                           | <b>10</b> |
| <b>RECOMMENDED SOLDERING PATTERN FOR REFLOW SOLDERING .....</b>  | <b>10</b> |
| <b>CHARACTERISTIC CURVES .....</b>                               | <b>11</b> |
| <b>RADIATION PATTERN .....</b>                                   | <b>12</b> |
| <b>PACKAGING .....</b>                                           | <b>13</b> |
| <b>TAPE DIMENSION .....</b>                                      | <b>13</b> |
| <b>REEL DIMENSION .....</b>                                      | <b>14</b> |
| <b>PACKING .....</b>                                             | <b>15</b> |
| <b>DRY PACK .....</b>                                            | <b>16</b> |
| <b>REFLOW SOLDERING .....</b>                                    | <b>17</b> |
| <b>PRECAUTIONS .....</b>                                         | <b>18</b> |
| <b>REWORKING .....</b>                                           | <b>18</b> |
| <b>CLEANING .....</b>                                            | <b>18</b> |
| <b>RELIABILITY .....</b>                                         | <b>19</b> |
| <b>REVISION HISTORY .....</b>                                    | <b>20</b> |

|                                                                                                |                               |               |                 |                      |
|------------------------------------------------------------------------------------------------|-------------------------------|---------------|-----------------|----------------------|
| Official Product                                                                               | Product: HT-F195 InGaN Series |               |                 | Data Sheet No.       |
| Tentative Product                                                                              | *****                         |               |                 | HT-F195 InGaN Series |
| Specifications are subject to change without notice. Data and drawings herein are copyrighted. |                               | Oct. 12, 2005 | Version of 1.01 | Page 2/20            |

**DISCLAIMER**

HARVATEK reserves the right to make changes without further notice to any products herein to improve reliability, function or design. HARVATEK does not assume any liability arising out of the application or use of any product or circuit described herein; neither does it convey any license under its patent rights, nor the rights of others.

**LIFE SUPPORT POLICY**

HARVATEK's products are not authorized for use as critical components in life support devices or systems without the express written approval of the President of HARVATEK or HARVATEK INTERNATIONAL. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

|                                                                                                |                               |               |                 |                      |
|------------------------------------------------------------------------------------------------|-------------------------------|---------------|-----------------|----------------------|
| Official Product                                                                               | Product: HT-F195 InGaN Series |               |                 | Data Sheet No.       |
| Tentative Product                                                                              | *****                         |               |                 | HT-F195 InGaN Series |
| Specifications are subject to change without notice. Data and drawings herein are copyrighted. |                               | Oct. 12, 2005 | Version of 1.01 | Page 3/20            |

## Product Specifications

| Product   | Emission Color | Technology | Test Current<br>$I_F$ (mA) | Luminous Intensity<br>$I_V$ (mcd) | Forward Voltage<br>$V_F$ (V) | Orderable Part Number |
|-----------|----------------|------------|----------------------------|-----------------------------------|------------------------------|-----------------------|
| HT-F195NB | Blue           | InGaN      | 20                         | 90 typ                            | 3.3 typ                      | HT-F195NB-ZZZZ        |
| HT-F195NG | True Green     | InGaN      | 20                         | 160 typ                           | 3.3 typ                      | HT-F195NG-ZZZZ        |
| HT-F195TW | White          | InGaN      | 20                         | 250 typ                           | 3.3 typ                      | HT-F195TW-ZZZZ        |

|              | Specification        | Material                          | Quantity         |
|--------------|----------------------|-----------------------------------|------------------|
| Resin        | Water clear          | Epoxy resin                       |                  |
| Carrier tape | Per EIA 481-1A specs | Conductive black tape             | 4000pcs per reel |
| Reel         | Per EIA 481-1A specs | Conductive black                  |                  |
| Label        | HT standard          | Paper                             |                  |
| Packing bag  | 220x240mm            | Aluminum laminated bag/ no-zipper | One reel per bag |
| Carton       | HT standard          | Paper                             |                  |

Others:

Each immediate box consists of 5 reels. The 5 reels may not necessarily have the same lot number or the same bin combinations of  $I_V$ ,  $\lambda_D$  and  $V_F$ . Each reel has a label identifying its specification; the immediate box consists of a product label as well.

### ATTENTION: Electrostatic Discharge (ESD) protection



The symbol to the left denotes that ESD precaution is needed. ESD protection for GaP and AlGaAs based chips is necessary even though they are relatively safe in the presence of low static-electric discharge. Parts built with AlInGaP, GaN, or/and InGaN based chips are **STATIC SENSITIVE devices**. ESD precaution must be taken during design and assembly.

If manual work or processing is needed, please ensure the device is adequately protected from ESD during the process.

|                                                                                                |                               |               |                      |
|------------------------------------------------------------------------------------------------|-------------------------------|---------------|----------------------|
| Official Product                                                                               | Product: HT-F195 InGaN Series |               | Data Sheet No.       |
| Tentative Product                                                                              | *****                         |               | HT-F195 InGaN Series |
| Specifications are subject to change without notice. Data and drawings herein are copyrighted. |                               | Oct. 12, 2005 | Version of 1.01      |
|                                                                                                |                               | Page 4/20     |                      |

## Label Specifications

|                   |              |                                                                                   |                      |
|-------------------|--------------|-----------------------------------------------------------------------------------|----------------------|
| <b>HARVATEK</b>   |              |  | Date: yyyy/mm/dd<br> |
| CUSTOMER P/N:<br> |              |                                                                                   |                      |
| HARVATEK P/N:<br> | QTY: PCS<br> |                                                                                   |                      |
| LOT NO:<br>       |              | QC                                                                                |                      |
| IV BIN:           | COLOR BIN:   | VF:                                                                               |                      |

## Harvatek P/N:

**H T - F195 XX - ZZZZ**

| Series Name                                                                                 | Emitting Color                                        | Customer Code                              |
|---------------------------------------------------------------------------------------------|-------------------------------------------------------|--------------------------------------------|
| <b>HT-F195</b><br>HT: Harvatek<br>F195: 0603 0.4mm series<br>1.6 (L) x 0.8 (W) x 0.4 (H) mm | <b>XXX</b><br>NB: Blue<br>NG: True Green<br>TW: White | <b>ZZZZ</b><br>Customer Product Code (TBD) |

## Lot No.:

1 2 3 4 5 6 7 8 9 10  
**P 1 2 2 3 0 A - D T**

|                                                                                                |                               |               |                 |                      |
|------------------------------------------------------------------------------------------------|-------------------------------|---------------|-----------------|----------------------|
| Official Product                                                                               | Product: HT-F195 InGaN Series |               |                 | Data Sheet No.       |
| Tentative Product                                                                              | *****                         |               |                 | HT-F195 InGaN Series |
| Specifications are subject to change without notice. Data and drawings herein are copyrighted. |                               | Oct. 12, 2005 | Version of 1.01 | Page 5/20            |

| Code 1                      | Code 2                                            | Code 3                                                                 | Code 4, 5  | Code 6, 7          | Code 9                  | Code 10        |
|-----------------------------|---------------------------------------------------|------------------------------------------------------------------------|------------|--------------------|-------------------------|----------------|
|                             | Mfg. Year                                         | Mfg. Month                                                             | Mfg. Date  | Lots               | Resin Color             | Packaging      |
| Internal<br>Tracing<br>Code | Z: 2000<br>1: 2001<br>2: 2002<br>3: 2003<br>..... | 1: Jan.<br>2: Feb.<br>....<br>9: Sep.<br>A: Oct.<br>B: Nov.<br>C: Dec. | 1~31/ (30) | 01~99,<br>A,B,C... | D: Diffused<br>C: Clear | T: Tape & Reel |

## Luminous Intensity (I<sub>v</sub>) Bin:

| Bin | Luminous Intensity Range (mcd) |         | Bin | Luminous Intensity Range (mcd) |         |
|-----|--------------------------------|---------|-----|--------------------------------|---------|
|     | Minimum                        | Maximum |     | Minimum                        | Maximum |
| H1  | 2.8                            | 3.6     | H2  | 3.6                            | 4.5     |
| J1  | 4.5                            | 5.7     | J2  | 5.7                            | 7.2     |
| K1  | 7.2                            | 9.0     | K2  | 9.0                            | 11.2    |
| L1  | 11.2                           | 14.2    | L2  | 14.2                           | 18.0    |
| M1  | 18.0                           | 22.5    | M2  | 22.5                           | 28.5    |
| N1  | 28.5                           | 36.0    | N2  | 36.0                           | 45.0    |
| P1  | 45.0                           | 57.0    | P2  | 57.0                           | 71.5    |
| Q1  | 71.5                           | 90.0    | Q2  | 90.0                           | 112.5   |
| R1  | 112.5                          | 142.0   | R2  | 142.0                          | 180.0   |
| S1  | 180.0                          | 227.0   | S2  | 227.0                          | 285.0   |
| T1  | 285.0                          | 360.0   | T2  | 360.0                          | 450.0   |
| U1  | 450.0                          | 570.0   | U2  | 570.0                          | 715.0   |

@20mA / Ta=25° C, Tolerance: ± 10%

|                                                                                                |                               |               |                      |
|------------------------------------------------------------------------------------------------|-------------------------------|---------------|----------------------|
| Official Product                                                                               | Product: HT-F195 InGaN Series |               | Data Sheet No.       |
| Tentative Product                                                                              | *****                         |               | HT-F195 InGaN Series |
| Specifications are subject to change without notice. Data and drawings herein are copyrighted. |                               | Oct. 12, 2005 | Version of 1.01      |
|                                                                                                |                               | Page 6/20     |                      |

## Wavelength ( $\lambda_D$ ) Bin:

| Bin | Wavelength Range (nm) |       |           |       |
|-----|-----------------------|-------|-----------|-------|
|     | True Green (NG)       |       | Blue (NB) |       |
|     | Min                   | Max   | Min       | Max   |
| -   |                       |       |           |       |
| A   | 515.0                 | 520.0 | 460.0     | 464.0 |
| B   | 520.0                 | 525.0 | 464.0     | 468.0 |
| C   | 525.0                 | 530.0 | 468.0     | 472.0 |
| D   | 530.0                 | 535.0 | 472.0     | 476.0 |
| E   | 535.0                 | 540.0 | 476.0     | 480.0 |
| F   |                       |       | 480.0     | 485.0 |
| H   |                       |       |           |       |
| J   |                       |       |           |       |

@20mA / Ta=25°C, Tolerance:  $\pm 0.5\text{nm}$

## Forward Voltage ( $V_F$ ) Bin:

| Color                                 | Bin Code | Spec. Range |
|---------------------------------------|----------|-------------|
| Blue (NB)<br>Green (NG)<br>White (TW) | G8       | 2.7-2.9 V   |
|                                       | H7       | 2.9-3.1 V   |
|                                       | H8       | 3.1-3.3 V   |
|                                       | J7       | 3.3-3.5 V   |
|                                       | J8       | 3.5-3.7 V   |
|                                       | K7       | 3.7-3.9 V   |

@20mA / Ta=25°C, Tolerance:  $\pm 0.05\text{ V}$

|                                                                                                |                               |               |                      |
|------------------------------------------------------------------------------------------------|-------------------------------|---------------|----------------------|
| Official Product                                                                               | Product: HT-F195 InGaN Series |               | Data Sheet No.       |
| Tentative Product                                                                              | *****                         |               | HT-F195 InGaN Series |
| Specifications are subject to change without notice. Data and drawings herein are copyrighted. |                               | Oct. 12, 2005 | Version of 1.01      |
|                                                                                                |                               | Page 7/20     |                      |

## Chromaticity Bin (for TW only):

|   | Rank A0 |       |       |       |
|---|---------|-------|-------|-------|
| x | 0.280   | 0.264 | 0.283 | 0.296 |
| y | 0.248   | 0.267 | 0.305 | 0.276 |


|   | Rank B3 |       |       |       |
|---|---------|-------|-------|-------|
| x | 0.287   | 0.283 | 0.304 | 0.307 |
| y | 0.295   | 0.305 | 0.330 | 0.315 |

|   | Rank B4 |       |       |       |
|---|---------|-------|-------|-------|
| x | 0.307   | 0.304 | 0.330 | 0.330 |
| y | 0.315   | 0.330 | 0.360 | 0.339 |

|   | Rank C0 |       |       |       |
|---|---------|-------|-------|-------|
| x | 0.330   | 0.330 | 0.361 | 0.356 |
| y | 0.318   | 0.360 | 0.385 | 0.351 |

|   | Rank B5 |       |       |       |
|---|---------|-------|-------|-------|
| x | 0.296   | 0.287 | 0.307 | 0.311 |
| y | 0.276   | 0.295 | 0.315 | 0.294 |

|   | Rank B6 |       |       |       |
|---|---------|-------|-------|-------|
| x | 0.311   | 0.307 | 0.330 | 0.330 |
| y | 0.294   | 0.315 | 0.339 | 0.318 |



@20mA / Ta=25°C, Tolerance:  $\pm 0.01$

|                                                                                                |                               |                 |                      |
|------------------------------------------------------------------------------------------------|-------------------------------|-----------------|----------------------|
| Official Product                                                                               | Product: HT-F195 InGaN Series |                 | Data Sheet No.       |
| Tentative Product                                                                              | *****                         |                 | HT-F195 InGaN Series |
| Specifications are subject to change without notice. Data and drawings herein are copyrighted. | Oct. 12, 2005                 | Version of 1.01 | Page 8/20            |



## Product Characteristics

### Absolute Maximum Ratings

| Product   | Emission Color | P <sub>d</sub> (mW) | I <sub>F</sub> (mA) | I <sub>FP</sub> * (mA) | V <sub>R</sub> (V) | T <sub>OP</sub> (°C) | T <sub>ST</sub> (°C) |
|-----------|----------------|---------------------|---------------------|------------------------|--------------------|----------------------|----------------------|
| HT-F195NB | Blue           | 117                 | 30                  | 120                    | 5                  | -40~+100             | -40~+100             |
| HT-F195NG | True Green     |                     |                     |                        |                    |                      |                      |
| HT-F195TW | White          |                     |                     |                        |                    |                      |                      |

\* Condition for I<sub>FP</sub> is pulse of 1/10 duty and 0.1msec width

### Electro-Optical Characteristics

(T<sub>a</sub> = 25 °C)

| Product   | Emission Color | I <sub>F</sub> (mA) | V <sub>F</sub> (V) |     | λ(nm)            |                |    | I <sub>v</sub> (mcd) |     |
|-----------|----------------|---------------------|--------------------|-----|------------------|----------------|----|----------------------|-----|
|           |                |                     | typ                | max | λ <sub>D</sub>   | λ <sub>P</sub> | Δλ | min                  | typ |
| HT-F195NB | Blue           | 20                  | 3.3                | 3.9 | 470              | 468            | 40 | 36                   | 90  |
| HT-F195NG | True Green     | 20                  | 3.3                | 3.9 | 527              | 520            | 40 | 90                   | 160 |
| HT-F195TW | White          | 20                  | 3.3                | 3.9 | X=0.29<br>Y=0.31 | -              | -  | 140                  | 250 |



\* Per NIST standards

|                                                                                                |                               |  |               |                      |           |
|------------------------------------------------------------------------------------------------|-------------------------------|--|---------------|----------------------|-----------|
| Official Product                                                                               | Product: HT-F195 InGaN Series |  |               | Data Sheet No.       |           |
| Tentative Product                                                                              | *****                         |  |               | HT-F195 InGaN Series |           |
| Specifications are subject to change without notice. Data and drawings herein are copyrighted. |                               |  | Oct. 12, 2005 | Version of 1.01      | Page 9/20 |

## Package Outline Dimension







## Recommended Soldering Pattern for Reflow Soldering

Unit: mm Tolerance: +/-0.1

| Outline Dimension                                                                                                                                                                                                                                                                                                                                   | Solder Pattern                                                                                      |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------|
|  <p>LED Die</p> <p>Lead Frame</p> <p>1.10</p> <p>0.80</p> <p>1.60</p> <p>0.40</p> <p>Resin</p> <p>Soldering Terminal</p> <p>1.10</p> <p>0.25</p> <p>Polarity</p> <p>It's not recommended this area has any print.</p> <p>0.8</p> <p>1.0</p> <p>0.8</p> <p>0.8</p> |  <p>Unit: mm</p> |
| Soldering terminals may shift in the x, y direction.                                                                                                                                                                                                                                                                                                | Unit: mm                                                                                            |


|                                                                                                |                               |                      |
|------------------------------------------------------------------------------------------------|-------------------------------|----------------------|
| Official Product                                                                               | Product: HT-F195 InGaN Series | Data Sheet No.       |
| Tentative Product                                                                              | *****                         | HT-F195 InGaN Series |
| Specifications are subject to change without notice. Data and drawings herein are copyrighted. | Oct. 12, 2005                 | Version of 1.01      |
|                                                                                                |                               | Page 10/20           |

## Characteristic Curves



|                                                                                                |                               |                      |
|------------------------------------------------------------------------------------------------|-------------------------------|----------------------|
| Official Product                                                                               | Product: HT-F195 InGaN Series | Data Sheet No.       |
| Tentative Product                                                                              | *****                         | HT-F195 InGaN Series |
| Specifications are subject to change without notice. Data and drawings herein are copyrighted. | Oct. 12, 2005                 | Version of 1.01      |
|                                                                                                |                               | Page 11/20           |


**Radiation Pattern**



|                                                                                                |                               |               |                 |                      |
|------------------------------------------------------------------------------------------------|-------------------------------|---------------|-----------------|----------------------|
| Official Product                                                                               | Product: HT-F195 InGaN Series |               |                 | Data Sheet No.       |
| Tentative Product                                                                              | *****                         |               |                 | HT-F195 InGaN Series |
| Specifications are subject to change without notice. Data and drawings herein are copyrighted. |                               | Oct. 12, 2005 | Version of 1.01 | Page 12/20           |

## Packaging

## Tape Dimension




| Part No. | Dim. A          | Dim. B          | Dim. C          | Q'ty/Reel |
|----------|-----------------|-----------------|-----------------|-----------|
| HT-F195  | $1.75 \pm 0.10$ | $0.90 \pm 0.10$ | $0.60 \pm 0.10$ | 4K        |

Unit: mm


|                                                                                                |                               |               |                 |                      |
|------------------------------------------------------------------------------------------------|-------------------------------|---------------|-----------------|----------------------|
| Official Product                                                                               | Product: HT-F195 InGaN Series |               |                 | Data Sheet No.       |
| Tentative Product                                                                              | *****                         |               |                 | HT-F195 InGaN Series |
| Specifications are subject to change without notice. Data and drawings herein are copyrighted. |                               | Oct. 12, 2005 | Version of 1.01 | Page 13/20           |

## Reel Dimension



|                                                                                                |                               |                      |
|------------------------------------------------------------------------------------------------|-------------------------------|----------------------|
| Official Product                                                                               | Product: HT-F195 InGaN Series | Data Sheet No.       |
| Tentative Product                                                                              | *****                         | HT-F195 InGaN Series |
| Specifications are subject to change without notice. Data and drawings herein are copyrighted. | Oct. 12, 2005                 | Version of 1.01      |
|                                                                                                |                               | Page 14/20           |

## Packing



5 boxes per carton is available depending on shipment quantity.

|                                                                                                                                                                                                                                                                      | Specification        | Material                          | Quantity         |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------|-----------------------------------|------------------|
| Carrier tape                                                                                                                                                                                                                                                         | Per EIA 481-1A specs | Conductive black tape             | 4000pcs per reel |
| Reel                                                                                                                                                                                                                                                                 | Per EIA 481-1A specs | Conductive black                  |                  |
| Label                                                                                                                                                                                                                                                                | HT standard          | Paper                             |                  |
| Packing bag                                                                                                                                                                                                                                                          | 220x240mm            | Aluminum laminated bag/ no-zipper | One reel per bag |
| Carton                                                                                                                                                                                                                                                               | HT standard          | Paper                             | Non-specified    |
| Others:                                                                                                                                                                                                                                                              |                      |                                   |                  |
| Each immediate box consists of 5 reels. The 5 reels may not necessarily have the same lot number or the same bin combinations of Iv, $\lambda_D$ and Vf. Each reel has a label identifying its specification; the immediate box consists of a product label as well. |                      |                                   |                  |


|                                                                                                |                               |                 |                      |
|------------------------------------------------------------------------------------------------|-------------------------------|-----------------|----------------------|
| Official Product                                                                               | Product: HT-F195 InGaN Series |                 | Data Sheet No.       |
| Tentative Product                                                                              | *****                         |                 | HT-F195 InGaN Series |
| Specifications are subject to change without notice. Data and drawings herein are copyrighted. | Oct. 12, 2005                 | Version of 1.01 | Page 15/20           |

## Dry Pack

All SMD optical devices are **MOISTURE SENSITIVE**. Avoid exposure to moisture at all times during transportation or storage. Every reel is packaged in a moisture protected anti-static bag. Each bag is properly sealed prior to shipment.

Upon request, a humidity indicator will be included in the moisture protected anti-static bag prior to shipment.

The packaging sequence is as follows:




|                                                                                                |                               |               |                 |                      |
|------------------------------------------------------------------------------------------------|-------------------------------|---------------|-----------------|----------------------|
| Official Product                                                                               | Product: HT-F195 InGaN Series |               |                 | Data Sheet No.       |
| Tentative Product                                                                              | *****                         |               |                 | HT-F195 InGaN Series |
| Specifications are subject to change without notice. Data and drawings herein are copyrighted. |                               | Oct. 12, 2005 | Version of 1.01 | Page 16/20           |




## Reflow Soldering

- Recommended tin glue specifications: melting temperature in the range of 178~192 °C
- The recommended reflow soldering profile is as follows (temperatures indicated are as measured on the surface of the LED resin):

Lead Solder Profile



Lead-free Solder Profile



|                                                                                                |                               |               |                 |                      |
|------------------------------------------------------------------------------------------------|-------------------------------|---------------|-----------------|----------------------|
| Official Product                                                                               | Product: HT-F195 InGaN Series |               |                 | Data Sheet No.       |
| Tentative Product                                                                              | *****                         |               |                 | HT-F195 InGaN Series |
| Specifications are subject to change without notice. Data and drawings herein are copyrighted. |                               | Oct. 12, 2005 | Version of 1.01 | Page 17/20           |

**Precautions**

1. Avoid exposure to moisture at all times during transportation or storage.
2. Anti-Static precaution must be taken when handling GaN, InGaN, and AlInGaP products.
3. It is suggested to connect the unit with a current limiting resistor of the proper size. Avoid applying a reverse voltage beyond the specified limit.
4. Avoid operation beyond the limits as specified by the absolute maximum ratings.
5. Avoid direct contact with the surface through which the LED emits light.
6. If possible, assemble the unit in a clean room or dust-free environment.

**Reworking**

- Rework should be completed within 5 seconds under 260 °C.
- The iron tip must not come in contact with the copper foil.
- Twin-head type is preferred.

**Cleaning**

Following are cleaning procedures after soldering:

- An alcohol-based solvent such as isopropyl alcohol (IPA) is recommended.
- Temperature x Time should be 50°C x 30sec. or <30°C x 3min
- Ultra sonic cleaning: < 15W/ bath; bath volume ≤ 1liter
- Curing: 100 °C max, <3min

**Cautions of Pick and Place**

- Avoid stress on the resin at elevated temperature.
- Avoid rubbing or scraping the resin by any object.
- Electro-static may cause damage to the component. Please ensure that the equipment is properly grounded. Use of an ionizer fan is recommended.

|                                                                                                |                               |               |                 |                      |
|------------------------------------------------------------------------------------------------|-------------------------------|---------------|-----------------|----------------------|
| Official Product                                                                               | Product: HT-F195 InGaN Series |               |                 | Data Sheet No.       |
| Tentative Product                                                                              | *****                         |               |                 | HT-F195 InGaN Series |
| Specifications are subject to change without notice. Data and drawings herein are copyrighted. |                               | Oct. 12, 2005 | Version of 1.01 | Page 18/20           |

## Reliability

| Item                                 | Frequency/ lots/ samples/ failures                              | Standards Reference            | Conditions                                                                                                                   |
|--------------------------------------|-----------------------------------------------------------------|--------------------------------|------------------------------------------------------------------------------------------------------------------------------|
| Precondition                         | For all reliability monitoring tests according to JEDEC Level 2 | J-STD-020                      | 1.) Baking at 85°C for 24hrs<br>2.) Moisture storage at 85°C/ 60% R.H. for 168hrs                                            |
| Solderability                        | 1Q/ 1/ 22/ 0                                                    | JESD22-B102-B<br>And CNS-5068  | Accelerated aging 155°C/ 24hrs<br>Tinning speed: 2.5+0.5cm/s<br>Tinning: A: 215°C/ 3+1s or B: 260°C/ 10+1s                   |
| Resistance to soldering heat         |                                                                 | CNS-5067                       | Dipping soldering terminal only<br>Soldering bath temperature<br>A: 260+/-5°C; 10+/-1s<br>B: 350+/-10°C; 3+/-0.5s            |
| Operating life test                  | 1Q/ 1/ 40/ 0                                                    | CNS-11829                      | 1.) Precondition: 85°C baking for 24hrs<br>85°C/ 60%R.H. for 168hrs<br>2.) Tamb25°C; IF=20mA; duration 1000hrs               |
| High humidity, high temperature bias | 1Q/ 1/ 45/ 0                                                    | JESD-A101-B                    | Tamb: 85°C<br>Humidity: 85% R.H., IF=5mA<br>Duration: 1000hrs                                                                |
| High temperature bias                | 1Q/ 1/ 20                                                       | HT specs.                      | Tamb: 55°C<br>IF=20mA<br>Duration: 1000hrs                                                                                   |
| Pulse life test                      | 1Q/ 1/ 40/ 0                                                    |                                | Tamb25°C, If=20mA, Ip=100mA, Duty cycle=0.125 (tp=125μs, T=1sec)<br>Duration 500hrs)                                         |
| Temperature cycle                    | 1Q/ 1/ 76/ 0                                                    | JESD-A104-A<br>IEC 68-2-14, Nb | A cycle: -40 degree C 15min; +85 degree C 15min<br>Thermal steady within 5 min..<br>300 cycles<br>2 chamber/ Air-to-air type |
| High humidity storage test           | 1Q/ 1/ 40/ 0                                                    | CNS-6117                       | 60+3°C<br>90+5/-10% R.H. for 500hrs                                                                                          |
| High temperature storage test        | 1Q/ 1/ 40/ 0                                                    | CNS-554                        | 100+10°C for 500hrs                                                                                                          |
| Low temperature storage test         | 1Q/ 1/ 40/ 0                                                    | CNS-6118                       | -40+5°C for 500hrs                                                                                                           |

|                                                                                                |                               |               |                 |                      |
|------------------------------------------------------------------------------------------------|-------------------------------|---------------|-----------------|----------------------|
| Official Product                                                                               | Product: HT-F195 InGaN Series |               |                 | Data Sheet No.       |
| Tentative Product                                                                              | *****                         |               |                 | HT-F195 InGaN Series |
| Specifications are subject to change without notice. Data and drawings herein are copyrighted. |                               | Oct. 12, 2005 | Version of 1.01 | Page 19/20           |

**Revision History**

| Changes since last revision | Page | Version No. | Revision Date |
|-----------------------------|------|-------------|---------------|
| New format                  |      | 1.0         | 07-15-2005    |
| Correct type in packaging   | 13   | 1.01        | 10-12-2005    |
|                             |      |             |               |
|                             |      |             |               |
|                             |      |             |               |
|                             |      |             |               |
|                             |      |             |               |
|                             |      |             |               |
|                             |      |             |               |

|                                                                                                |                               |                 |                      |
|------------------------------------------------------------------------------------------------|-------------------------------|-----------------|----------------------|
| Official Product                                                                               | Product: HT-F195 InGaN Series |                 | Data Sheet No.       |
| Tentative Product                                                                              | *****                         |                 | HT-F195 InGaN Series |
| Specifications are subject to change without notice. Data and drawings herein are copyrighted. | Oct. 12, 2005                 | Version of 1.01 | Page 20/20           |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Harvatek:

[HT-F195NB-5496](#) [HT-F195NG-5501](#) [HT-F195TW-5497](#)