



$$(1:1)$$


- 1 POWER CONTACT: 1 TO 4
OUTER DIMENSIONS OF INSULATION: MAX. Ø10,8 MM
- 2 SIGNAL CONTACT: 11 AND 12
OUTER DIMENSIONS OF INSULATION: MAX. Ø4,8 MM
- 3 GROUNDING CONTACT
- 4 SUITABLE HOOD SIZE 6: SERIES HB; HD; EMV AND HIP
- 5 STANDARDS:
DIN EN 61984; DIN EN 60664-1
- 6 UL; CSA AUTHORISATION
- 7 PACKAGING:
5 PIECES IN A CARTON




Technical drawing of the rear view of a mechanical component. The drawing shows a symmetrical design with two large circular openings in the center, each with a smaller circular feature inside. On the left side, there is a small circular feature labeled '11' and a larger circular feature labeled '12'. The component has four mounting points, each with a circular hole and a crosshair pattern. The drawing is a black and white line drawing.



1	SCREW	STEEL	NICKEL PLATED	BLUE	DIN EN ISO 1207-M5X8	9
4	FIXING SCREW	STEEL	NICKEL PLATED	BLUE	M3X10,5	8
2	SOCKET GROUNDING CONTACT	BRASS	NICKEL PLATED	BLUE	-	7
4	THREAD PIN	STEEL	NICKEL PLATED	BLUE		6
2	CONTACT SCREW	STEEL	NICKEL PLATED	BLUE	M3X5,7	5
1	CLAMP TAB	STEEL	NICKEL PLATED	BLUE	---	4
2	SOCKET CONTACT	BRASS	SILVER PLATED	BLUE	.	3
4	SOCKET CONTACT	BRASS	SILVER PLATED	BLUE	-	2
1	FEMALE INSERT	PBT-GF30	-	LIGHT GREY	-	1
QTY.	DESCRIPTION	MATERIAL	SURFACE	COLOR	NOTE	ITEM

PARTS LIST

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION. DIESES ZEICHNUNGSDOKUMENT WIRD DURCH AMP INCORPORATED KONTROLLIERT. AENDERUNGEN, DIE DEM TECHNISCHEN FORTSCHRITT ENTSPRECHEN, SIND VORBEHALTEN. DEN JEWEILS LETZTGUELTFEN AENDERUNGSSTAND ERFAEHREN SIE AUF ANFRAGE.		DWN 12.07.2005 SCHNEIDER		 Tyco / Electronics AMP GmbH D - 53819 Neunkirchen	
DIMENSIONS: DIMENSIONEN: mm		CHK 12.07.2005 SCHNURPFEIL			
		APVD - PRODUCT SPEC. 108-74058 PRODUKTSPEZ.		NAME FEMALE INSERT HMX.4/2.BU.S	
TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN n. ISO 8015 - mH-E n. ISO 2768 - 140 n. DIN 16901- 0 PLC # 1 PLC # 2 PLC # 3 PLC # ANGLES / WINKEL #		APPLICATION SPEC. 114-74058 VERARBEITUNGSSPEZ.			
MATERIAL		FINISH / OBERFLAECHE / FARBE		WEIGHT 0,126 KG GEWICHT	
				SIZE A3 CAGE CODE 00779 DRAWING NO. C-1102076 ZEICHNUNGS-NR.	
CUSTOMER DRAWING / KUNDENZEICHNUNG				SCALE MASSTAB 1:1 SHEET BLATT 1 OF VON 1 REV. D1	