





6 5 4 3 2 1 used for: D-SUB HD



POS.	A -0.76	B +0.25	C	D -0.3	Part No.
15	31.19	16.79	25.00 +0.12/-0.13	6.12	163A16649X
26	39.52	25.12	33.30 +0.15/-0.1	6.12	163A16659X
44	53.42	38.84	47.04 +0.13	5.99	163A16669X
62	69.70	55.30	63.50 +0.13	5.99	163A16679X

NOTES:

- METALSHELLS: STEEL; min. 320µ" TIN
- INSULATORS: PBT GF UL 94 V-0, BLACK
- CONTACTS: COPPER ALLOY
PLATING: min. 8µ" HARD GOLD OVER min. 50µ" NICKEL
SOLDER CUP ACCEPTS CABLE AWG 22
- THREADED INSERT: COPPER ALLOY; min. 200µ" TIN over 80µ" NICKEL
- COLLAR: COPPER ALLOY; min. 200µ" TIN over 80µ" NICKEL
- MAXIMUM TORQUE VALUE FOR THREAD: 6" LBS
- CONNECTOR IS PART MARKED: PART-NO. CONEC Y/WW
- ☐ = CRITICAL DIMENSION

Directive 2002/95/EC
RoHS
Compliant

APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL
CUSTOMER APPROVAL DATE:
NAME: TITLE:
COMPANY NAME:
APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY, WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name

tolerance	name
2002 date	Parei
drawn 10.09.	Mickenbecker
appd. 10.09.	DIN 41652
norm	d-old

scale: 2:1 (5:1)
material: SEE NOTES
title: D-SUB HD MALE 15-62pos. SOLDER CUP with threaded insert
dwg no: AutoCAD 2000 DIN-A 16K1A751 3 sh: 1/1
part no: SEE TABLE