



Fast Recovery Diodes (Stud Version), 6/12/16 A



DO-203AA (DO-4)

FEATURES

- Short reverse recovery time
- Low stored charge
- Wide current range
- Excellent surge capabilities
- Standard JEDEC types
- Stud cathode and stud anode versions
- Fully characterized reverse recovery conditions
- RoHS compliant



TYPICAL APPLICATIONS

- DC power supplies
- Inverters
- Converters
- Choppers
- Ultrasonic systems
- Freewheeling diodes

PRODUCT SUMMARY

$I_{F(AV)}$	6/12/16 A
-------------	-----------

MAJOR RATINGS AND CHARACTERISTICS

SYMBOL	CHARACTERISTICS	1N3879. TO 1N3883.	1N3889. TO 1N3893.	6FL..	12FL..	16FL..	UNITS
I _{F(AV)}	T _C = 100 °C	6 ⁽¹⁾	12 ⁽¹⁾	6	12	16	A
I _{F(RMS)}		9.5	19	9.5	19	25	A
I _{FSM}	50 Hz	72	145	110	145	180	A
	60 Hz	75 ⁽¹⁾	150 ⁽¹⁾	115	150	190	
I ² t	50 Hz	26	103	60	103	160	A ² s
	60 Hz	23	94	55	94	150	
I ² √t		363	856	1452	1452	2290	I ² √s
V _{RRM}	Range	50 to 400 ⁽¹⁾		50 to 1000			V
t _{rr}		See Recovery Characteristics table					ns
T _J	Range	- 65 to 150					°C

Note

⁽¹⁾ JEDEC registered values

1N3879(R), 1N3889(R), 6/12/16FL(R) Series

Vishay High Power Products Fast Recovery Diodes
(Stud Version), 6/12/16 A



ELECTRICAL SPECIFICATIONS

VOLTAGE RATINGS						
TYPE NUMBER	VOLTAGE CODE	V_{RRM} , MAXIMUM REPETITIVE PEAK AND OFF-STATE VOLTAGE V	V_{RSM} , MAXIMUM NON-REPETITIVE PEAK VOLTAGE V	I_{RRM} MAXIMUM AT $T_J = 25^\circ\text{C}$ μA	I_{RRM} MAXIMUM AT $T_J = 100^\circ\text{C}$ mA	I_{RRM} MAXIMUM AT $T_J = 150^\circ\text{C}$ mA
1N3879.	-	50	75	15 ⁽¹⁾	1.0 ⁽¹⁾	3.0 ⁽¹⁾
1N3880.		100	150			
1N3881.		200	250			
1N3882.		300	350			
1N3883.		400	450			
1N3889.	-	50	75	25 ⁽¹⁾	3.0 ⁽¹⁾	5.0 ⁽¹⁾
1N3890.		100	150			
1N3891.		200	250			
1N3892.		300	350			
1N3893.		400	450			
6FL.. 12FL.. 16FL..	5	50	75	50	-	6.0
	10	100	150			
	20	200	275			
	40	400	500			
	60	600	725			
	80	800	950			
	100	1000	1250			

Note

(1) JEDEC registered values

FORWARD CONDUCTION										
PARAMETER	SYMBOL	TEST CONDITIONS			1N3879. 1N3883.	6FL..	1N3889. 1N3893. 12FL..	16FL.. UNITS		
Maximum average forward current at case temperature	I _{F(AV)}	180° conduction, half sine wave DC			6 ⁽¹⁾	6	12 ⁽¹⁾	16	A	
					100	100	100	100	°C	
Maximum RMS current	I _{F(RMS)}				9.5	9.5	19	25	A	
Maximum peak, one-cycle non-repetitive forward current	I _{FSM}	t = 10 ms	No voltage reappplied	Sinusoidal half wave, initial T _J = 150 °C	85	130	170	215		
		t = 8.3 ms			90	135	180	225		
		t = 10 ms	100 % V _{RRM} reappplied		72	110	145	180		
		t = 8.3 ms			75 ⁽¹⁾	115	150 ⁽¹⁾	190		
Maximum I ² t for fusing	I ² t	t = 10 ms	No voltage reappplied		36	86	145	230	A ² s	
		t = 8.3 ms			33	78	130	210		
		t = 10 ms	100 % V _{RRM} reappplied		26	60	103	160		
		t = 8.3 ms			23	55	94	150		
Maximum I ² √t for fusing	I ² √t	t = 0.1 to 10 ms, no voltage reappplied			363	856	1452	2290		A ² √s
Maximum forward voltage drop	V _{FM}	T _J = 25 °C; I _F = Rated I _{F(AV)} (DC)			1.4 ⁽¹⁾	1.4	1.4 ⁽¹⁾	1.4	V	
		T _C = 100 °C; I _{FM} = π x rated I _{F(AV)}			1.5 ⁽¹⁾	1.5	1.5 ⁽¹⁾	1.5	V	

Note

(1) JEDEC registered values




1N3879(R), 1N3889(R), 6/12/16FL(R) Series

Fast Recovery Diodes Vishay High Power Products
(Stud Version), 6/12/16 A

RECOVERY CHARACTERISTICS

PARAMETER	SYMBOL	TEST CONDITIONS	1N3879. 1N3883.	1N3889. 1N3893.	6FL.. 12FL.. 16FL..		UNITS
					S02	S05	
Maximum reverse recovery time	t _{rr}	T _J = 25 °C, I _F = 1 A to V _R = 30 V, dI _F /dt = 100 A/μs	150	150	-	-	ns
		T _J = 25 °C, dI _F /dt = 25 A/μs, I _{FM} = π x rated I _{F(AV)}	300 (1)	300 (1)	200	500	
Maximum peak recovery current	I _{RM(REC)}	I _{FM} = π x rated I _{F(AV)}	4 (1)	5 (1)	-		-
Maximum reverse recovery charge	Q _{rr}	T _J = 25 °C, I _F = 1 A to V _R = 30 V, dI _F /dt = 100 A/μs	400	350	-	-	nC
		T _J = 25 °C, dI _F /dt = 25 A/μs, I _{FM} = π x rated I _{F(AV)}	400	400	-	-	



Note

⁽¹⁾ JEDEC registered values

THERMAL AND MECHANICAL SPECIFICATIONS

PARAMETER	SYMBOL	TEST CONDITIONS	1N3879. 1N3883. 6FL..	1N3889. 1N3893. 12FL..	16FL..	UNITS
Maximum junction operating temperature range	T _J		- 65 to 150			°C
Maximum storage temperature range	T _{Stg}		- 65 to 175			
Maximum thermal resistance, junction to case	R _{thJC}	DC operation	2.5	2.0	1.6	°C/W
Maximum thermal resistance, case to heatsink	R _{thCS}	Mounting surface, smooth, flat and greased	0.5			
Allowable mounting torque		Not lubricated threads	1.5 + 0 - 10 % (13)			N · m (lbf · in)
		Lubricated threads	1.2 + 0 - 10 % (10)			
Approximate weight			7			g
			0.25			oz.
Case style		JEDEC	DO-203AA (DO-4)			

1N3879(R), 1N3889(R), 6/12/16FL(R) Series

Vishay High Power Products Fast Recovery Diodes
(Stud Version), 6/12/16 A



ΔR_{thJC} CONDUCTION								
CONDUCTION ANGLE	1N3879. 1N3883. 6FL..	1N3889. 1N3893. 12FL..	16FL..	1N3879. 1N3883. 6FL..	1N3889. 1N3893. 12FL..	16FL..	TEST CONDITIONS	UNITS
	SINUSOIDAL CONDUCTION			RECTANGULAR CONDUCTION				
180°	0.58	0.46	0.37	0.33	0.26	0.21	T _J = 150 °C	K/W
120°	0.60	0.48	0.39	0.58	0.46	0.37		
60°	1.28	1.02	0.82	1.28	1.02	0.82		
30°	2.20	1.76	1.41	2.20	1.76	1.41		

Note

- The table above shows the increment of thermal resistance R_{thJC} when devices operate at different conduction angles than DC




Fig. 1 - Average Forward Current vs. Maximum Allowable Case Temperature, 1N3879 and 6FL Series




Fig. 3 - Average Forward Current vs. Maximum Allowable Case Temperature, 16FL Series




Fig. 2 - Average Forward Current vs. Maximum Allowable Case Temperature, 1N3889 and 12FL Series




Fig. 4 - Reverse Recovery Time Test Waveform



1N3879(R), 1N3889(R), 6/12/16FL(R) Series

Fast Recovery Diodes Vishay High Power Products
(Stud Version), 6/12/16 A




Fig. 5 - Current Rating Nomogram (Sinusoidal Waveforms), 1N3879 and 6FL Series




Fig. 6 - Current Rating Nomogram (Rectangular Waveforms), 1N3879 and 6FL Series




Fig. 7 - Current Rating Nomogram (Sinusoidal Waveforms), 1N3889 and 12FL Series

1N3879(R), 1N3889(R), 6/12/16FL(R) Series

Vishay High Power Products Fast Recovery Diodes
(Stud Version), 6/12/16 A




Fig. 8 - Current Rating Nomogram (Rectangular Waveforms), 1N3889 and 12FL Series




Fig. 9 - Current Rating Nomogram (Sinusoidal Waveforms), 16FL Series




Fig. 10 - Current Rating Nomogram (Rectangular Waveforms), 16FL Series



1N3879(R), 1N3889(R), 6/12/16FL(R) Series

Fast Recovery Diodes
(Stud Version), 6/12/16 A

Vishay High Power Products




Fig. 11 - Maximum Forward Voltage vs. Forward Current, 1N3879 and 6FL Series




Fig. 14 - Maximum High Level Forward Power Loss vs. Average Forward Current, 1N3889 and 12FL Series




Fig. 12 - Maximum High Level Forward Power Loss vs. Average Forward Current, 1N3879 and 6FL Series




Fig. 15 - Maximum Forward Voltage vs. Forward Current, 16FL Series




Fig. 13 - Maximum Forward Voltage vs. Forward Current, 1N3889 and 12FL Series




Fig. 16 - Maximum High Level Forward Power Loss vs. Average Forward Current, 16FL Series

1N3879(R), 1N3889(R), 6/12/16FL(R) Series

Vishay High Power Products Fast Recovery Diodes
(Stud Version), 6/12/16 A




Fig. 17a - Typical Reverse Recovery Time vs. Rate of Fall of Forward Current, All Series ...S02




Fig. 18b - Typical Recovered Charge vs. Rate of Fall of Forward Current, All Series ...S05




Fig. 17b - Typical Recovered Charge vs. Rate of Fall of Forward Current, All Series ...S02




Fig. 19a - Typical Reverse Recovery Time vs. Rate of Fall of Forward Current, All Series ...S10




Fig. 18a - Typical Reverse Recovery Time vs. Rate of Fall of Forward Current, All Series ...S05




Fig. 19b - Typical Recovered Charge vs. Rate of Fall of Forward Current, All Series ...S10



1N3879(R), 1N3889(R), 6/12/16FL(R) Series

Fast Recovery Diodes Vishay High Power Products
(Stud Version), 6/12/16 A




Fig. 20 - Maximum Non-Repetitive Surge Current vs. Number of Current Pulses, 1N3879 Series




Fig. 22 - Maximum Non-Repetitive Surge Current vs. Number of Current Pulses, 1N3889 and 12FL Series




Fig. 21 - Maximum Non-Repetitive Surge Current vs. Number of Current Pulses, 6FL Series




Fig. 23 - Maximum Non-Repetitive Surge Current vs. Number of Current Pulses, 16FL Series




Fig. 24 - Maximum Transient Thermal Impedance, Junction to Case vs. Pulse Duration, All Series

1N3879(R), 1N3889(R), 6/12/16FL(R) Series

Vishay High Power Products Fast Recovery Diodes
(Stud Version), 6/12/16 A



ORDERING INFORMATION TABLE

Device code	16	F	L	R	60	M	S02
	①	②	③	④	⑤	⑥	⑦

- 1** - Current code $I_{(AVG)}$ = Exact current rating
- 2** - F = Diode
- 3** - Omit = Standard recovery diode
L = Only for fast diode
- 4** - Omit = Stud forward polarity
R = Stud reverse polarity
- 5** - Voltage code $\times 10 = V_{RRM}$ (see Voltage Ratings table)
- 6** - Outlines:
Omit = Stud base UNF thread
M = Stud base metric thread
- 7** - t_{rr} code only for fast diode (see Recovery Characteristics table)

LINKS TO RELATED DOCUMENTS	
Dimensions	http://www.vishay.com/doc?95311



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.