

F

E

D

C

B

A

F



E

D

C

B



A



詳細 D
DETAIL D
(SCALE 5:1)

注記
NOTES

1. 材料
MATERIAL
ハウジング : ガラス入り耐熱樹脂、白色、UL 94V-0
HOUSING : G.F.HEAT RESISTANT PLASTIC, WHITE, UL94V-0
ターミナル : 燐青銅
TERMINAL : PHOSPHOR BRONZE
ネイル : 黄銅
NAIL : BRASS
2. めっき仕様
PLATING
ロングターミナル
LONG TERMINAL
接点部 : 金めっき 0.25µmMIN.
CONTACT AREA : GOLD 0.25 MICROMETER MINIMUM.
半田付け部 : 錫めっき 1.0µmMIN.
SOLDER TAIL AREA : TIN 1.0 MICROMETER MINIMUM.
下地めっき : ニッケルめっき 2.0µmMIN.
UNDER-PLATING : NICKEL 2.0 MICROMETER MINIMUM.
- ショートターミナル
SHORT TERMINAL
接点部 : 金めっき 0.25µmMIN.
CONTACT AREA : GOLD 0.25 MICROMETER MINIMUM.
半田付け部 : 錫めっき 1.0µmMIN.
SOLDER TAIL AREA : TIN 1.0 MICROMETER MINIMUM.
下地めっき : ニッケルめっき 2.0µmMIN.
UNDER-PLATING : NICKEL 2.0 MICROMETER MINIMUM.
- ネイル
NAIL
錫めっき : 1.0µmMIN.
TIN : 1.0 MICROMETER MINIMUM.
下地めっき : ニッケルめっき 1.0µmMIN.
UNDER-PLATING : NICKEL 1.0 MICROMETER MINIMUM.
3. テール平坦度は、0.1 MAX. とする。
TAIL COPLANARITY TO BE 0.1 MAX.
ネイル平坦度は、0.1 MAX. とする。
NAIL COPLANARITY TO BE 0.1 MAX.
4. 本製品は54698-144*の鉛フリー品である。
THIS PRODUCT IS LEAD FREE OF 54698-144*.



1.75	2.85	1.35	3.25	4.05	***V	ハードトレイ (高さ9)	54698-7008	54698-7001*
						ハードトレイ (高さ11)	54698-7005	
						標準トレイ	54698-7002	
3.25	1.35	2.85	1.75	5.55	5.0V	ハードトレイ (高さ9)	54698-7007	
						ハードトレイ (高さ11)	54698-7004	
						標準トレイ	54698-7001	
2.5	2.1	2.1	2.5	4.8	3.3V	ハードトレイ (高さ11)	54698-7003	
						標準トレイ	54698-7000	
						パッケージトレイ	MATERIAL NO.	
E	D	C	B	A	POWER SUPPLY	PACKAGING TRAY	MATERIAL NO.	MODEL NO.



REVISED EC NO: J2013-0247 DRWN: YGOTO CHKD: MOTOHITA APPR: YOTO 2012/08/28 2012/08/28 2012/08/28	DESCRIPTION REV	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
		10 UNDER ±0.2		DRAWN BY MNAGATA		DATE 2004/05/14					
		10 OVER 30 UNDER ±0.25		CHECKED BY KTOJO		DATE 2004/05/14					
		30 OVER ±0.3		APPROVED BY MSASAO		DATE 2004/05/14					
		ANGULAR ±3 °		MATERIAL NO.		DOCUMENT NO.					
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

0.8MM PITCH S.O.DIMM
SOCKET 144CKT.H=5.2
-LEAD FREE-







molex

SD-54698-004

1 OF 3



REVISED EC NO: J2013-0247 DRWN: YGOTO CHKD: M0101TA APPR: Y0110 C	DESCRIPTION 2012/08/28 2012/08/28 2012/08/28	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION			
				MM ONLY		2:1	METRIC				
		10 UNDER	±0.2	DRAWN BY	DATE	TITLE 0.8MM PITCH S.O.DIMM SOCKET 144CKT.H=5.2 -LEAD FREE-					
		10 OVER 30 UNDER	±0.25	CHECKED BY	DATE						
		30 OVER	±0.3	APPROVED BY	DATE						
		ANGULAR ±3 °		MSASAO	2004/05/14	DOCUMENT NO. molex					
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.		SHEET NO.						
SEE CHART			SD-54698-004					2 OF 3			
REV				SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						



推奨基板寸法
RECOMMENDED MATING BOARD CONFIGURATION
(THK: 1.0±0.1)

REVISED EC NO.: J2013-0247 DRAWN: YGOTO CHKD: M.TOMITA APPR: Y.OITO	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
		10 UNDER	± 0.2	DRAWN BY MNAGATA	DATE 2004/05/14	TITLE 0.8MM PITCH S.O.DIMM SOCKET 144CKT.H=5.2 -LEAD FREE-			
		10 OVER 30 UNDER	± 0.25	CHECKED BY KTOJO	DATE 2004/05/14				
		30 OVER	± 0.3	APPROVED BY MSASAO	DATE 2004/05/14				
		ANGULAR ±3 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-54698-004		3 OF 3	
C	REV	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							