






LOC		DIST		REVISIONS				
AD	00	P	LYR	DESCRIPTION	DATE	DWN	APVD	
			C	REVISED PER ECO-11-025276	24DEC11	KH	DY	

- 1 MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- 2 FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.
- 3 FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN-LEAD
ON PCB TAILS, NICKEL OVERALL.



UNGUIDED
BACKPLANE HOLE PATTERN
(CONNECTOR SIDE)



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. K. SHOBER 24DEC11	 TE Connectivity	
DIMENSIONS:		CHK J. EABY 24DEC11		
mm		APVD J. EABY 24DEC11	NAME	
		PRODUCT SPEC	IMPACT, 3 PAIR, 16 COLUMN, HEADER	
	9 PLC ±.1 2 PLC ±0.25 3 PLC ±0.13 4 PLC ±.1 6 PLC ±.1	TOLERANCES UNLESS OTHERWISE SPECIFIED:	UNGUIDED, OPEN END WALL	
			SIGNAL MODULE, 0.39 PTH	
MATERIAL	FINISH	SEE TABLE	SIZE CAGE CODE DRAWING NO	
			A100779C=2007804	
		CUSTOMER DRAWING	WEIGHT	RESTRICTED TO
			SCALE 6:1	SHEET 1 OF 2
				REV C

LOC	DIST	REVISIONS					
AD	00	REV	LYR	DESCRIPTION	DATE	DWN	APVD
		-	-	SEE SHEET 1	-	-	-

	5.5	2007804-6
	4.9	2007804-5
	4.5	2007804-4
	5.5	2007804-3
	4.9	2007804-2
	4.5	2007804-1
FINISH	DIM M	PART NUMBER

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. K. SHOBER 24DEC11	TE Connectivity	
CHK J. EABY 24DEC11		NAME		
APVD J. EABY 24DEC11		PRODUCT SPEC	IMPACT, 3 PAIR, 16 COLUMN, HEADER	
APPLICATION SPEC		UNGUIDED, OPEN END WALL		
SIGNAL MODULE, 0.39 PTH		SIZE	CAGE CODE	DRAWING NO
RESTRICTED TO		A100779C=2007804		
MATERIAL -		WEIGHT -	REV C	
FINISH SEE TABLE		CUSTOMER DRAWING		SCALE 5:1
		SHEET 2 OF 2		