



**Part Number: 75237-2109**

Image not available

**Status:** Active - Custom  
**Series:** [75237](#)  
**Category:** Backplane Connectors  
**Overview:** [GbX® Backplane Connector System](#)

Series image - Reference only

**Mates With Part(s):**  
[75360](#) GbX® Daughtercard

#### Product Environmental Compliance

[EU RoHS:](#) RoHS Compliant by Exemption

[China RoHS:](#) 

[REACH SVHC:](#)

[Low-Halogen Status:](#) Not Reviewed

**Part Detail****General**

<b>Status</b>	<b>Active - Custom</b>
Category	Backplane Connectors
Series	<a href="#">75237</a>
Application	Backplane
Application Tooling Documents	TM-622022099
Comments	Left Guide Header, No Keying Position
Component Type	PCB Header
Overview	<a href="#">GbX® Backplane Connector System</a>
Product Name	GbX®
Style	N/A

**Physical**

Circuits (Loaded)	100
Circuits (maximum)	100
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	Yes
Keying to Mating Part	Yes
Material - Plating Mating	Gold
Number of Columns	10
Number of Pairs	5
Number of Rows	10
Orientation	Vertical
PC Tail Length	2.30mm
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	1.85mm
Pitch - Termination Interface	1.85mm
Polarized to PCB	No
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	105°C

**Electrical****(Please review the Product Specification for specific details.)**

Current - Maximum per Contact	1A
Data Rate	8.0 Gbps
Real Signals (per 25mm)	135
Shield Type	Ground Plane Shield
Shielded	Yes
Voltage - Maximum	120V AC (RMS)/DC

**Agency Certification**

UL	E29179
----	--------

**Material Info**

UPC	822350176514
-----	--------------

**Reference - Drawing Numbers**

Product Specification	PS-75221-999
Sales Drawing	SD-75237-210

**Application Tooling**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

**Global**

Description	Product #
Insertion Tool, 5-pair by 10-Wide	<a href="#">0622022030</a>
Insertion Tool, 5-pair by 20-Wide	<a href="#">0622022040</a>
Single Pin Repair Tool	<a href="#">0622022090</a>
Shield Removal Tool	<a href="#">0622022100</a>

**Previously Available Application Tooling**

[Check our list of old tooling that used to be](#)

[available for this part](#)