



English | 简体中文 | 日本語

Search Entire Site

GO

Contact IDT | Investors | Press

About IDT

Products

Applications

Support

myIDT

Document Search | Package Search | Parametric Search | Cross Reference Search | Green & RoHS | Calculators | Thermal Data | Reliability & Quality | Military

Home > Products > Clock / Timing Devices > PC-Notebook-Server Clocks > DDR I and DDR II Buffers > Zero Delay Buffers > 93777 > 93777BFLF

Add to myIDT [?]

You may also like...

93777BFLF

Category: Zero Delay Buffers

Generic Part: 93777

Market Group: PC CLOCK

Description: PC BUFFER

Product Description/Features:

- Max frequency supported = 266MHz (DDR 533)
- Low skew, low jitter PLL clock driver
- I2C address selection for dual buffer application
- I2C for functional and output control
- Feedback pins for input to output synchronization
- Spread Spectrum tolerant inputs
- 3.3V toerant CLK_INT input

Time is money

Parameters

Package	SSOP 28 (PYG28)
Voltage	3.3 V
Package	SSOP 28
Speed	NA
Temperature	C
Status	Active
Sample	Yes
Minimum Order Quantity	141
Factory Order Increment	47

Distributor Inventory

No Pricing information is available from our Distributors at this time.

Documents

Type	Title	Size	Revision Date
Misc	PC Clocks Contact Info	61 KB	05/29/2007

Package

Description	SSOP 5.3 MM
Class	PLASTIC
Moisture Sensitivity Level (MSL)	1
Category	Green
Moisture Exposure Floor Life	Unlimited @ <30°C/85% RH
Peak Reflow Temprature	260°C
Rebake Conditions	N/A
Length	10.2
Mark	PYG
Width	5.3
Pitch	0.65
Thickness	1.73
Status	Active

Home | Site Map | Legal | Careers | Contact Us | Quality | [RSS](#) What is this?

Use of this website signifies your agreement to the [acceptable use](#) and [privacy policy](#). Copyright © 1997-2008 Integrated Device Technology, Inc. All Rights Reserved.