


FEATURES:

- ✓ Test tip adapter has been designed to IEC 1010, which is the latest international safety standard.
- ✓ Snaps onto Pomona's DMM Probes with .080" (2 mm) O.D. Tips, such as model 5519A.
- ✓ Adapter allows access to hard to reach test points.
- ✓ Tip is insulated to the point to prevent shorting of adjacent components.



MATERIALS:

Tip: Stainless Steel

Tip Insulation: Kynar

Body: Polypropylene, Fire Retardant, UL94 V-2 Rated, Color: One Red, One Black

RATING:

IEC 1010-2-031, Category II, P2 Compliant

Operating Voltage: 300 Vrms/DC

Current: 3 Amperes.

ORDERING INFORMATION:

Model 6262-02 (set of one black and red probe)

Model 6262-0 (black probe only)

Model 6262-2 (red probe only)

Ordering example: 6262-2 (red probe)

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02"$ (.51 mm), .xxx = $\pm .005"$ (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[6544-02](#)